

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581783

Luminaire Tested: **HCC6S15D010MW-HM60525927-61WWWB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581783
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S15D010MW-HM60525927-61WWWB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1199.9 lumens
Efficiency: N/A
Efficacy: 85.7 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.17
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581783
CATALOG NUMBER: HCC6S15D010MW-HM60525927-61WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581783

CATALOG NUMBER: HCC6S15D010MW-HM60525927-61WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87					87			
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76					76			
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66					66			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58					58			
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52					52			
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46					46			
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42					42			
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38					38			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34					34			
10	58	46	38	34	57	45	38	33	44	38	33	43	37	33	43	37	33	31					31			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	33588	33588	33588
5°	34316	33579	32979
10°	35365	33266	32147
15°	36487	32827	31351
20°	37062	31590	30079
25°	36456	29717	28356
30°	34702	27555	26491
35°	31655	24869	24480
40°	27673	22342	22220
45°	23809	19669	20118
50°	20707	17134	17492
55°	18083	15034	15197
60°	16062	13025	11929
65°	14321	10974	9119
70°	12614	8992	7646
75°	10823	7096	7265
80°	8713	6093	7135
85°	5787	5284	6290



TEST NUMBER: P581783
 CATALOG NUMBER: HCC6S15D010MW-HM60525927-61WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.0	4.8
10°-20°	165.1	13.8
20°-30°	235.8	19.6
30°-40°	246.9	20.6
40°-50°	207.9	17.3
50°-60°	148.0	12.3
60°-70°	86.6	7.2
70°-80°	41.0	3.4
80°-90°	10.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	458.9	38.2
0°-40°	705.9	58.8
0°-60°	1061.7	88.5
0°-90°	1199.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1199.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	613	613	613	613	613	
5°	624	619	610	602	599	60
15°	643	619	578	555	552	181
25°	603	560	491	468	469	276
35°	473	434	372	359	366	294
45°	307	284	254	254	260	238
55°	189	173	157	157	159	171
65°	110	98	85	71	70	110
75°	51	43	34	33	34	55
85°	9	8	8	10	10	12
90°	0	0	0	0	0	



TEST NUMBER: P581783

CATALOG NUMBER: HCC6S15D010MW-HM60525927-61WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	612.7	612.7	612.7	612.7	612.7	612.7	612.7	612.7	612.7
2.5°	613.6	613.6	612.7	611.9	610.2	607.7	606.0	604.3	604.3
5°	623.6	621.9	618.6	614.4	610.2	605.2	601.8	599.3	599.3
7.5°	632.0	628.6	621.9	614.4	606.9	600.2	594.3	590.9	590.1
10°	635.3	631.1	621.1	609.4	597.6	588.4	581.7	577.5	577.5
12.5°	638.7	633.7	620.3	603.5	588.4	575.9	569.2	565.8	565.0
15°	642.9	636.2	619.4	598.5	578.4	564.1	554.9	552.4	552.4
17.5°	642.9	634.5	613.6	587.6	562.5	546.6	538.2	535.7	536.5
20°	635.3	626.1	601.0	569.2	541.5	524.8	516.4	514.7	515.6
22.5°	621.1	610.2	581.7	547.4	517.3	499.7	492.1	492.1	491.3
25°	602.7	590.9	560.0	524.0	491.3	473.7	467.8	468.8	468.8
27.5°	578.4	566.7	535.7	497.2	464.6	447.0	442.8	444.5	445.3
30°	548.2	535.7	503.0	465.4	435.3	417.7	415.2	417.7	418.5
32.5°	511.4	502.2	470.5	431.9	403.5	388.4	387.5	390.1	393.4
35°	473.0	462.9	433.6	398.4	371.6	359.1	359.1	363.3	365.8
37.5°	431.1	421.0	394.2	364.9	342.3	330.6	332.3	336.5	337.3
40°	386.7	379.2	356.6	331.4	312.2	303.0	305.5	309.7	310.5
42.5°	344.8	338.1	319.7	297.1	283.0	276.3	279.6	284.5	286.2
45°	307.1	299.6	284.5	265.4	253.7	250.3	254.5	257.8	259.5
47.5°	272.9	266.2	253.7	236.1	227.7	226.0	230.2	231.9	233.6
50°	242.8	236.1	223.5	207.6	200.9	200.9	204.2	205.9	205.1
52.5°	213.5	207.6	195.9	182.5	178.3	178.3	180.8	181.6	183.3
55°	189.2	183.3	173.3	160.7	157.3	155.7	157.3	157.3	159.0
57.5°	166.6	161.5	152.3	140.6	136.4	134.7	133.9	133.1	134.7
60°	146.5	142.3	132.2	122.2	118.8	114.6	111.3	107.9	108.8
62.5°	128.0	123.8	114.6	104.6	101.2	95.5	91.3	87.1	88.8
65°	110.4	106.3	98.0	89.6	84.6	77.9	71.2	68.7	70.3
67.5°	94.5	91.3	82.9	74.5	70.3	62.8	56.1	56.1	56.9
70°	78.7	75.4	68.7	61.1	56.1	49.4	46.9	47.7	47.7
72.5°	64.5	62.0	55.3	48.6	43.5	39.4	39.4	40.2	41.0
75°	51.1	49.4	42.7	36.8	33.5	31.0	32.7	33.5	34.3
77.5°	39.4	36.8	31.8	27.6	25.1	26.0	27.6	28.5	29.3
80°	27.6	26.8	22.6	20.1	19.3	20.1	21.8	22.6	22.6
82.5°	17.6	16.7	14.2	13.4	13.4	14.2	15.9	15.9	15.9
85°	9.2	8.4	7.5	7.5	8.4	9.2	10.0	10.0	10.0
87.5°	3.3	2.5	3.3	3.3	4.2	4.2	4.2	4.2	4.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)