

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581791

Luminaire Tested: **HCC6W15D010MB-HM60525930-61PSMDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581791
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W15D010MB-HM60525930-61PSMDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1294.4 lumens
Efficiency: N/A
Efficacy: 92.5 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.09 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581791
CATALOG NUMBER: HCC6W15D010MB-HM60525930-61PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P581791
 CATALOG NUMBER: HCC6W15D010MB-HM60525930-61PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78																			
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69																			
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64	62																			
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56																			
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51																			
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46																			
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43																			
9	65	53	46	41	64	53	46	41	52	46	41	51	45	41	50	45	41	39																			
10	62	50	43	38	60	49	43	38	49	42	38	48	42	38	47	42	38	36																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	46263
5°	46137
10°	45451
15°	44728
20°	43258
25°	41198
30°	37620
35°	30283
40°	20410
45°	14885
50°	12861
55°	11622
60°	11030
65°	10442
70°	9825
75°	9298
80°	8682
85°	8051



TEST NUMBER: P581791
 CATALOG NUMBER: HCC6W15D010MB-HM60525930-61PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.3	6.1
10°-20°	221.3	17.1
20°-30°	311.0	24.0
30°-40°	276.8	21.4
40°-50°	154.7	11.9
50°-60°	110.2	8.5
60°-70°	80.2	6.2
70°-80°	46.4	3.6
80°-90°	14.4	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	611.6	47.3
0°-40°	888.4	68.6
0°-60°	1153.3	89.1
0°-90°	1294.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1294.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	844	
5°	838	79
15°	788	221
25°	681	311
35°	452	277
45°	192	155
55°	122	110
65°	80	80
75°	44	46
85°	13	14
90°	0	



TEST NUMBER: P581791
CATALOG NUMBER: HCC6W15D010MB-HM60525930-61PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	843.9
2.5°	840.2
5°	838.4
7.5°	831.0
10°	816.5
12.5°	802.8
15°	788.1
17.5°	768.1
20°	741.5
22.5°	712.2
25°	681.1
27.5°	642.8
30°	594.3
32.5°	532.1
35°	452.5
37.5°	363.0
40°	285.2
42.5°	227.7
45°	192.0
47.5°	168.2
50°	150.8
52.5°	135.3
55°	121.6
57.5°	110.7
60°	100.6
62.5°	91.5
65°	80.5
67.5°	71.3
70°	61.3
72.5°	52.1
75°	43.9
77.5°	35.6
80°	27.5
82.5°	20.1
85°	12.8
87.5°	6.4
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)