

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581818

Luminaire Tested: **HCC6S15D010BZ-HM60525935-61WWW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581818
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S15D010BZ-HM60525935-61WWW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1331.8 lumens
Efficiency: N/A
Efficacy: 95.1 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581818
CATALOG NUMBER: HCC6S15D010BZ-HM60525935-61WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581818

CATALOG NUMBER: HCC6S15D010BZ-HM60525935-61WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	39191	39191	39191
5°	40936	39082	37283
10°	42044	38409	35036
15°	43088	37571	32821
20°	43281	35866	30149
25°	42371	33583	27649
30°	40196	30878	25339
35°	36513	27753	22734
40°	31817	24725	20453
45°	27522	21638	17979
50°	24042	18635	15761
55°	21237	16372	13514
60°	19099	14352	11710
65°	17097	12479	11363
70°	15259	10643	10643
75°	13238	8960	9976
80°	10639	7608	9092
85°	7296	6667	7862



TEST NUMBER: P581818
 CATALOG NUMBER: HCC6S15D010BZ-HM60525935-61WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.2	5.0
10°-20°	186.8	14.0
20°-30°	260.3	19.5
30°-40°	268.2	20.1
40°-50°	222.3	16.7
50°-60°	159.8	12.0
60°-70°	101.7	7.6
70°-80°	52.2	3.9
80°-90°	13.3	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	514.3	38.6
0°-40°	782.5	58.8
0°-60°	1164.6	87.4
0°-90°	1331.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1331.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	715	715	715	715	715	
5°	744	732	710	687	678	71
15°	759	730	662	601	578	214
25°	700	652	555	484	457	321
35°	546	501	415	360	340	339
45°	355	330	279	244	232	275
55°	222	204	171	152	141	200
65°	132	117	96	84	88	132
75°	62	54	42	44	47	67
85°	12	11	11	12	12	15
90°	0	0	0	0	0	



TEST NUMBER: P581818

CATALOG NUMBER: HCC6S15D010BZ-HM60525935-61WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	714.9	714.9	714.9	714.9	714.9	714.9	714.9	714.9	714.9
2.5°	728.4	725.5	721.7	717.9	712.1	705.3	699.6	697.7	694.7
5°	743.9	740.0	732.3	722.7	710.2	697.7	687.0	680.3	677.5
7.5°	753.4	748.6	738.1	721.7	703.4	685.1	669.8	660.1	656.3
10°	755.3	750.6	736.2	714.0	690.0	664.9	645.7	634.1	629.4
12.5°	758.3	751.5	733.2	707.2	676.5	647.6	623.6	609.2	604.3
15°	759.2	751.5	730.4	698.6	662.0	627.4	601.4	584.1	578.3
17.5°	755.3	746.7	721.7	683.2	641.8	605.3	574.4	556.2	548.4
20°	741.9	732.3	703.4	660.1	614.8	576.4	544.7	525.4	516.8
22.5°	724.6	712.1	679.3	633.2	586.0	545.6	513.8	494.6	485.9
25°	700.5	688.9	652.4	603.4	555.2	512.9	484.0	463.8	457.1
27.5°	672.6	659.1	621.6	572.5	523.5	481.1	453.2	434.9	426.3
30°	635.0	622.5	585.1	535.9	487.8	448.4	419.5	404.2	400.3
32.5°	590.9	580.2	543.7	497.5	451.3	414.7	390.7	374.3	370.5
35°	545.6	533.1	501.3	458.1	414.7	382.0	359.9	345.5	339.7
37.5°	496.6	485.0	458.1	419.5	381.0	350.3	331.0	318.5	312.7
40°	444.6	436.0	410.9	380.1	345.5	318.5	302.1	291.6	285.8
42.5°	396.5	387.8	370.5	341.6	312.7	288.6	274.2	264.6	259.8
45°	355.0	347.4	330.1	305.1	279.1	258.9	243.5	236.8	231.9
47.5°	313.7	309.9	294.4	271.4	247.3	230.0	219.4	211.7	207.8
50°	281.9	277.2	262.8	238.7	218.5	205.0	195.3	188.6	184.8
52.5°	249.2	244.4	231.0	210.8	194.4	181.8	172.3	166.5	162.6
55°	222.2	218.5	204.0	185.7	171.3	160.7	152.1	145.3	141.4
57.5°	197.3	193.4	179.9	162.6	150.2	140.5	132.8	127.0	122.2
60°	174.2	171.3	157.8	141.4	130.9	121.2	114.5	109.6	106.8
62.5°	153.9	148.2	136.7	122.2	112.6	104.9	98.2	95.2	97.2
65°	131.8	128.9	117.4	104.9	96.2	88.5	83.8	85.7	87.6
67.5°	113.5	109.6	100.1	88.5	80.8	75.0	72.2	76.0	77.0
70°	95.2	91.4	82.7	73.1	66.4	62.5	62.5	65.5	66.4
72.5°	78.0	75.0	67.3	59.7	54.8	52.0	53.9	55.8	56.8
75°	62.5	59.7	53.9	47.1	42.3	42.3	44.3	46.2	47.1
77.5°	48.1	46.2	40.4	35.6	33.7	33.7	35.6	36.5	37.6
80°	33.7	31.8	28.8	26.0	24.1	26.0	27.9	27.9	28.8
82.5°	22.1	21.2	19.3	17.4	17.4	18.3	19.3	20.2	20.2
85°	11.6	11.6	10.6	9.6	10.6	11.6	11.6	12.5	12.5
87.5°	3.9	3.9	3.9	3.9	4.8	4.8	4.8	4.8	4.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)