

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581798

Luminaire Tested: **HCC6W15D010SL-HM60525930-61WDWB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581798
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W15D010SL-HM60525930-61WDWB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1437.8 lumens
Efficiency: N/A
Efficacy: 102.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.05
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581798
CATALOG NUMBER: HCC6W15D010SL-HM60525930-61WDWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581798

CATALOG NUMBER: HCC6W15D010SL-HM60525930-61WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									50									30									10									0									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100	100	100	100	100	100																
	1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91	91	91	91	91	91	91	91	91	91	91	91																
	2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82	82	82	82	82	82	82	82	82	82	82	82																
	3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75	75	75	75	75	75	75	75	75	75	75	75																
	4	93	85	78	73	91	83	78	73	81	76	72	79	75	71	77	73	70	69	69	69	69	69	69	69	69	69	69	69	69																
	5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	65	63	63	63	63	63	63	63	63	63	63	63	63																
	6	83	73	66	61	81	72	66	61	70	65	60	69	64	60	67	63	60	58	58	58	58	58	58	58	58	58	58	58	58																
	7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54	54	54	54	54	54	54	54	54	54	54	54																
	8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50	50	50	50	50	50	50	50	50	50	50	50																
	9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	48	46	46	46	46	46	46	46	46	46	46	46	46																
	10	66	56	49	45	65	55	49	45	54	48	45	53	48	44	53	48	44	43	43	43	43	43	43	43	43	43	43	43	43																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	53631
5°	54083
10°	56033
15°	60857
20°	63309
25°	60554
30°	52261
35°	37631
40°	21197
45°	10993
50°	6550
55°	4721
60°	4002
65°	4618
70°	5850
75°	6206
80°	6061
85°	5787



TEST NUMBER: P581798
 CATALOG NUMBER: HCC6W15D010SL-HM60525930-61WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.6	6.6
10°-20°	302.5	21.0
20°-30°	452.1	31.4
30°-40°	345.6	24.0
40°-50°	120.7	8.4
50°-60°	46.0	3.2
60°-70°	36.0	2.5
70°-80°	30.5	2.1
80°-90°	9.8	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	849.1	59.1
0°-40°	1194.7	83.1
0°-60°	1361.5	94.7
0°-90°	1437.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1437.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	978	
5°	983	95
15°	1072	302
25°	1001	452
35°	562	346
45°	142	121
55°	49	46
65°	36	36
75°	29	30
85°	9	10
90°	0	



TEST NUMBER: P581798
CATALOG NUMBER: HCC6W15D010SL-HM60525930-61WDWB

CANDELA DISTRIBUTION (FULL):

0°	
0°	978.3
2.5°	975.5
5°	982.8
7.5°	992.9
10°	1006.6
12.5°	1037.6
15°	1072.3
17.5°	1093.5
20°	1085.2
22.5°	1052.3
25°	1001.1
27.5°	928.0
30°	825.6
32.5°	703.0
35°	562.3
37.5°	416.9
40°	296.2
42.5°	207.5
45°	141.8
47.5°	99.7
50°	76.8
52.5°	60.4
55°	49.4
57.5°	40.2
60°	36.5
62.5°	35.6
65°	35.6
67.5°	37.5
70°	36.5
72.5°	33.8
75°	29.3
77.5°	24.6
80°	19.2
82.5°	13.7
85°	9.2
87.5°	3.6
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)