

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581868

Luminaire Tested: **HCC6S20D010SL-HM60525830-61WDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581868
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S20D010SL-HM60525830-61WDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2129.1 lumens
Efficiency: N/A
Efficacy: 106.5 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.08
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581868
CATALOG NUMBER: HCC6S20D010SL-HM60525830-61WDH

Luminous Intensity Polar Plot





TEST NUMBER: P581868
 CATALOG NUMBER: HCC6S20D010SL-HM60525830-61WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	98	97	96	95	94	92	92	92	84																
	1	113	110	107	105	110	108	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92	92	92	92	92	92	92	92	92															
	2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84	84	81	78	77	77	77	77	77	77	77	77															
	3	100	93	87	83	98	91	86	82	89	84	81	86	83	80	84	81	78	77	77	77	77	77	77	77	77	77	77	77	77															
	4	94	86	79	75	92	85	79	74	82	77	73	80	76	72	78	75	72	70	70	70	70	70	70	70	70	70	70	70	70															
	5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64	64	64	64	64	64	64	64	64	64	64	64															
	6	83	73	67	62	82	73	66	62	71	65	61	70	65	61	68	64	60	59	59	59	59	59	59	59	59	59	59	59	59															
	7	79	68	62	57	77	68	61	57	66	60	56	65	60	56	64	59	56	54	54	54	54	54	54	54	54	54	54	54	54															
	8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	51	50	50	50	50	50	50	50	50	50	50	50	50															
	9	70	59	53	48	69	59	53	48	58	52	48	57	52	48	56	51	48	46	46	46	46	46	46	46	46	46	46	46	46															
	10	66	56	49	45	65	55	49	45	54	49	45	53	48	45	53	48	44	43	43	43	43	43	43	43	43	43	43	43	43															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	83387
5°	83942
10°	84913
15°	86652
20°	87140
25°	84422
30°	76588
35°	62272
40°	41335
45°	23002
50°	12904
55°	7159
60°	3947
65°	2983
70°	2068
75°	1546
80°	884
85°	943



TEST NUMBER: P581868
 CATALOG NUMBER: HCC6S20D010SL-HM60525830-61WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.6	6.8
10°-20°	430.5	20.2
20°-30°	634.5	29.8
30°-40°	567.5	26.7
40°-50°	246.2	11.6
50°-60°	72.3	3.4
60°-70°	23.1	1.1
70°-80°	8.2	0.4
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1210.6	56.9
0°-40°	1778.1	83.5
0°-60°	2096.7	98.5
0°-90°	2129.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2129.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1521	
5°	1525	146
15°	1527	431
25°	1396	635
35°	930	568
45°	297	246
55°	75	72
65°	23	23
75°	7	8
85°	2	1
90°	0	



TEST NUMBER: P581868
CATALOG NUMBER: HCC6S20D010SL-HM60525830-61WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1521.1
2.5°	1516.7
5°	1525.4
7.5°	1528.3
10°	1525.4
12.5°	1525.4
15°	1526.8
17.5°	1518.2
20°	1493.7
22.5°	1451.9
25°	1395.7
27.5°	1316.5
30°	1209.9
32.5°	1083.1
35°	930.5
37.5°	756.2
40°	577.6
42.5°	422.0
45°	296.7
47.5°	211.8
50°	151.3
52.5°	108.0
55°	74.9
57.5°	50.4
60°	36.0
62.5°	28.8
65°	23.0
67.5°	17.3
70°	12.9
72.5°	10.1
75°	7.3
77.5°	5.8
80°	2.8
82.5°	1.5
85°	1.5
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)