

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581808

Luminaire Tested: **HCC6S15D010MB-HM60525935-61NDW**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581808  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-3)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S15D010MB-HM60525935-61NDW  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1309.7 lumens  
Efficiency: N/A  
Efficacy: 93.6 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.03  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581808  
CATALOG NUMBER: HCC6S15D010MB-HM60525935-61NDW

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P581808

CATALOG NUMBER: HCC6S15D010MB-HM60525935-61NDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89																			
2	104	97	92	87	101	95	90	86	92	88	84	89	85	83	86	83	81	79																			
3	97	88	82	77	94	87	81	76	84	79	75	81	77	73	79	75	72	70																			
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63																			
5	84	74	67	61	83	73	66	61	71	65	60	69	64	60	67	63	59	57																			
6	79	68	61	55	77	67	60	55	66	59	55	64	59	54	63	58	54	52																			
7	74	63	56	50	73	62	55	50	61	55	50	60	54	50	58	53	49	48																			
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44																			
9	66	55	48	43	65	54	47	43	53	47	42	52	46	42	51	46	42	41																			
10	62	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	49601
5°	49373
10°	48285
15°	47146
20°	45376
25°	42916
30°	39000
35°	31568
40°	21290
45°	14622
50°	11983
55°	10494
60°	9922
65°	9365
70°	8784
75°	8366
80°	7608
85°	6667



TEST NUMBER: P581808  
 CATALOG NUMBER: HCC6S15D010MB-HM60525935-61NDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	84.7	6.5
10°-20°	233.3	17.8
20°-30°	324.1	24.7
30°-40°	288.6	22.0
40°-50°	153.2	11.7
50°-60°	100.2	7.7
60°-70°	71.8	5.5
70°-80°	41.7	3.2
80°-90°	12.2	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	642.1	49.0
0°-40°	930.7	71.1
0°-60°	1184.1	90.4
0°-90°	1309.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1309.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	905	
5°	897	85
15°	831	233
25°	710	324
35°	472	289
45°	189	153
55°	110	100
65°	72	72
75°	40	42
85°	11	12
90°	0	



TEST NUMBER: P581808  
CATALOG NUMBER: HCC6S15D010MB-HM60525935-61NDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	904.8
2.5°	900.1
5°	897.2
7.5°	886.5
10°	867.4
12.5°	850.0
15°	830.7
17.5°	806.6
20°	777.8
22.5°	745.1
25°	709.5
27.5°	668.1
30°	616.1
32.5°	553.5
35°	471.7
37.5°	381.2
40°	297.5
42.5°	231.1
45°	188.6
47.5°	160.7
50°	140.5
52.5°	124.2
55°	109.8
57.5°	99.2
60°	90.5
62.5°	81.8
65°	72.2
67.5°	63.6
70°	54.8
72.5°	47.2
75°	39.5
77.5°	31.8
80°	24.1
82.5°	17.4
85°	10.6
87.5°	4.8
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)