

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581927

Luminaire Tested: **HCC6S20D010SL-HM60525927-61WWWB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581927
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S20D010SL-HM60525927-61WWWB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1619.9 lumens
Efficiency: N/A
Efficacy: 81.0 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.09 / 1.17
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581927
CATALOG NUMBER: HCC6S20D010SL-HM60525927-61WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581927

CATALOG NUMBER: HCC6S20D010SL-HM60525927-61WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76								
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66								
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58								
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52								
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	38	34	57	45	38	33	44	38	33	43	37	33	43	37	33	31								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	45347	45347	45347
5°	46324	45333	44524
10°	47745	44911	43403
15°	49257	44319	42333
20°	50037	42651	40609
25°	49213	40127	38276
30°	46855	37196	35765
35°	42724	33575	33047
40°	37363	30164	29999
45°	32151	26545	27158
50°	27948	23129	23615
55°	24410	20300	20520
60°	21676	17586	16117
65°	19354	14801	12310
70°	17038	12133	10322
75°	14594	9574	9807
80°	11775	8177	9629
85°	7862	7108	8554



TEST NUMBER: P581927
 CATALOG NUMBER: HCC6S20D010SL-HM60525927-61WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.3	4.8
10°-20°	223.0	13.8
20°-30°	318.3	19.6
30°-40°	333.4	20.6
40°-50°	280.7	17.3
50°-60°	199.8	12.3
60°-70°	116.9	7.2
70°-80°	55.3	3.4
80°-90°	14.2	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	619.5	38.2
0°-40°	952.9	58.8
0°-60°	1433.4	88.5
0°-90°	1619.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1619.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	827	827	827	827	827	
5°	842	835	824	812	809	81
15°	868	836	781	749	746	245
25°	814	756	663	632	633	372
35°	638	585	502	485	494	397
45°	415	384	342	344	350	322
55°	255	234	212	212	215	230
65°	149	132	114	96	95	149
75°	69	58	45	44	46	74
85°	12	10	11	14	14	16
90°	0	0	0	0	0	



TEST NUMBER: P581927

CATALOG NUMBER: HCC6S20D010SL-HM60525927-61WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	827.2	827.2	827.2	827.2	827.2	827.2	827.2	827.2	827.2
2.5°	828.3	828.3	827.2	826.1	823.8	820.4	818.1	815.9	815.9
5°	841.8	839.6	835.1	829.5	823.8	817.0	812.5	809.1	809.1
7.5°	853.1	848.6	839.6	829.5	819.3	810.2	802.3	797.7	796.6
10°	857.7	852.0	838.4	822.7	806.8	794.3	785.4	779.7	779.7
12.5°	862.2	855.4	837.3	814.7	794.3	777.5	768.4	763.9	762.7
15°	867.9	858.8	836.3	807.9	780.9	761.6	749.3	745.9	745.9
17.5°	867.9	856.5	828.3	793.3	759.3	737.9	726.6	723.2	724.3
20°	857.7	845.2	811.3	768.4	731.1	708.5	697.2	695.0	696.1
22.5°	838.4	823.8	785.4	739.1	698.4	674.6	664.5	664.5	663.4
25°	813.6	797.7	755.9	707.4	663.4	639.6	631.6	632.8	632.8
27.5°	780.9	765.0	723.2	671.2	627.1	603.4	597.8	600.0	601.2
30°	740.2	723.2	679.1	628.2	587.6	563.9	560.5	563.9	565.0
32.5°	690.5	678.0	635.0	583.0	544.6	524.4	523.2	526.6	531.2
35°	638.4	624.8	585.3	537.8	501.7	484.8	484.8	490.5	493.8
37.5°	581.9	568.4	532.3	492.7	462.2	446.4	448.7	454.2	455.4
40°	522.1	511.9	481.4	447.5	421.5	409.0	412.4	418.1	419.2
42.5°	465.5	456.5	431.7	401.2	381.9	372.9	377.4	384.2	386.5
45°	414.7	404.6	384.2	358.3	342.4	337.9	343.5	348.1	350.3
47.5°	368.3	359.4	342.4	318.7	307.4	305.1	310.8	313.0	315.3
50°	327.7	318.7	301.7	280.2	271.2	271.2	275.8	278.0	276.9
52.5°	288.1	280.2	264.4	246.3	240.6	240.6	244.0	245.2	247.4
55°	255.4	247.4	234.0	217.0	212.4	210.2	212.4	212.4	214.7
57.5°	224.9	218.1	205.6	189.9	184.2	182.0	180.8	179.7	182.0
60°	197.7	192.2	178.6	165.0	160.4	154.8	150.2	145.8	147.0
62.5°	172.9	167.2	154.8	141.3	136.8	128.8	123.2	117.5	119.8
65°	149.2	143.6	132.2	120.9	114.1	105.1	96.1	92.7	94.9
67.5°	127.7	123.2	111.8	100.6	94.9	84.7	75.7	75.7	76.8
70°	106.3	101.7	92.7	82.5	75.7	66.6	63.3	64.4	64.4
72.5°	87.0	83.6	74.6	65.5	58.8	53.1	53.1	54.3	55.4
75°	68.9	66.6	57.7	49.7	45.2	41.8	44.1	45.2	46.3
77.5°	53.1	49.7	42.9	37.3	33.9	35.0	37.3	38.4	39.5
80°	37.3	36.1	30.5	27.1	25.9	27.1	29.3	30.5	30.5
82.5°	23.7	22.5	19.3	18.1	18.1	19.3	21.4	21.4	21.4
85°	12.5	11.3	10.2	10.2	11.3	12.5	13.6	13.6	13.6
87.5°	4.5	3.4	4.5	4.5	5.7	5.7	5.7	5.7	5.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)