

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581919

Luminaire Tested: **HCC6W20D010MB-HM60525927-61RWWH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581919
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W20D010MB-HM60525927-61RWWH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1690.0 lumens
Efficiency: N/A
Efficacy: 84.5 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.12 / 1.19
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581919
CATALOG NUMBER: HCC6W20D010MB-HM60525927-61RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581919

CATALOG NUMBER: HCC6W20D010MB-HM60525927-61RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77								
3	95	86	79	74	93	84	78	73	82	76	72	79	74	70	77	73	69	67								
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59								
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	50	74	63	56	50	61	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	47277	47277	47277
5°	47771	47336	47023
10°	48452	47194	46693
15°	49592	46896	46447
20°	50049	45504	45632
25°	48952	43212	44035
30°	46368	40139	41506
35°	41981	36694	38046
40°	36561	33162	34379
45°	31026	29352	30406
50°	27470	25645	26319
55°	24200	21925	21820
60°	21687	18474	16983
65°	19354	14814	12167
70°	17038	10691	7613
75°	14382	6460	4321
80°	11049	2873	1799
85°	6416	692	692



TEST NUMBER: P581919
 CATALOG NUMBER: HCC6W20D010MB-HM60525927-61RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.9	4.8
10°-20°	235.3	13.9
20°-30°	340.1	20.1
30°-40°	357.9	21.2
40°-50°	300.9	17.8
50°-60°	211.2	12.5
60°-70°	116.2	6.9
70°-80°	41.3	2.4
80°-90°	5.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	657.3	38.9
0°-40°	1015.2	60.1
0°-60°	1527.2	90.4
0°-90°	1690.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1690.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	862	862	862	862	862	
5°	868	866	860	857	854	83
15°	874	859	826	816	818	247
25°	809	769	714	716	728	370
35°	627	591	548	560	568	389
45°	400	389	379	388	392	314
55°	253	240	229	229	228	228
65°	149	133	114	94	94	148
75°	68	54	30	20	20	73
85°	10	6	1	1	1	14
90°	0	0	0	0	0	



TEST NUMBER: P581919

CATALOG NUMBER: HCC6W20D010MB-HM60525927-61RWWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	862.4	862.4	862.4	862.4	862.4	862.4	862.4	862.4	862.4
2.5°	862.4	862.4	861.3	861.3	859.0	859.0	857.9	857.9	857.9
5°	868.1	868.1	865.8	862.4	860.2	856.8	856.8	855.6	854.5
7.5°	871.5	870.4	867.0	862.4	856.8	851.1	849.0	850.0	849.0
10°	870.4	868.1	863.6	854.5	847.8	839.9	838.8	837.6	838.8
12.5°	872.6	869.2	860.2	849.0	837.6	828.6	827.4	827.4	828.6
15°	873.8	870.4	859.0	842.2	826.3	817.2	816.1	817.2	818.4
17.5°	870.4	865.8	849.0	826.3	808.2	799.2	799.2	801.4	803.6
20°	857.9	851.1	827.4	800.4	780.0	773.2	775.4	780.0	782.2
22.5°	835.4	827.4	800.4	769.8	748.3	742.7	748.3	753.9	756.2
25°	809.3	800.4	768.6	737.0	714.4	707.6	715.5	724.6	728.0
27.5°	774.3	764.1	734.8	698.6	675.9	672.5	681.6	691.8	694.1
30°	732.5	721.2	688.4	654.5	634.1	633.0	643.2	652.3	655.7
32.5°	681.6	671.4	643.2	609.2	591.2	591.2	601.4	609.2	612.6
35°	627.3	616.0	591.2	562.9	548.3	549.4	559.5	565.1	568.5
37.5°	562.9	559.5	540.3	516.5	506.5	508.7	516.5	521.1	524.5
40°	510.9	501.9	489.5	470.2	463.4	465.7	473.6	478.1	480.4
42.5°	454.4	448.8	438.6	425.0	420.5	423.9	430.7	434.1	432.9
45°	400.2	399.0	388.8	380.9	378.6	383.2	387.7	391.1	392.2
47.5°	360.6	356.1	347.0	341.4	339.1	343.6	348.2	350.4	350.4
50°	322.1	317.6	308.6	303.0	300.7	305.2	308.6	310.9	308.6
52.5°	283.7	279.2	271.2	264.6	263.4	265.7	266.8	267.8	270.1
55°	253.2	248.7	239.6	231.7	229.4	230.6	229.4	229.4	228.3
57.5°	223.8	219.2	210.3	201.2	197.8	196.7	193.3	192.2	191.0
60°	197.8	192.2	183.1	172.9	168.5	163.9	158.3	154.9	154.9
62.5°	172.9	167.3	157.1	148.1	141.3	133.4	124.3	119.9	119.9
65°	149.2	144.7	133.4	123.2	114.2	104.0	93.8	91.5	93.8
67.5°	126.6	122.0	110.8	100.6	89.3	76.8	67.9	67.9	70.1
70°	106.3	101.7	91.5	79.1	66.7	54.3	47.5	47.5	47.5
72.5°	87.0	82.5	71.3	59.9	47.5	35.0	31.6	32.7	31.6
75°	67.9	64.5	54.3	41.8	30.5	21.5	20.4	19.3	20.4
77.5°	50.9	47.5	38.4	27.1	17.0	12.5	11.3	11.3	11.3
80°	35.0	31.6	24.8	15.9	9.1	5.7	5.7	5.7	5.7
82.5°	21.5	18.1	13.6	7.9	3.4	3.4	3.4	3.4	3.4
85°	10.2	7.9	5.7	2.3	1.1	1.1	1.1	1.1	1.1
87.5°	2.3	2.3	1.1	1.1	0.0	1.1	1.1	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)