

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581953

Luminaire Tested: **HCC6W20D010MW-HM60525935-61RWWC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581953
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W20D010MW-HM60525935-61RWWC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1935.7 lumens
Efficiency: N/A
Efficacy: 96.8 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.15 / 1.2
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581953
CATALOG NUMBER: HCC6W20D010MW-HM60525935-61RWWC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581953

CATALOG NUMBER: HCC6W20D010MW-HM60525935-61RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88								
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77								
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	69	68								
4	88	78	70	64	86	76	69	64	74	68	63	72	67	62	70	65	61	60								
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	50	74	63	56	50	62	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	45	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	52567	52567	52567
5°	52834	53120	53120
10°	54313	53378	53155
15°	56039	53678	53678
20°	56693	52446	53665
25°	55558	49823	52182
30°	52546	46305	49014
35°	47556	42342	44430
40°	41378	38300	39796
45°	35353	34143	35353
50°	31027	29918	31138
55°	27067	25213	26207
60°	23924	20941	20656
65°	21234	16513	14152
70°	18737	11653	8543
75°	15949	6608	4130
80°	11902	2052	1231
85°	6542	755	755



TEST NUMBER: P581953
 CATALOG NUMBER: HCC6W20D010MW-HM60525935-61RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.0	4.8
10°-20°	269.1	13.9
20°-30°	393.0	20.3
30°-40°	412.2	21.3
40°-50°	347.2	17.9
50°-60°	243.3	12.6
60°-70°	130.4	6.7
70°-80°	43.7	2.3
80°-90°	4.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	754.1	39.0
0°-40°	1166.2	60.2
0°-60°	1756.8	90.8
0°-90°	1935.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1935.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	959	959	959	959	959	
5°	960	964	965	965	965	92
15°	987	974	946	941	946	279
25°	918	880	824	838	863	421
35°	711	674	633	651	664	441
45°	456	448	440	452	456	355
55°	283	274	264	269	274	255
65°	164	149	127	105	109	163
75°	75	58	31	20	20	80
85°	10	5	1	1	1	14
90°	0	0	0	0	0	



TEST NUMBER: P581953

CATALOG NUMBER: HCC6W20D010MW-HM60525935-61RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	958.9	958.9	958.9	958.9	958.9	958.9	958.9	958.9	958.9
2.5°	952.3	952.3	954.9	957.5	960.1	960.1	961.4	962.7	961.4
5°	960.1	960.1	964.0	965.3	965.3	964.0	965.3	965.3	965.3
7.5°	971.8	969.2	970.5	967.9	965.3	964.0	962.7	962.7	962.7
10°	975.7	973.1	970.5	965.3	958.9	954.9	953.6	954.9	954.9
12.5°	980.8	978.3	971.8	961.4	953.6	947.1	945.8	948.4	948.4
15°	987.4	984.8	974.4	957.5	945.8	939.4	940.6	943.2	945.8
17.5°	987.4	982.2	965.3	943.2	928.9	922.4	927.6	934.2	938.0
20°	971.8	966.6	943.2	915.9	899.0	895.2	904.2	915.9	919.9
22.5°	951.0	940.6	913.3	880.9	862.7	862.7	875.7	890.0	895.2
25°	918.5	910.7	879.5	841.9	823.7	822.4	838.0	857.5	862.7
27.5°	882.2	871.7	838.0	799.0	779.5	780.9	797.7	817.2	822.4
30°	830.1	817.2	787.3	749.6	731.5	736.7	753.6	767.8	774.3
32.5°	771.7	760.0	732.7	697.7	682.1	687.3	701.6	714.6	719.8
35°	710.6	697.7	674.2	643.1	632.7	637.9	650.9	661.3	663.9
37.5°	641.8	632.7	615.8	591.1	583.4	589.8	600.3	606.7	609.3
40°	578.2	570.4	556.1	537.8	535.2	540.4	550.9	554.7	556.1
42.5°	515.7	509.3	500.2	487.2	487.2	492.4	501.5	504.1	505.4
45°	456.0	452.1	448.2	437.8	440.4	447.0	452.1	456.0	456.0
47.5°	404.0	405.4	400.2	392.4	395.0	401.4	405.4	409.2	409.2
50°	363.8	359.8	354.6	346.9	350.8	356.0	361.2	363.8	365.1
52.5°	317.0	315.7	311.8	302.7	305.3	307.9	313.2	317.0	318.3
55°	283.2	279.3	274.2	263.8	263.8	266.4	269.0	271.6	274.2
57.5°	250.7	246.9	239.1	227.4	226.0	226.0	224.8	227.4	231.2
60°	218.2	217.0	205.3	194.9	191.0	187.1	181.8	183.2	188.4
62.5°	189.7	187.1	176.6	163.7	155.9	149.4	142.9	141.6	146.8
65°	163.7	161.1	149.4	136.4	127.3	115.7	105.3	105.3	109.1
67.5°	140.3	135.2	124.7	110.5	98.7	84.4	74.1	76.7	78.0
70°	116.9	113.1	101.3	87.0	72.7	58.5	52.0	53.3	53.3
72.5°	96.2	91.0	79.2	64.9	50.6	37.7	35.1	33.8	33.8
75°	75.3	70.1	58.5	44.2	31.2	22.1	19.5	19.5	19.5
77.5°	54.6	50.6	40.2	27.3	16.9	10.4	9.1	7.8	7.8
80°	37.7	33.8	24.7	14.3	6.5	3.9	3.9	3.9	3.9
82.5°	22.1	18.2	11.7	6.5	2.6	1.2	1.2	1.2	1.2
85°	10.4	7.8	5.2	2.6	1.2	1.2	1.2	1.2	1.2
87.5°	1.2	1.2	1.2	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)