

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593137

Luminaire Tested: **HCC6S20D010BZ-HM60525850-61RWWC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593137
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S20D010BZ-HM60525850-61RWWC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2249.6 lumens
Efficiency: N/A
Efficacy: 112.5 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.15 / 1.2
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593137
CATALOG NUMBER: HCC6S20D010BZ-HM60525850-61RWWC

Luminous Intensity Polar Plot





TEST NUMBER: P593137

CATALOG NUMBER: HCC6S20D010BZ-HM60525850-61RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88								
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77								
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	69	68								
4	88	78	70	64	86	76	69	64	74	68	63	72	67	62	70	65	61	60								
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	50	74	63	56	50	62	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	45	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	61086	61086	61086
5°	61402	61732	61732
10°	63120	62028	61778
15°	65125	62384	62384
20°	65887	60958	62364
25°	64570	57905	60645
30°	61079	53812	56964
35°	55278	49209	51638
40°	48083	44512	46251
45°	41090	39686	41090
50°	36050	34771	36186
55°	31454	29294	30451
60°	27816	24340	24000
65°	24672	19198	16448
70°	21766	13544	9922
75°	18554	7689	4808
80°	13796	2399	1421
85°	7611	943	943



TEST NUMBER: P593137
 CATALOG NUMBER: HCC6S20D010BZ-HM60525850-61RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.9	4.8
10°-20°	312.7	13.9
20°-30°	456.7	20.3
30°-40°	479.0	21.3
40°-50°	403.6	17.9
50°-60°	282.7	12.6
60°-70°	151.6	6.7
70°-80°	50.8	2.3
80°-90°	5.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	876.4	39.0
0°-40°	1355.4	60.2
0°-60°	2041.7	90.8
0°-90°	2249.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2249.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1114	1114	1114	1114	1114	
5°	1116	1120	1122	1122	1122	107
15°	1148	1132	1099	1093	1099	324
25°	1068	1022	957	974	1003	489
35°	826	784	735	756	772	513
45°	530	521	512	526	530	413
55°	329	319	306	313	319	296
65°	190	174	148	122	127	190
75°	88	68	36	23	23	93
85°	12	6	2	2	2	17
90°	0	0	0	0	0	



TEST NUMBER: P593137

CATALOG NUMBER: HCC6S20D010BZ-HM60525850-61RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1114.3	1114.3	1114.3	1114.3	1114.3	1114.3	1114.3	1114.3	1114.3
2.5°	1106.7	1106.7	1109.8	1112.8	1115.8	1115.8	1117.4	1118.8	1117.4
5°	1115.8	1115.8	1120.3	1121.8	1121.8	1120.3	1121.8	1121.8	1121.8
7.5°	1129.4	1126.3	1127.9	1124.8	1121.8	1120.3	1118.8	1118.8	1118.8
10°	1133.9	1130.8	1127.9	1121.8	1114.3	1109.8	1108.3	1109.8	1109.8
12.5°	1139.9	1137.0	1129.4	1117.4	1108.3	1100.7	1099.2	1102.2	1102.2
15°	1147.5	1144.4	1132.4	1112.8	1099.2	1091.6	1093.1	1096.2	1099.2
17.5°	1147.5	1141.5	1121.8	1096.2	1079.5	1072.0	1078.0	1085.6	1090.2
20°	1129.4	1123.4	1096.2	1064.5	1044.9	1040.3	1050.9	1064.5	1069.0
22.5°	1105.2	1093.1	1061.4	1023.7	1002.6	1002.6	1017.7	1034.3	1040.3
25°	1067.5	1058.4	1022.2	978.3	957.3	955.8	973.8	996.5	1002.6
27.5°	1025.3	1013.1	973.8	928.6	905.9	907.4	927.0	949.7	955.8
30°	964.9	949.7	915.0	871.2	850.1	856.1	875.7	892.4	899.9
32.5°	896.9	883.3	851.6	810.8	792.6	798.8	815.3	830.4	836.5
35°	826.0	810.8	783.6	747.4	735.3	741.3	756.5	768.5	771.6
37.5°	745.9	735.3	715.7	686.9	678.0	685.5	697.6	705.1	708.1
40°	671.9	662.8	646.3	625.1	622.0	628.1	640.1	644.7	646.3
42.5°	599.5	591.9	581.3	566.2	566.2	572.3	582.8	585.9	587.3
45°	530.0	525.5	521.0	508.8	511.9	519.4	525.5	530.0	530.0
47.5°	469.5	471.1	465.1	456.0	459.0	466.6	471.1	475.6	475.6
50°	422.7	418.2	412.2	403.1	407.7	413.7	419.8	422.7	424.3
52.5°	368.5	366.9	362.3	351.8	354.9	357.8	363.9	368.5	369.9
55°	329.1	324.6	318.6	306.5	306.5	309.5	312.6	315.5	318.6
57.5°	291.4	286.9	277.8	264.2	262.7	262.7	261.2	264.2	268.7
60°	253.7	252.2	238.6	226.5	222.0	217.4	211.4	212.9	218.9
62.5°	220.5	217.4	205.3	190.2	181.2	173.7	166.1	164.6	170.6
65°	190.2	187.2	173.7	158.5	148.0	134.4	122.3	122.3	126.8
67.5°	163.0	157.0	144.9	128.4	114.8	98.1	86.1	89.1	90.6
70°	135.8	131.3	117.7	101.2	84.5	68.0	60.4	61.9	61.9
72.5°	111.7	105.7	92.1	75.5	58.9	43.7	40.8	39.2	39.2
75°	87.6	81.6	68.0	51.3	36.3	25.7	22.7	22.7	22.7
77.5°	63.4	58.9	46.8	31.7	19.6	12.1	10.5	9.1	9.1
80°	43.7	39.2	28.7	16.7	7.6	4.5	4.5	4.5	4.5
82.5°	25.7	21.2	13.6	7.6	3.1	1.5	1.5	1.5	1.5
85°	12.1	9.1	6.0	3.1	1.5	1.5	1.5	1.5	1.5
87.5°	1.5	1.5	1.5	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)