

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581930

Luminaire Tested: **HCC6S20D010MW-HM60525930-61MDH**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581930  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-5)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S20D010MW-HM60525930-61MDH  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1748.6 lumens  
Efficiency: N/A  
Efficacy: 87.4 lumens/watt  
Spacing Criteria (0/90/45): 1.01 / 1.01 / 0.97  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 20  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581930  
CATALOG NUMBER: HCC6S20D010MW-HM60525930-61MDH

### Luminous Intensity Polar Plot





TEST NUMBER: P581930  
 CATALOG NUMBER: HCC6S20D010MW-HM60525930-61MDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	94	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79			79
4	96	88	82	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72			72
5	90	81	75	71	89	80	75	70	79	74	70	77	73	69	75	72	68	67			67
6	85	76	70	65	84	75	69	65	74	68	64	72	67	64	71	67	63	62			62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57			57
8	77	67	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53			53
9	73	62	56	52	72	62	56	52	61	56	52	60	55	52	59	55	51	50			50
10	69	59	53	49	68	58	52	48	57	52	48	57	52	48	56	51	48	47			47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	87575
5°	87508
10°	86594
15°	84853
20°	80379
25°	72591
30°	61655
35°	45528
40°	26328
45°	13978
50°	7897
55°	4129
60°	2708
65°	1920
70°	1378
75°	1059
80°	789
85°	755



TEST NUMBER: P581930  
 CATALOG NUMBER: HCC6S20D010MW-HM60525930-61MDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	150.7	8.6
10°-20°	418.2	23.9
20°-30°	545.8	31.2
30°-40°	417.1	23.9
40°-50°	151.0	8.6
50°-60°	43.9	2.5
60°-70°	15.6	0.9
70°-80°	5.4	0.3
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1114.7	63.7
0°-40°	1531.7	87.6
0°-60°	1726.6	98.7
0°-90°	1748.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1748.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1598	
5°	1590	151
15°	1495	418
25°	1200	546
35°	680	417
45°	180	151
55°	43	44
65°	15	16
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P581930  
CATALOG NUMBER: HCC6S20D010MW-HM60525930-61MDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1597.5
2.5°	1590.2
5°	1590.2
7.5°	1579.1
10°	1555.6
12.5°	1528.4
15°	1495.1
17.5°	1445.7
20°	1377.8
22.5°	1293.9
25°	1200.1
27.5°	1093.8
30°	974.0
32.5°	839.6
35°	680.3
37.5°	513.6
40°	367.9
42.5°	254.4
45°	180.3
47.5°	129.6
50°	92.6
52.5°	65.5
55°	43.2
57.5°	30.8
60°	24.7
62.5°	19.7
65°	14.8
67.5°	12.3
70°	8.6
72.5°	6.1
75°	5.0
77.5°	3.7
80°	2.5
82.5°	1.2
85°	1.2
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)