

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581934

Luminaire Tested: **HCC6W20D010SL-HM60525930-61NDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581934
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W20D010SL-HM60525930-61NDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1679.6 lumens
Efficiency: N/A
Efficacy: 84.0 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.03
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581934
CATALOG NUMBER: HCC6W20D010SL-HM60525930-61NDW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581934

CATALOG NUMBER: HCC6W20D010SL-HM60525930-61NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89					89			
2	104	97	92	87	101	95	90	86	92	88	84	89	85	83	86	83	81	79					79			
3	97	88	82	77	94	87	81	76	84	79	75	81	77	73	79	75	72	70					70			
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63					63			
5	84	74	67	61	83	73	66	61	71	65	60	69	64	60	67	63	59	57					57			
6	79	68	61	55	77	67	60	55	66	59	55	64	59	54	63	58	54	52					52			
7	74	63	56	50	73	62	55	50	61	55	50	60	54	50	58	53	49	48					48			
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44					44			
9	66	55	48	43	65	54	47	43	53	47	42	52	46	42	51	46	42	41					41			
10	62	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38					38			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	63613
5°	63317
10°	61917
15°	60466
20°	58193
25°	55031
30°	50008
35°	40482
40°	27301
45°	18762
50°	15377
55°	13448
60°	12718
65°	12012
70°	11284
75°	10718
80°	9723
85°	8554



TEST NUMBER: P581934
 CATALOG NUMBER: HCC6W20D010SL-HM60525930-61NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.6	6.5
10°-20°	299.2	17.8
20°-30°	415.7	24.7
30°-40°	370.1	22.0
40°-50°	196.5	11.7
50°-60°	128.5	7.6
60°-70°	92.1	5.5
70°-80°	53.4	3.2
80°-90°	15.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	823.5	49.0
0°-40°	1193.6	71.1
0°-60°	1518.5	90.4
0°-90°	1679.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1679.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1160	
5°	1151	109
15°	1065	299
25°	910	416
35°	605	370
45°	242	196
55°	141	128
65°	93	92
75°	51	53
85°	14	16
90°	0	



TEST NUMBER: P581934
CATALOG NUMBER: HCC6W20D010SL-HM60525930-61NDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1160.4
2.5°	1154.2
5°	1150.6
7.5°	1137.0
10°	1112.3
12.5°	1090.1
15°	1065.4
17.5°	1034.5
20°	997.5
22.5°	955.5
25°	909.8
27.5°	856.8
30°	790.0
32.5°	709.8
35°	604.9
37.5°	488.9
40°	381.5
42.5°	296.3
45°	242.0
47.5°	206.2
50°	180.3
52.5°	159.3
55°	140.7
57.5°	127.1
60°	116.0
62.5°	104.9
65°	92.6
67.5°	81.5
70°	70.4
72.5°	60.5
75°	50.6
77.5°	40.8
80°	30.8
82.5°	22.2
85°	13.6
87.5°	6.1
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)