

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581955

Luminaire Tested: **HCC6S20D010SL-HM60525935-61WDBB**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581955  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-11)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S20D010SL-HM60525935-61WDBB  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1714.8 lumens  
Efficiency: N/A  
Efficacy: 85.7 lumens/watt  
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.14  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 20  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581955  
CATALOG NUMBER: HCC6S20D010SL-HM60525935-61WDBB

### Luminous Intensity Polar Plot





TEST NUMBER: P581955

CATALOG NUMBER: HCC6S20D010SL-HM60525935-61WDBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92					92			
2	107	101	97	93	104	100	95	92	96	93	90	93	91	88	90	88	86	85					85			
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77					77			
4	95	86	80	75	93	85	79	75	83	78	74	81	77	73	79	75	72	71					71			
5	89	80	73	68	87	79	73	68	77	72	67	75	70	67	73	69	66	65					65			
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59					59			
7	79	68	62	57	77	68	61	57	66	61	57	65	60	56	64	59	56	54					54			
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52	50					50			
9	70	59	53	48	69	59	53	48	58	52	48	57	52	48	56	51	48	46					46			
10	66	56	49	45	65	55	49	45	54	49	45	53	48	44	53	48	44	43					43			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	60900
5°	61352
10°	62418
15°	64893
20°	67620
25°	70026
30°	69087
35°	57567
40°	36919
45°	18436
50°	7317
55°	2475
60°	713
65°	506
70°	417
75°	551
80°	379
85°	0



TEST NUMBER: P581955  
 CATALOG NUMBER: HCC6S20D010SL-HM60525935-61WDBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	106.6	6.2
10°-20°	324.3	18.9
20°-30°	529.5	30.9
30°-40°	519.1	30.3
40°-50°	199.1	11.6
50°-60°	29.2	1.7
60°-70°	4.3	0.3
70°-80°	2.2	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	960.4	56.0
0°-40°	1479.6	86.3
0°-60°	1707.8	99.6
0°-90°	1714.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1714.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1111	
5°	1115	107
15°	1143	324
25°	1158	530
35°	860	519
45°	238	199
55°	26	29
65°	4	4
75°	3	2
85°	0	0
90°	0	



TEST NUMBER: P581955  
CATALOG NUMBER: HCC6S20D010SL-HM60525935-61WDBB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1110.9
2.5°	1108.3
5°	1114.9
7.5°	1118.7
10°	1121.3
12.5°	1130.4
15°	1143.4
17.5°	1153.8
20°	1159.1
22.5°	1160.3
25°	1157.7
27.5°	1139.6
30°	1091.4
32.5°	1000.6
35°	860.2
37.5°	687.4
40°	515.9
42.5°	367.8
45°	237.8
47.5°	145.5
50°	85.8
52.5°	49.4
55°	25.9
57.5°	11.7
60°	6.5
62.5°	5.2
65°	3.9
67.5°	3.9
70°	2.6
72.5°	2.6
75°	2.6
77.5°	1.2
80°	1.2
82.5°	1.2
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)