

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581954

Luminaire Tested: **HCC6S20D010SL-HM60525935-61RWWH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581954
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S20D010SL-HM60525935-61RWWH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1942.2 lumens
Efficiency: N/A
Efficacy: 97.1 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.12 / 1.19
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581954
CATALOG NUMBER: HCC6S20D010SL-HM60525935-61RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581954

CATALOG NUMBER: HCC6S20D010SL-HM60525935-61RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77								
3	95	86	79	74	93	84	78	73	82	76	72	79	74	70	77	73	69	67								
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59								
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	50	74	63	56	50	61	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	54332	54332	54332
5°	54903	54397	54045
10°	55683	54235	53662
15°	56992	53894	53377
20°	57516	52289	52440
25°	56259	49660	50604
30°	53287	46127	47691
35°	48245	42168	43728
40°	42014	38114	39510
45°	35655	33740	34949
50°	31581	29475	30242
55°	27813	25213	25079
60°	24921	21215	19516
65°	22233	17019	13996
70°	19571	12278	8751
75°	16521	7434	4935
80°	12691	3283	2052
85°	7359	755	755



TEST NUMBER: P581954
 CATALOG NUMBER: HCC6S20D010SL-HM60525935-61RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.1	4.8
10°-20°	270.4	13.9
20°-30°	390.9	20.1
30°-40°	411.3	21.2
40°-50°	345.8	17.8
50°-60°	242.7	12.5
60°-70°	133.5	6.9
70°-80°	47.4	2.4
80°-90°	6.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	755.4	38.9
0°-40°	1166.7	60.1
0°-60°	1755.1	90.4
0°-90°	1942.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1942.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	991	991	991	991	991	
5°	998	995	988	985	982	95
15°	1004	987	950	938	940	283
25°	930	883	821	822	837	426
35°	721	680	630	643	653	447
45°	460	447	435	446	451	361
55°	291	275	264	264	262	262
65°	171	153	131	108	108	171
75°	78	62	35	23	23	84
85°	12	6	1	1	1	16
90°	0	0	0	0	0	



TEST NUMBER: P581954

CATALOG NUMBER: HCC6S20D010SL-HM60525935-61RWWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	991.1	991.1	991.1	991.1	991.1	991.1	991.1	991.1	991.1
2.5°	991.1	991.1	989.9	989.9	987.3	987.3	985.9	985.9	985.9
5°	997.7	997.7	995.1	991.1	988.5	984.7	984.7	983.4	982.1
7.5°	1001.6	1000.3	996.4	991.1	984.7	978.2	975.6	976.9	975.6
10°	1000.3	997.7	992.5	982.1	974.3	965.2	964.0	962.6	964.0
12.5°	1002.9	999.0	988.5	975.6	962.6	952.2	950.9	950.9	952.2
15°	1004.2	1000.3	987.3	967.8	949.6	939.3	937.9	939.3	940.5
17.5°	1000.3	995.1	975.6	949.6	928.8	918.4	918.4	921.0	923.6
20°	985.9	978.2	950.9	919.8	896.3	888.6	891.1	896.3	898.9
22.5°	960.0	950.9	919.8	884.6	859.9	853.5	859.9	866.5	869.1
25°	930.1	919.8	883.4	847.0	821.0	813.3	822.3	832.6	836.6
27.5°	889.9	878.2	844.4	802.8	776.8	772.9	783.4	795.0	797.6
30°	841.8	828.8	791.2	752.2	728.7	727.5	739.2	749.6	753.4
32.5°	783.4	771.7	739.2	700.2	679.5	679.5	691.1	700.2	704.0
35°	720.9	708.0	679.5	646.9	630.1	631.3	643.1	649.5	653.4
37.5°	646.9	643.1	621.0	593.7	582.0	584.6	593.7	598.9	602.8
40°	587.1	576.8	562.5	540.4	532.6	535.2	544.3	549.5	552.1
42.5°	522.2	515.7	504.1	488.4	483.2	487.2	494.9	498.9	497.5
45°	459.9	458.5	446.9	437.8	435.2	440.4	445.6	449.5	450.8
47.5°	414.5	409.2	398.8	392.4	389.8	395.0	400.1	402.7	402.7
50°	370.3	365.1	354.6	348.2	345.6	350.8	354.6	357.2	354.6
52.5°	326.1	320.9	311.8	304.0	302.7	305.2	306.6	307.8	310.4
55°	291.0	285.7	275.4	266.3	263.8	265.0	263.8	263.8	262.4
57.5°	257.2	252.0	241.7	231.2	227.3	226.0	222.2	220.8	219.6
60°	227.3	220.8	210.4	198.7	193.5	188.4	181.8	178.0	178.0
62.5°	198.7	192.3	180.6	170.2	162.4	153.3	142.9	137.7	137.7
65°	171.4	166.3	153.3	141.6	131.2	119.5	107.9	105.3	107.9
67.5°	145.5	140.3	127.3	115.6	102.6	88.4	78.0	78.0	80.6
70°	122.1	116.9	105.3	91.0	76.6	62.3	54.6	54.6	54.6
72.5°	100.0	94.8	81.8	68.9	54.6	40.2	36.4	37.7	36.4
75°	78.0	74.1	62.3	48.0	35.1	24.7	23.3	22.1	23.3
77.5°	58.5	54.6	44.2	31.2	19.5	14.3	13.0	13.0	13.0
80°	40.2	36.4	28.6	18.2	10.4	6.5	6.5	6.5	6.5
82.5°	24.7	20.7	15.6	9.1	3.9	3.9	3.9	3.9	3.9
85°	11.7	9.1	6.5	2.6	1.2	1.2	1.2	1.2	1.2
87.5°	2.6	2.6	1.2	1.2	0.0	1.2	1.2	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)