

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582031

Luminaire Tested: **HCC6S25D010SL-HM60525835-61WDW**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582031  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-9)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S25D010SL-HM60525835-61WDW  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2648.1 lumens  
Efficiency: N/A  
Efficacy: 98.8 lumens/watt  
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.09  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582031  
CATALOG NUMBER: HCC6S25D010SL-HM60525835-61WDW

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P582031

CATALOG NUMBER: HCC6S25D010SL-HM60525835-61WDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89																			
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78																			
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69																			
4	89	80	72	67	87	78	72	66	76	70	66	74	69	65	72	67	64	62																			
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56																			
6	78	67	59	54	76	66	59	54	64	58	53	63	57	53	61	56	52	51																			
7	73	62	54	49	72	61	54	49	60	53	48	58	52	48	57	52	48	46																			
8	69	57	50	45	68	57	50	45	55	49	44	54	48	44	53	48	44	42																			
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39																			
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	47	41	38	36																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	90366
5°	90315
10°	89438
15°	88514
20°	86014
25°	82378
30°	76455
35°	65779
40°	48019
45°	32903
50°	26447
55°	23053
60°	21281
65°	20236
70°	18897
75°	17665
80°	16006
85°	13712



TEST NUMBER: P582031  
 CATALOG NUMBER: HCC6S25D010SL-HM60525835-61WDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	155.6	5.9
10°-20°	438.0	16.5
20°-30°	623.0	23.5
30°-40°	599.8	22.6
40°-50°	345.1	13.0
50°-60°	218.7	8.3
60°-70°	154.8	5.8
70°-80°	88.2	3.3
80°-90°	25.1	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1216.5	45.9
0°-40°	1816.3	68.6
0°-60°	2380.0	89.9
0°-90°	2648.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2648.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1648	
5°	1641	156
15°	1560	438
25°	1362	623
35°	983	600
45°	424	345
55°	241	219
65°	156	155
75°	83	88
85°	22	25
90°	0	



TEST NUMBER: P582031  
CATALOG NUMBER: HCC6S25D010SL-HM60525835-61WDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1648.4
2.5°	1641.2
5°	1641.2
7.5°	1630.3
10°	1606.7
12.5°	1583.2
15°	1559.6
17.5°	1523.3
20°	1474.4
22.5°	1420.0
25°	1361.9
27.5°	1291.2
30°	1207.8
32.5°	1106.3
35°	982.9
37.5°	832.4
40°	671.0
42.5°	529.5
45°	424.4
47.5°	357.2
50°	310.1
52.5°	272.0
55°	241.2
57.5°	214.0
60°	194.1
62.5°	175.9
65°	156.0
67.5°	137.8
70°	117.9
72.5°	99.7
75°	83.4
77.5°	67.2
80°	50.7
82.5°	36.2
85°	21.8
87.5°	9.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)