

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582056

Luminaire Tested: **HCC6W25D010BZ-HM60525927-61MDH**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582056  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-5)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6W25D010BZ-HM60525927-61MDH  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1986.3 lumens  
Efficiency: N/A  
Efficacy: 74.1 lumens/watt  
Spacing Criteria (0/90/45): 1.01 / 1.01 / 0.97  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582056  
CATALOG NUMBER: HCC6W25D010BZ-HM60525927-61MDH

### Luminous Intensity Polar Plot





TEST NUMBER: P582056

CATALOG NUMBER: HCC6W25D010BZ-HM60525927-61MDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	94	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79	79	79	79
4	96	88	82	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72	72	72	72
5	90	81	75	71	89	80	75	70	79	74	70	77	73	69	75	72	68	67	67	67	67
6	85	76	70	65	84	75	69	65	74	68	64	72	67	64	71	67	63	62	62	62	62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57	57	57	57
8	77	67	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53	53	53	53
9	73	62	56	52	72	62	56	52	61	56	52	60	55	52	59	55	51	50	50	50	50
10	69	59	53	49	68	58	52	48	57	52	48	57	52	48	56	51	48	47	47	47	47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	99482
5°	99400
10°	98362
15°	96385
20°	91305
25°	82450
30°	70042
35°	51711
40°	29906
45°	15870
50°	8963
55°	4693
60°	3081
65°	2179
70°	1571
75°	1186
80°	884
85°	881



TEST NUMBER: P582056  
 CATALOG NUMBER: HCC6W25D010BZ-HM60525927-61MDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	171.2	8.6
10°-20°	475.0	23.9
20°-30°	620.0	31.2
30°-40°	473.8	23.9
40°-50°	171.5	8.6
50°-60°	49.8	2.5
60°-70°	17.8	0.9
70°-80°	6.1	0.3
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1266.2	63.7
0°-40°	1739.9	87.6
0°-60°	1961.3	98.7
0°-90°	1986.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1986.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1815	
5°	1806	171
15°	1698	475
25°	1363	620
35°	773	474
45°	205	172
55°	49	50
65°	17	18
75°	6	6
85°	1	1
90°	0	



TEST NUMBER: P582056  
CATALOG NUMBER: HCC6W25D010BZ-HM60525927-61MDH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1814.7
2.5°	1806.3
5°	1806.3
7.5°	1793.7
10°	1767.0
12.5°	1736.2
15°	1698.3
17.5°	1642.2
20°	1565.1
22.5°	1469.8
25°	1363.1
27.5°	1242.5
30°	1106.5
32.5°	953.7
35°	772.7
37.5°	583.4
40°	417.9
42.5°	288.9
45°	204.7
47.5°	147.2
50°	105.1
52.5°	74.3
55°	49.1
57.5°	35.1
60°	28.1
62.5°	22.4
65°	16.8
67.5°	14.0
70°	9.8
72.5°	7.0
75°	5.6
77.5°	4.3
80°	2.8
82.5°	1.4
85°	1.4
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)