

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582011

Luminaire Tested: **HCC6S25D010BZ-HM60525830-61WDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582011
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-7)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S25D010BZ-HM60525830-61WDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2879.5 lumens
Efficiency: N/A
Efficacy: 107.4 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.28 / 1.09
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582011
CATALOG NUMBER: HCC6S25D010BZ-HM60525830-61WDC

Luminous Intensity Polar Plot





TEST NUMBER: P582011

CATALOG NUMBER: HCC6S25D010BZ-HM60525830-61WDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	99	97	97	96	94	94	93	93	85																
	1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93	93	91	89	89	87	87	85	85	85	78																
	2	107	102	97	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	82	81	85	82	80	80	78	78	72																
	3	101	94	89	85	99	93	88	84	90	86	82	88	84	81	85	82	80	78	78	75	74	80	76	74	72	72	72	66																
	4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	74	72	72	69	68	75	71	68	66	66	66	61																
	5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66	66	63	63	70	66	62	61	61	61	56																
	6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61	61	58	58	66	61	58	56	56	56	52																
	7	80	70	63	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56	56	54	54	61	57	53	52	52	52	48																
	8	76	65	59	54	74	65	59	54	64	58	54	62	57	54	61	57	53	52	52	50	50	58	53	50	48	48	48	44																
	9	71	61	55	50	70	60	54	50	60	54	50	59	53	50	58	53	50	48	48	46	46	54	50	46	44	44	44	40																
	10	68	57	51	47	67	57	51	47	56	50	46	55	50	46	54	50	46	44	44	42	42	54	50	46	44	44	44	40																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	102081
5°	103456
10°	107335
15°	116726
20°	130509
25°	137361
30°	120924
35°	83881
40°	50080
45°	23809
50°	8989
55°	3747
60°	1173
65°	921
70°	561
75°	381
80°	568
85°	0



TEST NUMBER: P582011
 CATALOG NUMBER: HCC6S25D010BZ-HM60525830-61WDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.9	6.3
10°-20°	590.6	20.5
20°-30°	1012.0	35.1
30°-40°	785.9	27.3
40°-50°	259.8	9.0
50°-60°	39.9	1.4
60°-70°	7.0	0.2
70°-80°	2.6	0.1
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1783.5	61.9
0°-40°	2569.4	89.2
0°-60°	2869.1	99.6
0°-90°	2879.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2879.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1862	
5°	1880	181
15°	2057	591
25°	2271	1012
35°	1253	786
45°	307	260
55°	39	40
65°	7	7
75°	2	3
85°	0	1
90°	0	



TEST NUMBER: P582011
CATALOG NUMBER: HCC6S25D010BZ-HM60525830-61WDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	1862.1
2.5°	1860.3
5°	1880.0
7.5°	1901.4
10°	1928.2
12.5°	1981.7
15°	2056.7
17.5°	2147.8
20°	2237.1
22.5°	2288.9
25°	2270.9
27.5°	2147.8
30°	1910.3
32.5°	1590.8
35°	1253.4
37.5°	951.7
40°	699.8
42.5°	494.6
45°	307.1
47.5°	171.4
50°	105.4
52.5°	64.3
55°	39.2
57.5°	19.7
60°	10.7
62.5°	8.9
65°	7.1
67.5°	5.4
70°	3.5
72.5°	3.5
75°	1.8
77.5°	1.8
80°	1.8
82.5°	1.8
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)