

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582008

Luminaire Tested: **HCC6S25D010BZ-HM60525830-61RWWC**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582008  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-14)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S25D010BZ-HM60525830-61RWWC  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2659.8 lumens  
Efficiency: N/A  
Efficacy: 99.2 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.15 / 1.2  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582008  
CATALOG NUMBER: HCC6S25D010BZ-HM60525830-61RWWC

### Luminous Intensity Polar Plot





TEST NUMBER: P582008

CATALOG NUMBER: HCC6S25D010BZ-HM60525830-61RWWC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88			
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77			
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	69	68			
4	88	78	70	64	86	76	69	64	74	68	63	72	67	62	70	65	61	60			
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53			
6	76	64	56	50	74	63	56	50	62	55	50	60	54	49	58	53	49	47			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	45	54	48	44	42			
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35			
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	72226	72226	72226
5°	72601	72991	72991
10°	74631	73340	73039
15°	76998	73758	73758
20°	77899	72065	73734
25°	76341	68460	71696
30°	72207	63617	67352
35°	65350	58190	61054
40°	56849	52634	54681
45°	48579	46920	48579
50°	42625	41107	42788
55°	37198	34637	36003
60°	32892	28770	28386
65°	29173	22687	19457
70°	25742	16028	11733
75°	21922	9087	5676
80°	16322	2810	1705
85°	8995	1132	1132



TEST NUMBER: P582008  
 CATALOG NUMBER: HCC6S25D010BZ-HM60525830-61RWWC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	126.4	4.8
10°-20°	369.7	13.9
20°-30°	540.0	20.3
30°-40°	566.4	21.3
40°-50°	477.1	17.9
50°-60°	334.3	12.6
60°-70°	179.2	6.7
70°-80°	60.1	2.3
80°-90°	6.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1036.2	39.0
0°-40°	1602.5	60.2
0°-60°	2414.0	90.8
0°-90°	2659.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2659.8	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1318	1318	1318	1318	1318	
5°	1319	1325	1326	1326	1326	127
15°	1357	1339	1300	1292	1300	383
25°	1262	1209	1132	1152	1185	578
35°	976	927	870	894	912	606
45°	627	616	605	621	627	488
55°	389	377	362	370	377	350
65°	225	205	175	145	150	225
75°	104	80	43	27	27	110
85°	14	7	2	2	2	20
90°	0	0	0	0	0	



TEST NUMBER: P582008

CATALOG NUMBER: HCC6S25D010BZ-HM60525830-61RWWC

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1317.5	1317.5	1317.5	1317.5	1317.5	1317.5	1317.5	1317.5	1317.5
2.5°	1308.6	1308.6	1312.1	1315.6	1319.3	1319.3	1321.0	1322.8	1321.0
5°	1319.3	1319.3	1324.7	1326.4	1326.4	1324.7	1326.4	1326.4	1326.4
7.5°	1335.3	1331.8	1333.6	1329.9	1326.4	1324.7	1322.8	1322.8	1322.8
10°	1340.7	1337.1	1333.6	1326.4	1317.5	1312.1	1310.4	1312.1	1312.1
12.5°	1347.9	1344.2	1335.3	1321.0	1310.4	1301.5	1299.6	1303.2	1303.2
15°	1356.7	1353.2	1339.0	1315.6	1299.6	1290.7	1292.5	1296.1	1299.6
17.5°	1356.7	1349.6	1326.4	1296.1	1276.4	1267.5	1274.7	1283.6	1289.0
20°	1335.3	1328.2	1296.1	1258.6	1235.3	1230.1	1242.5	1258.6	1263.9
22.5°	1306.8	1292.5	1255.0	1210.4	1185.3	1185.3	1203.3	1222.9	1230.1
25°	1262.1	1251.5	1208.6	1156.8	1131.8	1130.1	1151.5	1178.2	1185.3
27.5°	1212.2	1197.9	1151.5	1097.9	1071.2	1072.9	1096.1	1122.9	1130.1
30°	1140.7	1122.9	1081.8	1030.1	1005.0	1012.2	1035.5	1055.0	1064.0
32.5°	1060.4	1044.4	1006.9	958.7	937.2	944.4	964.1	981.9	989.0
35°	976.5	958.7	926.6	883.7	869.5	876.6	894.4	908.7	912.3
37.5°	881.9	869.5	846.2	812.3	801.5	810.4	824.7	833.7	837.3
40°	794.4	783.8	764.1	739.1	735.5	742.7	756.9	762.3	764.1
42.5°	708.7	699.8	687.3	669.5	669.5	676.6	689.2	692.7	694.4
45°	626.6	621.2	615.8	601.6	605.2	614.1	621.2	626.6	626.6
47.5°	555.2	557.0	549.8	539.2	542.7	551.7	557.0	562.3	562.3
50°	499.8	494.6	487.4	476.6	482.0	489.2	496.3	499.8	501.7
52.5°	435.5	433.8	428.4	416.0	419.5	423.1	430.3	435.5	437.4
55°	389.2	383.8	376.7	362.4	362.4	366.0	369.5	373.1	376.7
57.5°	344.6	339.2	328.5	312.4	310.6	310.6	308.9	312.4	317.8
60°	300.0	298.1	282.1	267.8	262.4	257.1	250.0	251.7	258.9
62.5°	260.6	257.1	242.8	224.9	214.3	205.2	196.3	194.6	201.7
65°	224.9	221.4	205.2	187.4	174.9	158.9	144.6	144.6	150.0
67.5°	192.8	185.7	171.4	151.7	135.7	116.0	101.7	105.4	107.1
70°	160.6	155.4	139.2	119.7	100.0	80.3	71.4	73.2	73.2
72.5°	132.1	124.9	108.9	89.2	69.7	51.7	48.2	46.4	46.4
75°	103.5	96.4	80.3	60.6	42.9	30.3	26.8	26.8	26.8
77.5°	74.9	69.7	55.4	37.5	23.2	14.3	12.5	10.7	10.7
80°	51.7	46.4	34.0	19.7	8.9	5.4	5.4	5.4	5.4
82.5°	30.3	24.9	16.0	8.9	3.5	1.8	1.8	1.8	1.8
85°	14.3	10.7	7.1	3.5	1.8	1.8	1.8	1.8	1.8
87.5°	1.8	1.8	1.8	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)