

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582016

Luminaire Tested: **HCC6W25D010BZ-HM60525830-61WWW**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582016  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6W25D010BZ-HM60525830-61WWW  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2470.6 lumens  
Efficiency: N/A  
Efficacy: 92.2 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.06 / 1.14  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582016  
CATALOG NUMBER: HCC6W25D010BZ-HM60525830-61WWW

### Luminous Intensity Polar Plot





TEST NUMBER: P582016

CATALOG NUMBER: HCC6W25D010BZ-HM60525830-61WWW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87		
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76		
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66		
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58		
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51		
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46		
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42		
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38		
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34		
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32		

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	72708	72708	72708
5°	75935	72496	69161
10°	78010	71247	64984
15°	79932	69705	60886
20°	80291	66547	55917
25°	78603	62302	51287
30°	74581	57287	47014
35°	67740	51484	42168
40°	59018	45857	37935
45°	51067	40128	33352
50°	44604	34557	29227
55°	39416	30374	25079
60°	35425	26621	21720
65°	31728	23167	21066
70°	28322	19747	19747
75°	24570	16648	18533
80°	19731	14080	16890
85°	13460	12391	14593



TEST NUMBER: P582016

CATALOG NUMBER: HCC6W25D010BZ-HM60525830-61WWW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	124.7	5.0
10°-20°	346.5	14.0
20°-30°	482.9	19.5
30°-40°	497.6	20.1
40°-50°	412.4	16.7
50°-60°	296.4	12.0
60°-70°	188.7	7.6
70°-80°	96.9	3.9
80°-90°	24.6	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	954.1	38.6
0°-40°	1451.6	58.8
0°-60°	2160.3	87.4
0°-90°	2470.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2470.6	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1326	1326	1326	1326	1326	
5°	1380	1358	1317	1275	1257	132
15°	1408	1355	1228	1116	1073	397
25°	1300	1210	1030	898	848	595
35°	1012	930	769	668	630	629
45°	659	612	518	452	430	510
55°	412	378	318	282	262	371
65°	245	218	179	155	162	245
75°	116	100	79	82	88	124
85°	21	20	20	21	23	27
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P582016

CATALOG NUMBER: HCC6W25D010BZ-HM60525830-61WWW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1326.3	1326.3	1326.3	1326.3	1326.3	1326.3	1326.3	1326.3	1326.3
2.5°	1351.4	1346.0	1338.8	1331.7	1320.9	1308.5	1297.7	1294.2	1288.8
5°	1379.9	1372.8	1358.5	1340.6	1317.4	1294.2	1274.6	1262.0	1256.8
7.5°	1397.7	1388.8	1369.2	1338.8	1304.9	1271.0	1242.5	1224.6	1217.4
10°	1401.4	1392.3	1365.6	1324.5	1279.9	1233.5	1197.7	1176.3	1167.4
12.5°	1406.6	1394.2	1360.3	1312.0	1254.9	1201.4	1156.8	1130.0	1121.1
15°	1408.4	1394.2	1354.9	1296.0	1228.2	1163.9	1115.7	1083.6	1072.8
17.5°	1401.4	1385.2	1338.8	1267.4	1190.6	1122.8	1065.7	1031.7	1017.6
20°	1376.3	1358.5	1304.9	1224.6	1140.7	1069.3	1010.4	974.7	958.5
22.5°	1344.2	1320.9	1260.3	1174.6	1087.1	1012.2	953.3	917.6	901.4
25°	1299.5	1278.1	1210.3	1119.3	1030.0	951.4	897.9	860.4	847.9
27.5°	1247.7	1222.8	1153.1	1062.2	971.1	892.5	840.8	806.8	790.8
30°	1178.2	1154.9	1085.3	994.3	905.0	831.9	778.2	749.8	742.7
32.5°	1096.0	1076.5	1008.5	922.8	837.3	769.3	724.7	694.4	687.3
35°	1012.2	989.0	930.0	849.7	769.3	708.7	667.6	640.8	630.1
37.5°	921.1	899.7	849.7	778.2	706.9	649.8	614.1	590.9	580.1
40°	824.7	808.7	762.2	705.1	640.8	590.9	560.5	540.9	530.1
42.5°	735.5	719.3	687.3	633.8	580.1	535.5	508.7	490.9	482.0
45°	658.7	644.4	612.3	565.9	517.6	480.1	451.6	439.2	430.2
47.5°	581.9	574.8	546.2	503.5	458.7	426.6	407.0	392.7	385.5
50°	523.0	514.1	487.3	442.7	405.2	380.3	362.4	349.8	342.7
52.5°	462.4	453.5	428.4	390.9	360.6	337.4	319.5	308.9	301.7
55°	412.4	405.2	378.4	344.6	317.8	298.1	282.1	269.5	262.4
57.5°	366.0	358.9	333.8	301.7	278.4	260.6	246.3	235.7	226.7
60°	323.1	317.8	292.7	262.4	242.8	224.9	212.4	203.5	198.1
62.5°	285.6	274.9	253.5	226.7	208.9	194.6	182.1	176.7	180.3
65°	244.6	239.2	217.8	194.6	178.6	164.3	155.2	158.9	162.4
67.5°	210.6	203.5	185.7	164.3	150.0	139.2	133.8	141.0	142.8
70°	176.7	169.5	153.5	135.7	123.2	116.0	116.0	121.4	123.2
72.5°	144.6	139.2	124.9	110.6	101.7	96.4	100.0	103.5	105.4
75°	116.0	110.6	100.0	87.5	78.6	78.6	82.1	85.7	87.5
77.5°	89.2	85.7	74.9	66.0	62.5	62.5	66.0	67.8	69.7
80°	62.5	58.9	53.5	48.2	44.6	48.2	51.7	51.7	53.5
82.5°	41.1	39.2	35.7	32.1	32.1	34.0	35.7	37.5	37.5
85°	21.4	21.4	19.7	17.8	19.7	21.4	21.4	23.2	23.2
87.5°	7.1	7.1	7.1	7.1	8.9	8.9	8.9	8.9	8.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)