

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582103

Luminaire Tested: **HCC6S25D010BZ-HM60525935-61WDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582103
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S25D010BZ-HM60525935-61WDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2352.0 lumens
Efficiency: N/A
Efficacy: 87.8 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.09
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582103
CATALOG NUMBER: HCC6S25D010BZ-HM60525935-61WDW

Luminous Intensity Polar Plot





TEST NUMBER: P582103

CATALOG NUMBER: HCC6S25D010BZ-HM60525935-61WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89																			
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78																			
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69																			
4	89	80	72	67	87	78	72	66	76	70	66	74	69	65	72	67	64	62																			
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	61	58	56																			
6	78	67	59	54	76	66	59	54	64	58	53	63	57	53	61	56	52	51																			
7	73	62	54	49	72	61	54	49	60	53	48	58	52	48	57	52	48	46																			
8	69	57	50	45	68	57	50	45	55	49	44	54	48	44	53	48	44	42																			
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39																			
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	47	41	38	36																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	80262
5°	80211
10°	79435
15°	78616
20°	76394
25°	73166
30°	67903
35°	58424
40°	42644
45°	29220
50°	23488
55°	20482
60°	18891
65°	17979
70°	16798
75°	15695
80°	14238
85°	12140



TEST NUMBER: P582103
 CATALOG NUMBER: HCC6S25D010BZ-HM60525935-61WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.2	5.9
10°-20°	389.0	16.5
20°-30°	553.3	23.5
30°-40°	532.7	22.6
40°-50°	306.5	13.0
50°-60°	194.2	8.3
60°-70°	137.5	5.8
70°-80°	78.4	3.3
80°-90°	22.3	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1080.5	45.9
0°-40°	1613.1	68.6
0°-60°	2113.9	89.9
0°-90°	2352.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2352.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1464	
5°	1458	138
15°	1385	389
25°	1210	553
35°	873	533
45°	377	306
55°	214	194
65°	139	137
75°	74	78
85°	19	22
90°	0	



TEST NUMBER: P582103
CATALOG NUMBER: HCC6S25D010BZ-HM60525935-61WDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1464.1
2.5°	1457.6
5°	1457.6
7.5°	1448.0
10°	1427.0
12.5°	1406.1
15°	1385.2
17.5°	1353.0
20°	1309.5
22.5°	1261.1
25°	1209.6
27.5°	1146.9
30°	1072.7
32.5°	982.5
35°	873.0
37.5°	739.3
40°	595.9
42.5°	470.4
45°	376.9
47.5°	317.3
50°	275.4
52.5°	241.6
55°	214.3
57.5°	190.1
60°	172.3
62.5°	156.2
65°	138.6
67.5°	122.4
70°	104.8
72.5°	88.6
75°	74.1
77.5°	59.6
80°	45.1
82.5°	32.2
85°	19.3
87.5°	8.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)