

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582048

Luminaire Tested: **HCC6S25D010MB-HM60525840-61WDH**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582048  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-8)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S25D010MB-HM60525840-61WDH  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2871.3 lumens  
Efficiency: N/A  
Efficacy: 107.1 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.08  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582048  
CATALOG NUMBER: HCC6S25D010MB-HM60525840-61WDH

### Luminous Intensity Polar Plot





TEST NUMBER: P582048  
 CATALOG NUMBER: HCC6S25D010MB-HM60525840-61WDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	113	110	107	105	110	108	105	103	103	101	100	100	98	97	96	95	94	92																											
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84																											
3	100	93	87	83	98	91	86	82	89	84	81	86	83	80	84	81	78	77																											
4	94	86	79	75	92	85	79	74	82	77	73	80	76	72	78	75	72	70																											
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64																											
6	83	73	67	62	82	73	66	62	71	65	61	70	65	61	68	64	60	59																											
7	79	68	62	57	77	68	61	57	66	60	56	65	60	56	64	59	56	54																											
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	51	50																											
9	70	59	53	48	69	59	53	48	58	52	48	57	52	48	56	51	48	46																											
10	66	56	49	45	65	55	49	45	54	49	45	53	48	45	53	48	44	43																											

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	112447
5°	113190
10°	114499
15°	116851
20°	117505
25°	113843
30°	103288
35°	83975
40°	55740
45°	31019
50°	17398
55°	9653
60°	5329
65°	4034
70°	2805
75°	2076
80°	1231
85°	1258



TEST NUMBER: P582048  
 CATALOG NUMBER: HCC6S25D010MB-HM60525840-61WDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	196.3	6.8
10°-20°	580.5	20.2
20°-30°	855.7	29.8
30°-40°	765.3	26.7
40°-50°	332.0	11.6
50°-60°	97.6	3.4
60°-70°	31.1	1.1
70°-80°	11.1	0.4
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1632.5	56.9
0°-40°	2397.8	83.5
0°-60°	2827.4	98.5
0°-90°	2871.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2871.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2051	
5°	2057	196
15°	2059	581
25°	1882	856
35°	1255	765
45°	400	332
55°	101	98
65°	31	31
75°	10	11
85°	2	2
90°	0	



TEST NUMBER: P582048

CATALOG NUMBER: HCC6S25D010MB-HM60525840-61WDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2051.2
2.5°	2045.3
5°	2056.9
7.5°	2060.8
10°	2056.9
12.5°	2056.9
15°	2058.9
17.5°	2047.3
20°	2014.2
22.5°	1957.9
25°	1882.1
27.5°	1775.4
30°	1631.7
32.5°	1460.6
35°	1254.8
37.5°	1019.7
40°	778.9
42.5°	569.1
45°	400.1
47.5°	285.6
50°	204.0
52.5°	145.7
55°	101.0
57.5°	68.0
60°	48.6
62.5°	38.8
65°	31.1
67.5°	23.3
70°	17.5
72.5°	13.7
75°	9.8
77.5°	7.8
80°	3.9
82.5°	2.0
85°	2.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)