

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582134

Luminaire Tested: **HCC6S30D010SL-HM63040827-61RWWC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582134
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S30D010SL-HM63040827-61RWWC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3050.3 lumens
Efficiency: N/A
Efficacy: 108.9 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.15 / 1.2
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582134
CATALOG NUMBER: HCC6S30D010SL-HM63040827-61RWWC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582134

CATALOG NUMBER: HCC6S30D010SL-HM63040827-61RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88								
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77								
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	69	68								
4	88	78	70	64	86	76	69	64	74	68	63	72	67	62	70	65	61	60								
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	50	74	63	56	50	62	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	45	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	82828	82828	82828
5°	83260	83705	83705
10°	85586	84106	83766
15°	88304	84586	84586
20°	89339	82648	84562
25°	87555	78513	82227
30°	82817	72961	77240
35°	74947	66722	70015
40°	65194	60363	62710
45°	55711	53804	55711
50°	48885	47146	49056
55°	42665	39721	41289
60°	37716	32991	32552
65°	33467	26021	22298
70°	29540	18368	13448
75°	25163	10400	6503
80°	18721	3220	1957
85°	10315	1258	1258



TEST NUMBER: P582134
 CATALOG NUMBER: HCC6S30D010SL-HM63040827-61RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.9	4.8
10°-20°	424.0	13.9
20°-30°	619.3	20.3
30°-40°	649.5	21.3
40°-50°	547.2	17.9
50°-60°	383.4	12.6
60°-70°	205.5	6.7
70°-80°	68.9	2.3
80°-90°	7.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1188.3	39.0
0°-40°	1837.8	60.2
0°-60°	2768.3	90.8
0°-90°	3050.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3050.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1511	1511	1511	1511	1511	
5°	1513	1519	1521	1521	1521	145
15°	1556	1536	1490	1482	1490	439
25°	1448	1386	1298	1320	1359	663
35°	1120	1062	997	1026	1046	695
45°	719	706	694	712	719	560
55°	446	432	416	424	432	402
65°	258	235	201	166	172	258
75°	119	92	49	31	31	126
85°	16	8	2	2	2	23
90°	0	0	0	0	0	



TEST NUMBER: P582134

CATALOG NUMBER: HCC6S30D010SL-HM63040827-61RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1510.9	1510.9	1510.9	1510.9	1510.9	1510.9	1510.9	1510.9	1510.9
2.5°	1500.6	1500.6	1504.8	1508.8	1513.0	1513.0	1515.0	1517.0	1515.0
5°	1513.0	1513.0	1519.1	1521.1	1521.1	1519.1	1521.1	1521.1	1521.1
7.5°	1531.4	1527.3	1529.3	1525.2	1521.1	1519.1	1517.0	1517.0	1517.0
10°	1537.5	1533.5	1529.3	1521.1	1510.9	1504.8	1502.7	1504.8	1504.8
12.5°	1545.7	1541.7	1531.4	1515.0	1502.7	1492.4	1490.4	1494.6	1494.6
15°	1555.9	1551.9	1535.5	1508.8	1490.4	1480.2	1482.2	1486.4	1490.4
17.5°	1555.9	1547.7	1521.1	1486.4	1463.8	1453.6	1461.8	1472.0	1478.2
20°	1531.4	1523.2	1486.4	1443.3	1416.7	1410.6	1424.9	1443.3	1449.5
22.5°	1498.6	1482.2	1439.3	1388.0	1359.4	1359.4	1379.8	1402.4	1410.6
25°	1447.5	1435.1	1386.0	1326.7	1298.0	1295.9	1320.5	1351.2	1359.4
27.5°	1390.1	1373.8	1320.5	1259.0	1228.4	1230.4	1257.0	1287.7	1295.9
30°	1308.3	1287.7	1240.6	1181.3	1152.6	1160.8	1187.5	1209.9	1220.2
32.5°	1216.1	1197.7	1154.6	1099.3	1074.9	1083.1	1105.5	1126.0	1134.2
35°	1119.9	1099.3	1062.5	1013.4	997.0	1005.2	1025.8	1042.0	1046.2
37.5°	1011.4	997.0	970.5	931.5	919.2	929.4	945.8	956.1	960.2
40°	911.0	898.8	876.3	847.5	843.5	851.7	868.1	874.2	876.3
42.5°	812.8	802.6	788.2	767.7	767.7	775.9	790.2	794.4	796.4
45°	718.6	712.4	706.3	690.0	694.0	704.2	712.4	718.6	718.6
47.5°	636.7	638.7	630.5	618.3	622.3	632.7	638.7	644.9	644.9
50°	573.2	567.2	558.9	546.6	552.8	561.0	569.2	573.2	575.2
52.5°	499.5	497.5	491.3	477.0	481.1	485.2	493.4	499.5	501.6
55°	446.4	440.2	432.0	415.6	415.6	419.7	423.8	427.9	432.0
57.5°	395.1	389.0	376.7	358.2	356.2	356.2	354.2	358.2	364.4
60°	344.0	342.0	323.5	307.1	300.9	294.8	286.7	288.7	296.9
62.5°	298.9	294.8	278.5	258.0	245.6	235.4	225.2	223.2	231.4
65°	258.0	253.9	235.4	215.0	200.6	182.2	165.9	165.9	171.9
67.5°	221.2	212.9	196.5	174.1	155.6	133.0	116.6	120.8	122.8
70°	184.3	178.1	159.7	137.2	114.6	92.1	81.9	83.9	83.9
72.5°	151.5	143.3	124.8	102.4	79.9	59.3	55.3	53.3	53.3
75°	118.8	110.6	92.1	69.6	49.1	34.8	30.7	30.7	30.7
77.5°	86.0	79.9	63.5	43.0	26.6	16.4	14.4	12.2	12.2
80°	59.3	53.3	38.9	22.5	10.2	6.2	6.2	6.2	6.2
82.5°	34.8	28.7	18.4	10.2	4.0	2.0	2.0	2.0	2.0
85°	16.4	12.2	8.2	4.0	2.0	2.0	2.0	2.0	2.0
87.5°	2.0	2.0	2.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)