

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582140

Luminaire Tested: **HCC6S30D010SL-HM63040827-61WDWB**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582140  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-10)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S30D010SL-HM63040827-61WDWB  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3220.3 lumens  
Efficiency: N/A  
Efficacy: 115.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.05  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582140  
CATALOG NUMBER: HCC6S30D010SL-HM63040827-61WDWB

### Luminous Intensity Polar Plot





TEST NUMBER: P582140

CATALOG NUMBER: HCC6S30D010SL-HM63040827-61WDWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	85	78	73	91	83	78	73	81	76	72	79	75	71	77	73	70	69			
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	65	63			
6	83	73	66	61	81	72	66	61	70	65	60	69	64	60	67	63	60	58			
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54			
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50			
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	48	46			
10	66	56	49	45	65	55	49	45	54	48	45	53	48	44	53	48	44	43			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	120106
5°	121126
10°	125488
15°	136312
20°	141786
25°	135619
30°	117037
35°	84276
40°	47482
45°	24599
50°	14669
55°	10571
60°	8980
65°	10364
70°	13127
75°	13873
80°	13575
85°	12894



TEST NUMBER: P582140  
 CATALOG NUMBER: HCC6S30D010SL-HM63040827-61WDWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	211.8	6.6
10°-20°	677.4	21.0
20°-30°	1012.5	31.4
30°-40°	774.0	24.0
40°-50°	270.3	8.4
50°-60°	103.0	3.2
60°-70°	80.8	2.5
70°-80°	68.3	2.1
80°-90°	22.0	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1901.7	59.1
0°-40°	2675.7	83.1
0°-60°	3049.1	94.7
0°-90°	3220.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3220.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2191	
5°	2201	212
15°	2402	677
25°	2242	1013
35°	1259	774
45°	317	270
55°	111	103
65°	80	81
75°	66	68
85°	20	22
90°	0	



TEST NUMBER: P582140  
CATALOG NUMBER: HCC6S30D010SL-HM63040827-61WDWB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2190.9
2.5°	2184.8
5°	2201.1
7.5°	2223.7
10°	2254.3
12.5°	2324.0
15°	2401.8
17.5°	2448.9
20°	2430.4
22.5°	2356.7
25°	2242.1
27.5°	2078.3
30°	1848.9
32.5°	1574.6
35°	1259.3
37.5°	933.7
40°	663.5
42.5°	464.8
45°	317.3
47.5°	223.2
50°	172.0
52.5°	135.2
55°	110.6
57.5°	90.1
60°	81.9
62.5°	79.9
65°	79.9
67.5°	83.9
70°	81.9
72.5°	75.7
75°	65.5
77.5°	55.3
80°	43.0
82.5°	30.7
85°	20.5
87.5°	8.2
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)