

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582161

Luminaire Tested: **HCC6S30D010SL-HM63040830-61WWWB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582161
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S30D010SL-HM63040830-61WWWB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3147.2 lumens
Efficiency: N/A
Efficacy: 112.4 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.17
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582161
CATALOG NUMBER: HCC6S30D010SL-HM63040830-61WWWB

Luminous Intensity Polar Plot





TEST NUMBER: P582161

CATALOG NUMBER: HCC6S30D010SL-HM63040830-61WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76								
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66								
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58								
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52								
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	38	34	57	45	38	33	44	38	33	43	37	33	43	37	33	31								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	88101	88101	88101
5°	90006	88075	86506
10°	92762	87262	84328
15°	95693	86096	82237
20°	97215	82870	78897
25°	95618	77956	74363
30°	91027	72271	69485
35°	83018	65230	64206
40°	72586	58603	58288
45°	62472	51571	52765
50°	54301	44945	45875
55°	47425	39444	39865
60°	42124	34186	31291
65°	37592	28758	23920
70°	33083	23578	20051
75°	28361	18618	19063
80°	22856	15943	18721
85°	15159	13838	16605



TEST NUMBER: P582161
 CATALOG NUMBER: HCC6S30D010SL-HM63040830-61WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.2	4.8
10°-20°	433.2	13.8
20°-30°	618.4	19.6
30°-40°	647.7	20.6
40°-50°	545.3	17.3
50°-60°	388.1	12.3
60°-70°	227.2	7.2
70°-80°	107.5	3.4
80°-90°	27.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1203.7	38.2
0°-40°	1851.4	58.8
0°-60°	2784.9	88.5
0°-90°	3147.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3147.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1607	1607	1607	1607	1607	
5°	1636	1622	1600	1578	1572	157
15°	1686	1625	1517	1456	1449	476
25°	1581	1469	1289	1227	1229	724
35°	1240	1137	975	942	959	770
45°	806	746	665	667	681	626
55°	496	454	413	413	417	447
65°	290	257	222	187	184	289
75°	134	112	88	86	90	144
85°	24	20	22	26	26	31
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582161

CATALOG NUMBER: HCC6S30D010SL-HM63040830-61WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1607.1	1607.1	1607.1	1607.1	1607.1	1607.1	1607.1	1607.1	1607.1
2.5°	1609.3	1609.3	1607.1	1604.9	1600.5	1593.9	1589.5	1585.1	1585.1
5°	1635.6	1631.2	1622.4	1611.5	1600.5	1587.3	1578.5	1572.0	1572.0
7.5°	1657.6	1648.8	1631.2	1611.5	1591.7	1574.1	1558.8	1550.0	1547.8
10°	1666.4	1655.3	1629.0	1598.3	1567.6	1543.4	1525.8	1514.9	1514.9
12.5°	1675.2	1662.0	1626.8	1582.9	1543.4	1510.5	1492.9	1484.1	1482.0
15°	1686.1	1668.5	1624.6	1569.7	1517.0	1479.7	1455.6	1449.0	1449.0
17.5°	1686.1	1664.1	1609.3	1541.2	1475.3	1433.6	1411.7	1405.0	1407.3
20°	1666.4	1642.2	1576.4	1492.9	1420.5	1376.5	1354.6	1350.2	1352.4
22.5°	1629.0	1600.5	1525.8	1435.8	1356.8	1310.6	1290.9	1290.9	1288.8
25°	1580.8	1550.0	1468.8	1374.4	1288.8	1242.6	1227.3	1229.4	1229.4
27.5°	1517.0	1486.4	1405.0	1304.1	1218.5	1172.4	1161.4	1165.8	1168.0
30°	1438.0	1405.0	1319.4	1220.6	1141.7	1095.5	1088.9	1095.5	1097.7
32.5°	1341.4	1317.3	1233.8	1132.9	1058.2	1018.7	1016.5	1023.1	1031.8
35°	1240.5	1214.1	1137.3	1045.0	974.7	941.8	941.8	952.9	959.4
37.5°	1130.6	1104.3	1034.1	957.3	897.9	867.3	871.5	882.6	884.7
40°	1014.3	994.5	935.3	869.4	818.9	794.7	801.4	812.3	814.5
42.5°	904.5	887.0	838.7	779.4	742.1	724.5	733.3	746.5	750.9
45°	805.8	785.9	746.5	695.9	665.2	656.4	667.4	676.2	680.6
47.5°	715.7	698.2	665.2	619.1	597.1	592.7	603.8	608.2	612.6
50°	636.7	619.1	586.2	544.4	527.0	527.0	535.6	540.0	537.9
52.5°	559.8	544.4	513.8	478.6	467.6	467.6	474.2	476.4	480.8
55°	496.2	480.8	454.4	421.5	412.7	408.3	412.7	412.7	417.1
57.5°	436.8	423.8	399.6	368.8	357.9	353.5	351.2	349.1	353.5
60°	384.2	373.2	346.8	320.6	311.8	300.8	292.0	283.2	285.4
62.5°	335.9	325.0	300.8	274.4	265.6	250.3	239.3	228.3	232.7
65°	289.8	278.8	256.8	234.9	221.7	204.2	186.6	180.0	184.4
67.5°	248.1	239.3	217.3	195.4	184.4	164.7	147.1	147.1	149.3
70°	206.4	197.6	180.0	160.3	147.1	129.5	122.9	125.1	125.1
72.5°	169.1	162.4	144.9	127.3	114.1	103.2	103.2	105.3	107.6
75°	133.9	129.5	112.0	96.5	87.9	81.2	85.6	87.9	90.0
77.5°	103.2	96.5	83.5	72.4	65.9	68.0	72.4	74.7	76.8
80°	72.4	70.3	59.3	52.7	50.5	52.7	57.1	59.3	59.3
82.5°	46.1	43.9	37.3	35.1	35.1	37.3	41.7	41.7	41.7
85°	24.1	22.0	19.7	19.7	22.0	24.1	26.4	26.4	26.4
87.5°	8.8	6.5	8.8	8.8	10.9	10.9	10.9	10.9	10.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)