

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582114

Luminaire Tested: **HCC6S25D010SL-HM60525940-61NDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582114
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S25D010SL-HM60525940-61NDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2219.9 lumens
Efficiency: N/A
Efficacy: 82.8 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.03
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582114
CATALOG NUMBER: HCC6S25D010SL-HM60525940-61NDW

Luminous Intensity Polar Plot





TEST NUMBER: P582114

CATALOG NUMBER: HCC6S25D010SL-HM60525940-61NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89																			
2	104	97	92	87	101	95	90	86	92	88	84	89	85	83	86	83	81	79																			
3	97	88	82	77	94	87	81	76	84	79	75	81	77	73	79	75	72	70																			
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63																			
5	84	74	67	61	83	73	66	61	71	65	60	69	64	60	67	63	59	57																			
6	79	68	61	55	77	67	60	55	66	59	55	64	59	54	63	58	54	52																			
7	74	63	56	50	73	62	55	50	61	55	50	60	54	50	58	53	49	48																			
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44																			
9	66	55	48	43	65	54	47	43	53	47	42	52	46	42	51	46	42	41																			
10	63	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	84083
5°	83689
10°	81834
15°	79921
20°	76913
25°	72742
30°	66105
35°	53505
40°	36082
45°	24793
50°	20315
55°	17787
60°	16819
65°	15877
70°	14906
75°	14170
80°	12880
85°	11259



TEST NUMBER: P582114
 CATALOG NUMBER: HCC6S25D010SL-HM60525940-61NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	143.6	6.5
10°-20°	395.4	17.8
20°-30°	549.4	24.7
30°-40°	489.2	22.0
40°-50°	259.7	11.7
50°-60°	169.8	7.6
60°-70°	121.7	5.5
70°-80°	70.6	3.2
80°-90°	20.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1088.4	49.0
0°-40°	1577.6	71.1
0°-60°	2007.1	90.4
0°-90°	2219.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2219.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1534	
5°	1521	144
15°	1408	395
25°	1203	549
35°	800	489
45°	320	260
55°	186	170
65°	122	122
75°	67	71
85°	18	21
90°	0	



TEST NUMBER: P582114
CATALOG NUMBER: HCC6S25D010SL-HM60525940-61NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1533.8
2.5°	1525.7
5°	1520.8
7.5°	1502.8
10°	1470.1
12.5°	1440.8
15°	1408.2
17.5°	1367.4
20°	1318.4
22.5°	1262.9
25°	1202.6
27.5°	1132.5
30°	1044.3
32.5°	938.2
35°	799.5
37.5°	646.2
40°	504.2
42.5°	391.6
45°	319.8
47.5°	272.5
50°	238.2
52.5°	210.5
55°	186.1
57.5°	168.0
60°	153.4
62.5°	138.7
65°	122.4
67.5°	107.6
70°	93.0
72.5°	79.9
75°	66.9
77.5°	53.9
80°	40.8
82.5°	29.3
85°	17.9
87.5°	8.1
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)