

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582142

Luminaire Tested: **HCC6W30D010MW-HM63040827-61WWW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582142
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W30D010MW-HM63040827-61WWW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2833.3 lumens
Efficiency: N/A
Efficacy: 101.2 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582142
CATALOG NUMBER: HCC6W30D010MW-HM63040827-61WWW

Luminous Intensity Polar Plot





TEST NUMBER: P582142

CATALOG NUMBER: HCC6W30D010MW-HM63040827-61WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	83381	83381	83381
5°	87079	83133	79309
10°	89461	81706	74525
15°	91663	79932	69830
20°	92081	76312	64131
25°	90144	71448	58818
30°	85526	65700	53907
35°	77678	59053	48365
40°	67677	52591	43517
45°	58564	46028	38244
50°	51162	39632	33526
55°	45198	34828	28759
60°	40622	30535	24910
65°	36385	26553	24166
70°	32489	22648	22648
75°	28171	19084	21266
80°	22635	16132	19415
85°	15473	14152	16731



TEST NUMBER: P582142
 CATALOG NUMBER: HCC6W30D010MW-HM63040827-61WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	143.0	5.0
10°-20°	397.4	14.0
20°-30°	553.8	19.5
30°-40°	570.6	20.1
40°-50°	472.9	16.7
50°-60°	339.9	12.0
60°-70°	216.4	7.6
70°-80°	111.1	3.9
80°-90°	28.3	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1094.1	38.6
0°-40°	1664.7	58.8
0°-60°	2477.5	87.4
0°-90°	2833.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2833.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1521	1521	1521	1521	1521	
5°	1582	1558	1511	1462	1441	152
15°	1615	1554	1408	1280	1230	455
25°	1490	1388	1181	1030	972	683
35°	1161	1066	882	766	723	721
45°	755	702	594	518	493	585
55°	473	434	364	323	301	426
65°	280	250	205	178	186	281
75°	133	115	90	94	100	142
85°	25	22	22	25	27	31
90°	0	0	0	0	0	



TEST NUMBER: P582142

CATALOG NUMBER: HCC6W30D010MW-HM63040827-61WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1521.0	1521.0	1521.0	1521.0	1521.0	1521.0	1521.0	1521.0	1521.0
2.5°	1549.6	1543.6	1535.4	1527.2	1514.9	1500.5	1488.3	1484.2	1478.0
5°	1582.4	1574.2	1557.8	1537.4	1510.7	1484.2	1461.6	1447.4	1441.2
7.5°	1602.9	1592.7	1570.2	1535.4	1496.5	1457.6	1424.8	1404.3	1396.1
10°	1607.1	1596.7	1566.0	1518.9	1467.8	1414.6	1373.7	1349.0	1338.8
12.5°	1613.1	1598.8	1560.0	1504.7	1439.2	1377.7	1326.6	1295.9	1285.5
15°	1615.1	1598.8	1553.8	1486.2	1408.4	1334.8	1279.5	1242.6	1230.4
17.5°	1607.1	1588.6	1535.4	1453.4	1365.4	1287.7	1222.2	1183.3	1166.9
20°	1578.4	1557.8	1496.5	1404.3	1308.1	1226.2	1158.7	1117.8	1099.3
22.5°	1541.5	1514.9	1445.2	1347.0	1246.7	1160.7	1093.2	1052.3	1033.8
25°	1490.3	1465.8	1387.9	1283.5	1181.2	1091.1	1029.7	986.8	972.4
27.5°	1431.0	1402.3	1322.4	1218.0	1113.6	1023.6	964.2	925.3	906.9
30°	1351.1	1324.5	1244.6	1140.3	1037.9	953.9	892.6	859.8	851.6
32.5°	1256.9	1234.4	1156.7	1058.3	960.1	882.4	831.1	796.4	788.2
35°	1160.7	1134.1	1066.5	974.4	882.4	812.7	765.6	734.9	722.7
37.5°	1056.3	1031.7	974.4	892.6	810.7	745.1	704.2	677.6	665.4
40°	945.7	927.3	874.2	808.6	734.9	677.6	642.8	620.3	608.1
42.5°	843.5	825.0	788.2	726.7	665.4	614.1	583.4	563.0	552.8
45°	755.4	739.0	702.2	649.0	593.7	550.6	517.9	503.5	493.3
47.5°	667.4	659.2	626.4	577.3	526.1	489.3	466.8	450.4	442.2
50°	599.9	589.6	558.8	507.7	464.7	436.0	415.6	401.3	393.1
52.5°	530.2	519.9	491.3	448.4	413.5	386.9	366.4	354.2	346.0
55°	472.9	464.7	434.0	395.1	364.4	341.8	323.4	309.1	300.9
57.5°	419.7	411.5	382.9	346.0	319.4	298.9	282.5	270.3	260.0
60°	370.5	364.4	335.8	300.9	278.5	257.9	243.6	233.4	227.2
62.5°	327.6	315.2	290.7	260.0	239.5	223.2	208.8	202.7	206.8
65°	280.5	274.3	249.8	223.2	204.7	188.3	178.1	182.2	186.3
67.5°	241.6	233.4	212.9	188.3	171.9	159.7	153.5	161.7	163.7
70°	202.7	194.5	176.1	155.6	141.3	133.0	133.0	139.2	141.3
72.5°	165.9	159.7	143.3	126.9	116.6	110.6	114.6	118.8	120.8
75°	133.0	126.9	114.6	100.4	90.1	90.1	94.2	98.2	100.4
77.5°	102.4	98.2	86.0	75.7	71.7	71.7	75.7	77.8	79.8
80°	71.7	67.5	61.5	55.3	51.1	55.3	59.3	59.3	61.5
82.5°	47.1	45.1	40.9	36.9	36.9	38.9	40.9	43.0	43.0
85°	24.6	24.6	22.5	20.5	22.5	24.6	24.6	26.6	26.6
87.5°	8.2	8.2	8.2	8.2	10.2	10.2	10.2	10.2	10.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)