

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582153

Luminaire Tested: **HCC6W30D010MB-HM63040830-61RWWH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582153
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W30D010MB-HM63040830-61RWWH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3283.3 lumens
Efficiency: N/A
Efficacy: 117.3 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.12 / 1.19
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582153
CATALOG NUMBER: HCC6W30D010MB-HM63040830-61RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582153

CATALOG NUMBER: HCC6W30D010MB-HM63040830-61RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77								
3	95	86	79	74	93	84	78	73	82	76	72	79	74	70	77	73	69	67								
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59								
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	50	74	63	56	50	61	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	91862	91862	91862
5°	92813	91971	91366
10°	94131	91687	90708
15°	96351	91113	90239
20°	97244	88406	88657
25°	95116	83950	85547
30°	90083	77987	80633
35°	81566	71280	73930
40°	71040	64435	66797
45°	60278	57045	59076
50°	53380	49824	51128
55°	47014	42608	42398
60°	42135	35874	32980
65°	37605	28784	23647
70°	33083	20773	14794
75°	27895	12560	8366
80°	21499	5556	3441
85°	12391	1321	1321



TEST NUMBER: P582153
 CATALOG NUMBER: HCC6W30D010MB-HM63040830-61RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.1	4.8
10°-20°	457.1	13.9
20°-30°	660.8	20.1
30°-40°	695.3	21.2
40°-50°	584.5	17.8
50°-60°	410.2	12.5
60°-70°	225.7	6.9
70°-80°	80.1	2.4
80°-90°	10.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1277.0	38.9
0°-40°	1972.3	60.1
0°-60°	2967.1	90.4
0°-90°	3283.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3283.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1676	1676	1676	1676	1676	
5°	1687	1682	1671	1665	1660	161
15°	1698	1669	1605	1586	1590	479
25°	1572	1493	1388	1390	1414	719
35°	1219	1149	1065	1087	1105	755
45°	778	756	736	753	762	610
55°	492	466	446	446	444	443
65°	290	259	222	182	182	289
75°	132	106	59	40	40	141
85°	20	11	2	2	2	27
90°	0	0	0	0	0	



TEST NUMBER: P582153

CATALOG NUMBER: HCC6W30D010MB-HM63040830-61RWWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1675.7	1675.7	1675.7	1675.7	1675.7	1675.7	1675.7	1675.7	1675.7
2.5°	1675.7	1675.7	1673.4	1673.4	1669.0	1669.0	1666.9	1666.9	1666.9
5°	1686.6	1686.6	1682.2	1675.7	1671.3	1664.7	1664.7	1662.5	1660.3
7.5°	1693.3	1691.0	1684.5	1675.7	1664.7	1653.7	1649.3	1651.5	1649.3
10°	1691.0	1686.6	1677.8	1660.3	1647.1	1631.7	1629.5	1627.4	1629.5
12.5°	1695.4	1688.9	1671.3	1649.3	1627.4	1609.8	1607.5	1607.5	1609.8
15°	1697.7	1691.0	1669.0	1636.1	1605.4	1587.8	1585.7	1587.8	1590.0
17.5°	1691.0	1682.2	1649.3	1605.4	1570.2	1552.7	1552.7	1557.0	1561.4
20°	1666.9	1653.7	1607.5	1554.9	1515.4	1502.2	1506.6	1515.4	1519.7
22.5°	1623.0	1607.5	1554.9	1495.5	1453.8	1442.9	1453.8	1464.8	1469.2
25°	1572.5	1554.9	1493.4	1431.9	1387.9	1374.7	1390.2	1407.7	1414.3
27.5°	1504.3	1484.6	1427.5	1357.2	1313.3	1306.7	1324.3	1344.0	1348.4
30°	1423.1	1401.1	1337.4	1271.5	1232.0	1229.8	1249.6	1267.1	1273.8
32.5°	1324.3	1304.5	1249.6	1183.8	1148.6	1148.6	1168.3	1183.8	1190.3
35°	1218.8	1196.8	1148.6	1093.6	1065.1	1067.4	1087.1	1098.0	1104.7
37.5°	1093.6	1087.1	1049.8	1003.6	983.9	988.3	1003.6	1012.4	1019.0
40°	992.7	975.1	951.0	913.6	900.4	904.8	920.2	929.0	933.4
42.5°	882.8	871.9	852.0	825.8	817.0	823.5	836.7	843.4	841.1
45°	777.5	775.2	755.5	740.2	735.8	744.4	753.2	759.9	762.0
47.5°	700.6	691.8	674.2	663.2	658.8	667.6	676.4	680.8	680.8
50°	625.9	617.1	599.5	588.6	584.2	593.0	599.5	603.9	599.5
52.5°	551.2	542.4	527.1	513.9	511.7	516.1	518.3	520.4	524.8
55°	491.9	483.1	465.6	450.2	445.8	448.0	445.8	445.8	443.6
57.5°	434.8	426.0	408.4	390.9	384.3	382.1	375.5	373.3	371.1
60°	384.3	373.3	355.7	336.0	327.2	318.4	307.5	300.8	300.8
62.5°	336.0	325.1	305.2	287.7	274.5	259.2	241.6	232.8	232.8
65°	289.9	281.1	259.2	239.3	221.9	202.0	182.3	177.9	182.3
67.5°	246.0	237.2	215.2	195.5	173.5	149.3	131.7	131.7	136.1
70°	206.4	197.6	177.9	153.7	129.6	105.5	92.3	92.3	92.3
72.5°	169.1	160.3	138.4	116.4	92.3	68.1	61.5	63.7	61.5
75°	131.7	125.2	105.5	81.2	59.3	41.7	39.5	37.3	39.5
77.5°	98.8	92.3	74.7	52.7	32.9	24.1	22.0	22.0	22.0
80°	68.1	61.5	48.3	30.8	17.6	10.9	10.9	10.9	10.9
82.5°	41.7	35.2	26.4	15.3	6.5	6.5	6.5	6.5	6.5
85°	19.7	15.3	10.9	4.4	2.1	2.1	2.1	2.1	2.1
87.5°	4.4	4.4	2.1	2.1	0.0	2.1	2.1	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)