

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582158

Luminaire Tested: **HCC6S30D010MW-HM63040830-61WDWB**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582158  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-10)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S30D010MW-HM63040830-61WDWB  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3454.7 lumens  
Efficiency: N/A  
Efficacy: 123.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.05  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582158  
CATALOG NUMBER: HCC6S30D010MW-HM63040830-61WDWB

### Luminous Intensity Polar Plot





TEST NUMBER: P582158  
 CATALOG NUMBER: HCC6S30D010MW-HM63040830-61WDWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89	86	84	82
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83	80	77	75
4	93	85	78	73	91	83	78	73	81	76	72		79	75	71		77	73	70	69
5	88	78	72	67	86	77	71	66	75	70	66		74	69	65		72	68	65	63
6	83	73	66	61	81	72	66	61	70	65	60		69	64	60		67	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63	59	55	54
8	74	63	57	52	73	63	56	52	61	56	52		60	55	51		59	55	51	50
9	70	59	53	48	69	59	52	48	58	52	48		57	51	48		56	51	48	46
10	66	56	49	45	65	55	49	45	54	48	45		53	48	44		53	48	44	43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	128849
5°	129947
10°	134628
15°	146238
20°	152112
25°	145490
30°	125564
35°	90406
40°	50931
45°	26398
50°	15735
55°	11345
60°	9637
65°	11117
70°	14089
75°	14890
80°	14554
85°	13838



TEST NUMBER: P582158  
 CATALOG NUMBER: HCC6S30D010MW-HM63040830-61WDWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	227.2	6.6
10°-20°	726.7	21.0
20°-30°	1086.2	31.4
30°-40°	830.3	24.0
40°-50°	290.1	8.4
50°-60°	110.5	3.2
60°-70°	86.7	2.5
70°-80°	73.3	2.1
80°-90°	23.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2040.2	59.1
0°-40°	2870.5	83.1
0°-60°	3271.1	94.7
0°-90°	3454.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3454.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2350	
5°	2361	227
15°	2577	727
25°	2405	1086
35°	1351	830
45°	340	290
55°	119	111
65°	86	87
75°	70	73
85°	22	24
90°	0	



TEST NUMBER: P582158  
CATALOG NUMBER: HCC6S30D010MW-HM63040830-61WDWB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2350.4
2.5°	2343.8
5°	2361.4
7.5°	2385.5
10°	2418.5
12.5°	2493.2
15°	2576.7
17.5°	2627.2
20°	2607.4
22.5°	2528.3
25°	2405.3
27.5°	2229.6
30°	1983.6
32.5°	1689.2
35°	1350.9
37.5°	1001.6
40°	711.7
42.5°	498.7
45°	340.5
47.5°	239.5
50°	184.5
52.5°	144.9
55°	118.7
57.5°	96.7
60°	87.9
62.5°	85.7
65°	85.7
67.5°	90.0
70°	87.9
72.5°	81.3
75°	70.3
77.5°	59.3
80°	46.1
82.5°	32.9
85°	22.0
87.5°	8.8
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)