

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582212

Luminaire Tested: **HCC6S30D010MW-HM63040927-61WDWB**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582212  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-10)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S30D010MW-HM63040927-61WDWB  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2719.0 lumens  
Efficiency: N/A  
Efficacy: 97.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.05  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582212  
CATALOG NUMBER: HCC6S30D010MW-HM63040927-61WDWB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P582212

CATALOG NUMBER: HCC6S30D010MW-HM63040927-61WDWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91			91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82			82
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			75
4	93	85	78	73	91	83	78	73	81	76	72	79	75	71	77	73	70	69			69
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	65	63			63
6	83	73	66	61	81	72	66	61	70	65	60	69	64	60	67	63	60	58			58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54			54
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50			50
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	48	46			46
10	66	56	49	45	65	55	49	45	54	48	45	53	48	44	53	48	44	43			43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	101406
5°	102272
10°	105960
15°	115097
20°	119722
25°	114509
30°	98825
35°	71153
40°	40082
45°	20777
50°	12383
55°	8917
60°	7587
65°	8743
70°	11092
75°	11713
80°	11460
85°	10819



TEST NUMBER: P582212  
 CATALOG NUMBER: HCC6S30D010MW-HM63040927-61WDWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	178.8	6.6
10°-20°	572.0	21.0
20°-30°	854.9	31.4
30°-40°	653.5	24.0
40°-50°	228.3	8.4
50°-60°	87.0	3.2
60°-70°	68.2	2.5
70°-80°	57.7	2.1
80°-90°	18.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1605.7	59.1
0°-40°	2259.2	83.1
0°-60°	2574.5	94.7
0°-90°	2719.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2719.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1850	
5°	1858	179
15°	2028	572
25°	1893	855
35°	1063	653
45°	268	228
55°	93	87
65°	67	68
75°	55	58
85°	17	19
90°	0	



TEST NUMBER: P582212

CATALOG NUMBER: HCC6S30D010MW-HM63040927-61WDWB

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1849.8
2.5°	1844.7
5°	1858.5
7.5°	1877.5
10°	1903.5
12.5°	1962.2
15°	2028.0
17.5°	2067.7
20°	2052.2
22.5°	1989.9
25°	1893.1
27.5°	1754.8
30°	1561.2
32.5°	1329.5
35°	1063.2
37.5°	788.3
40°	560.1
42.5°	392.5
45°	268.0
47.5°	188.5
50°	145.2
52.5°	114.1
55°	93.3
57.5°	76.1
60°	69.2
62.5°	67.4
65°	67.4
67.5°	70.9
70°	69.2
72.5°	64.0
75°	55.3
77.5°	46.7
80°	36.3
82.5°	25.9
85°	17.2
87.5°	6.9
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)