

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582227

Luminaire Tested: **HCC6S30D010MB-HM63040930-61WDC**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582227  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-7)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S30D010MB-HM63040930-61WDC  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3330.3 lumens  
Efficiency: N/A  
Efficacy: 118.9 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.28 / 1.09  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582227  
CATALOG NUMBER: HCC6S30D010MB-HM63040930-61WDC

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P582227

CATALOG NUMBER: HCC6S30D010MB-HM63040930-61WDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	99	97	97	96	94	94	93	93	85																
	1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93	93	91	89	89	87	87	85	85	85	78																
	2	107	102	97	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	82	81	85	82	80	80	78	78	72																
	3	101	94	89	85	99	93	88	84	90	86	82	88	84	81	85	82	80	78	78	75	74	80	76	74	72	72	72	66																
	4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	74	72	72	69	68	75	71	68	66	66	66	61																
	5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66	66	63	63	70	66	62	61	61	61	56																
	6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61	61	58	58	66	61	58	56	56	56	52																
	7	80	70	63	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56	56	54	54	61	57	53	52	52	52	48																
	8	76	65	59	54	74	65	59	54	64	58	54	62	57	54	61	57	53	52	52	50	50	58	53	50	48	48	48	44																
	9	71	61	55	50	70	60	54	50	60	54	50	59	53	50	58	53	50	48	48	46	46	54	50	46	44	44	44	40																
	10	68	57	51	47	67	57	51	47	56	50	46	55	50	46	54	50	46	44	44	44	54	50	46	44	44	44	44	40																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	118072
5°	119651
10°	124140
15°	135006
20°	150945
25°	158876
30°	139863
35°	97012
40°	57930
45°	27538
50°	10396
55°	4339
60°	1360
65°	1064
70°	673
75°	424
80°	631
85°	0



TEST NUMBER: P582227  
 CATALOG NUMBER: HCC6S30D010MB-HM63040930-61WDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	209.3	6.3
10°-20°	683.1	20.5
20°-30°	1170.4	35.1
30°-40°	909.0	27.3
40°-50°	300.5	9.0
50°-60°	46.1	1.4
60°-70°	8.1	0.2
70°-80°	3.0	0.1
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2062.8	61.9
0°-40°	2971.8	89.2
0°-60°	3318.4	99.6
0°-90°	3330.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3330.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2154	
5°	2174	209
15°	2379	683
25°	2627	1170
35°	1450	909
45°	355	301
55°	45	46
65°	8	8
75°	2	3
85°	0	1
90°	0	



TEST NUMBER: P582227  
CATALOG NUMBER: HCC6S30D010MB-HM63040930-61WDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2153.8
2.5°	2151.6
5°	2174.3
7.5°	2199.2
10°	2230.1
12.5°	2292.0
15°	2378.8
17.5°	2484.1
20°	2587.4
22.5°	2647.2
25°	2626.6
27.5°	2484.1
30°	2209.5
32.5°	1839.9
35°	1449.6
37.5°	1100.7
40°	809.5
42.5°	572.0
45°	355.2
47.5°	198.2
50°	121.9
52.5°	74.3
55°	45.4
57.5°	22.7
60°	12.4
62.5°	10.3
65°	8.2
67.5°	6.2
70°	4.2
72.5°	4.2
75°	2.0
77.5°	2.0
80°	2.0
82.5°	2.0
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)