

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582170

Luminaire Tested: **HCC6W30D010MB-HM63040835-61RWWC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582170
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W30D010MB-HM63040835-61RWWC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3395.9 lumens
Efficiency: N/A
Efficacy: 121.3 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.15 / 1.2
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582170
CATALOG NUMBER: HCC6W30D010MB-HM63040835-61RWWC

Luminous Intensity Polar Plot





TEST NUMBER: P582170

CATALOG NUMBER: HCC6W30D010MB-HM63040835-61RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88								
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77								
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	69	68								
4	88	78	70	64	86	76	69	64	74	68	63	72	67	62	70	65	61	60								
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	50	74	63	56	50	62	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	45	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	92213	92213	92213
5°	92686	93193	93193
10°	95283	93636	93257
15°	98315	94166	94166
20°	99461	92011	94141
25°	97475	87404	91548
30°	92191	81228	85988
35°	83440	74291	77945
40°	72579	67204	69817
45°	62022	59898	62022
50°	54420	52484	54625
55°	47492	44213	45972
60°	41981	36740	36236
65°	37241	28978	24828
70°	32874	20452	14987
75°	28001	11586	7244
80°	20868	3599	2178
85°	11448	1447	1447



TEST NUMBER: P582170
 CATALOG NUMBER: HCC6W30D010MB-HM63040835-61RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.4	4.8
10°-20°	472.1	13.9
20°-30°	689.5	20.3
30°-40°	723.1	21.3
40°-50°	609.2	17.9
50°-60°	426.8	12.6
60°-70°	228.8	6.7
70°-80°	76.7	2.3
80°-90°	8.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1322.9	39.0
0°-40°	2046.0	60.2
0°-60°	3082.0	90.8
0°-90°	3395.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3395.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1682	1682	1682	1682	1682	
5°	1684	1691	1694	1694	1694	162
15°	1732	1709	1659	1650	1659	489
25°	1612	1543	1445	1470	1514	738
35°	1247	1183	1110	1142	1165	774
45°	800	786	773	793	800	623
55°	497	481	463	472	481	447
65°	287	262	223	185	191	287
75°	132	103	55	34	34	140
85°	18	9	2	2	2	25
90°	0	0	0	0	0	



TEST NUMBER: P582170

CATALOG NUMBER: HCC6W30D010MB-HM63040835-61RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1682.1	1682.1	1682.1	1682.1	1682.1	1682.1	1682.1	1682.1	1682.1
2.5°	1670.7	1670.7	1675.3	1679.8	1684.3	1684.3	1686.6	1689.0	1686.6
5°	1684.3	1684.3	1691.2	1693.5	1693.5	1691.2	1693.5	1693.5	1693.5
7.5°	1704.9	1700.3	1702.6	1698.0	1693.5	1691.2	1689.0	1689.0	1689.0
10°	1711.7	1707.2	1702.6	1693.5	1682.1	1675.3	1672.9	1675.3	1675.3
12.5°	1720.8	1716.3	1704.9	1686.6	1672.9	1661.6	1659.2	1663.9	1663.9
15°	1732.3	1727.6	1709.4	1679.8	1659.2	1648.0	1650.2	1654.7	1659.2
17.5°	1732.3	1723.1	1693.5	1654.7	1629.6	1618.2	1627.4	1638.8	1645.6
20°	1704.9	1695.8	1654.7	1606.8	1577.2	1570.4	1586.4	1606.8	1613.7
22.5°	1668.4	1650.2	1602.3	1545.3	1513.5	1513.5	1536.2	1561.3	1570.4
25°	1611.5	1597.8	1543.1	1477.0	1445.0	1442.7	1470.1	1504.3	1513.5
27.5°	1547.6	1529.4	1470.1	1401.7	1367.6	1369.8	1399.5	1433.7	1442.7
30°	1456.4	1433.7	1381.3	1315.2	1283.2	1292.3	1321.9	1347.0	1358.4
32.5°	1353.9	1333.3	1285.5	1224.0	1196.6	1205.8	1230.7	1253.6	1262.7
35°	1246.8	1224.0	1182.9	1128.2	1110.1	1119.1	1141.9	1160.1	1164.7
37.5°	1126.0	1110.1	1080.3	1037.0	1023.4	1034.8	1053.0	1064.4	1068.9
40°	1014.2	1000.5	975.6	943.6	939.1	948.1	966.4	973.2	975.6
42.5°	904.8	893.4	877.5	854.8	854.8	863.8	879.7	884.4	886.6
45°	800.0	793.2	786.3	768.1	772.6	784.0	793.2	800.0	800.0
47.5°	708.9	711.1	702.0	688.3	692.9	704.2	711.1	717.9	717.9
50°	638.1	631.4	622.2	608.5	615.4	624.5	633.6	638.1	640.5
52.5°	556.1	553.8	547.1	531.0	535.6	540.2	549.3	556.1	558.5
55°	496.9	490.0	481.0	462.6	462.6	467.3	471.8	476.3	481.0
57.5°	439.9	433.0	419.4	398.9	396.5	396.5	394.3	398.9	405.7
60°	382.9	380.6	360.1	341.8	335.1	328.2	319.1	321.4	330.5
62.5°	332.8	328.2	310.0	287.1	273.5	262.1	250.8	248.4	257.5
65°	287.1	282.6	262.1	239.3	223.4	202.8	184.7	184.7	191.4
67.5°	246.1	237.1	218.8	193.7	173.2	148.1	130.0	134.5	136.7
70°	205.1	198.3	177.8	152.7	127.6	102.6	91.2	93.5	93.5
72.5°	168.7	159.6	139.0	113.9	88.9	66.1	61.6	59.2	59.2
75°	132.2	123.1	102.6	77.5	54.7	38.8	34.2	34.2	34.2
77.5°	95.7	88.9	70.6	47.9	29.6	18.2	15.9	13.7	13.7
80°	66.1	59.2	43.3	25.1	11.4	6.9	6.9	6.9	6.9
82.5°	38.8	31.9	20.6	11.4	4.5	2.3	2.3	2.3	2.3
85°	18.2	13.7	9.2	4.5	2.3	2.3	2.3	2.3	2.3
87.5°	2.3	2.3	2.3	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)