

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582231

Luminaire Tested: **HCC6S30D010MB-HM63040930-61WWBB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582231
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S30D010MB-HM63040930-61WWBB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2616.0 lumens
Efficiency: N/A
Efficacy: 93.4 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582231
CATALOG NUMBER: HCC6S30D010MB-HM63040930-61WWBB

Luminous Intensity Polar Plot





TEST NUMBER: P582231

CATALOG NUMBER: HCC6S30D010MB-HM63040930-61WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89								
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78								
3	96	87	80	75	93	86	79	74	83	77	73	80	76	72	78	74	71	69								
4	89	79	71	66	87	78	71	65	75	69	64	73	68	64	71	66	63	61								
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54								
6	77	65	58	52	75	65	57	52	63	56	51	61	55	51	60	55	51	49								
7	72	60	52	47	70	59	52	47	58	51	46	56	51	46	55	50	46	44								
8	67	55	48	43	66	55	47	42	53	47	42	52	46	42	51	46	42	40								
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37								
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	80471	80471	80471
5°	82027	80327	78511
10°	84818	79307	75967
15°	87413	77918	73587
20°	88774	74679	69738
25°	87168	69560	64945
30°	82861	63390	59598
35°	74472	56644	53753
40°	64278	49643	48019
45°	54424	42733	41617
50°	46668	36101	35743
55°	40457	30384	29208
60°	35315	24680	20832
65°	31067	19016	11519
70°	26815	12582	5626
75°	22748	6121	2182
80°	17616	2589	1326
85°	10378	1258	1258



TEST NUMBER: P582231
 CATALOG NUMBER: HCC6S30D010MB-HM63040930-61WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.5	5.3
10°-20°	391.7	15.0
20°-30°	551.7	21.1
30°-40°	563.6	21.5
40°-50°	454.4	17.4
50°-60°	304.8	11.7
60°-70°	154.3	5.9
70°-80°	49.3	1.9
80°-90°	7.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1081.9	41.4
0°-40°	1645.6	62.9
0°-60°	2404.8	91.9
0°-90°	2616.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2616.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1468	1468	1468	1468	1468	
5°	1491	1480	1460	1437	1427	144
15°	1540	1478	1373	1311	1297	435
25°	1441	1328	1150	1080	1074	660
35°	1113	1012	846	799	803	693
45°	702	646	551	533	537	546
55°	423	376	318	304	306	381
65°	240	198	147	97	89	239
75°	107	76	29	10	10	115
85°	16	8	2	2	2	22
90°	0	0	0	0	0	



TEST NUMBER: P582231

CATALOG NUMBER: HCC6S30D010MB-HM63040930-61WWBB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1467.9	1467.9	1467.9	1467.9	1467.9	1467.9	1467.9	1467.9	1467.9
2.5°	1474.1	1472.1	1470.1	1465.9	1459.7	1453.6	1449.4	1445.2	1443.2
5°	1490.6	1486.5	1480.3	1472.1	1459.7	1445.2	1437.0	1428.7	1426.7
7.5°	1513.4	1505.2	1488.6	1470.1	1449.4	1428.7	1414.3	1406.0	1399.8
10°	1523.7	1509.2	1486.5	1455.6	1424.7	1399.8	1381.3	1368.9	1364.7
12.5°	1531.9	1515.5	1482.4	1441.1	1399.8	1366.8	1346.2	1335.8	1331.7
15°	1540.2	1523.7	1478.3	1424.7	1372.9	1333.7	1311.0	1300.8	1296.6
17.5°	1540.2	1517.5	1463.8	1395.6	1333.7	1286.3	1263.6	1253.2	1251.2
20°	1521.7	1496.8	1430.8	1350.2	1280.1	1226.5	1205.8	1199.6	1195.4
22.5°	1486.5	1457.6	1383.3	1292.4	1216.1	1164.5	1141.8	1137.6	1133.5
25°	1441.1	1412.2	1327.5	1230.5	1150.0	1098.4	1079.8	1075.7	1073.7
27.5°	1383.3	1352.4	1263.6	1164.5	1077.7	1028.2	1011.7	1011.7	1009.6
30°	1309.0	1273.9	1187.2	1088.1	1001.4	956.0	943.6	943.6	941.5
32.5°	1218.1	1183.1	1104.6	1009.6	927.1	879.5	869.2	873.3	871.3
35°	1112.8	1083.9	1011.7	918.7	846.4	803.2	799.0	803.2	803.2
37.5°	1007.6	980.7	918.7	838.2	770.1	730.9	730.9	737.1	735.0
40°	898.2	877.5	819.7	749.4	693.7	666.9	662.7	668.9	671.0
42.5°	794.8	778.3	728.9	671.0	621.5	594.6	600.8	605.0	607.0
45°	702.0	685.5	646.2	586.4	551.2	532.7	532.7	538.9	536.8
47.5°	619.4	607.0	567.7	510.0	479.0	470.7	474.9	479.0	479.0
50°	547.2	528.5	491.4	446.0	423.3	412.9	417.1	419.1	419.1
52.5°	479.0	466.6	429.5	388.2	367.5	361.3	361.3	363.4	363.4
55°	423.3	408.8	375.7	334.5	317.9	309.7	303.6	301.4	305.6
57.5°	369.5	357.2	326.3	287.0	268.4	260.2	247.8	243.6	247.8
60°	322.1	311.8	280.8	243.6	225.1	208.6	194.0	185.8	190.0
62.5°	280.8	268.4	237.4	206.4	185.8	167.3	144.6	132.1	138.3
65°	239.5	229.1	198.2	167.3	146.6	123.9	97.0	88.8	88.8
67.5°	202.4	192.0	163.1	136.3	111.5	84.7	59.9	57.8	59.9
70°	167.3	156.9	132.1	105.3	78.5	51.6	35.1	35.1	35.1
72.5°	138.3	125.9	103.2	76.3	49.6	26.9	18.5	20.7	20.7
75°	107.4	97.0	76.3	51.6	28.9	12.4	10.3	10.3	10.3
77.5°	80.5	72.3	53.6	33.1	14.5	4.2	4.2	4.2	4.2
80°	55.8	47.4	35.1	20.7	8.2	4.2	4.2	4.2	4.2
82.5°	33.1	28.9	20.7	10.3	4.2	2.0	2.0	2.0	2.0
85°	16.5	14.5	8.2	4.2	2.0	2.0	2.0	2.0	2.0
87.5°	4.2	4.2	2.0	2.0	0.0	2.0	2.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)