

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582186

Luminaire Tested: **HCC6W30D010SL-HM63040840-61NDW**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582186  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-3)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6W30D010SL-HM63040840-61NDW  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3259.3 lumens  
Efficiency: N/A  
Efficacy: 116.4 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.03  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582186  
CATALOG NUMBER: HCC6W30D010SL-HM63040840-61NDW

### Luminous Intensity Polar Plot





TEST NUMBER: P582186  
 CATALOG NUMBER: HCC6W30D010SL-HM63040840-61NDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89																											
2	104	97	92	87	101	95	90	86	92	88	84	89	85	83	86	83	81	79																											
3	97	88	82	77	94	87	81	76	84	79	75	81	77	73	79	75	72	70																											
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63																											
5	84	74	67	61	83	73	66	61	71	65	60	69	64	60	67	63	59	57																											
6	79	68	61	55	77	67	60	55	66	59	55	64	59	54	63	58	54	52																											
7	74	63	56	50	73	62	55	50	61	55	50	60	54	50	58	53	49	48																											
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44																											
9	66	55	48	43	65	54	47	43	53	47	42	52	46	42	51	46	42	41																											
10	62	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38																											

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	123444
5°	122865
10°	120149
15°	117333
20°	112920
25°	106790
30°	97053
35°	78554
40°	52978
45°	36399
50°	29833
55°	26102
60°	24691
65°	23310
70°	21879
75°	20800
80°	18910
85°	16605



TEST NUMBER: P582186  
 CATALOG NUMBER: HCC6W30D010SL-HM63040840-61NDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	210.8	6.5
10°-20°	580.6	17.8
20°-30°	806.6	24.7
30°-40°	718.2	22.0
40°-50°	381.2	11.7
50°-60°	249.3	7.6
60°-70°	178.7	5.5
70°-80°	103.6	3.2
80°-90°	30.3	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1597.9	49.0
0°-40°	2316.1	71.1
0°-60°	2946.7	90.4
0°-90°	3259.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3259.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2252	
5°	2233	211
15°	2067	581
25°	1766	807
35°	1174	718
45°	470	381
55°	273	249
65°	180	179
75°	98	104
85°	26	30
90°	0	



TEST NUMBER: P582186

CATALOG NUMBER: HCC6W30D010SL-HM63040840-61NDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2251.8
2.5°	2239.8
5°	2232.7
7.5°	2206.3
10°	2158.4
12.5°	2115.3
15°	2067.4
17.5°	2007.5
20°	1935.6
22.5°	1854.1
25°	1765.5
27.5°	1662.6
30°	1533.2
32.5°	1377.5
35°	1173.8
37.5°	948.7
40°	740.3
42.5°	574.9
45°	469.5
47.5°	400.1
50°	349.8
52.5°	309.0
55°	273.1
57.5°	246.7
60°	225.2
62.5°	203.7
65°	179.7
67.5°	158.1
70°	136.5
72.5°	117.4
75°	98.2
77.5°	79.1
80°	59.9
82.5°	43.2
85°	26.4
87.5°	12.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)