

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582236

Luminaire Tested: **HCC6S30D010MW-HM63040935-61MDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582236
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S30D010MW-HM63040935-61MDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2884.8 lumens
Efficiency: N/A
Efficacy: 103.0 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 0.97
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582236
CATALOG NUMBER: HCC6S30D010MW-HM63040935-61MDH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582236

CATALOG NUMBER: HCC6S30D010MW-HM63040935-61MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100							100																					
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	94	93							93																					
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85							85																					
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79							79																					
4	96	88	82	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72							72																					
5	90	81	75	71	89	80	75	70	79	74	70	77	73	69	75	72	68	67							67																					
6	85	76	70	65	84	75	69	65	74	68	64	72	67	64	71	67	63	62							62																					
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57							57																					
8	77	67	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53							53																					
9	73	62	56	52	72	62	56	52	61	56	52	60	55	52	59	55	51	50							50																					
10	69	59	53	49	68	58	52	48	57	52	48	57	52	48	56	51	48	47							47																					

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	144473
5°	144359
10°	142850
15°	139984
20°	132597
25°	119747
30°	101718
35°	75101
40°	43439
45°	23057
50°	13032
55°	6815
60°	4473
65°	3178
70°	2292
75°	1737
80°	1263
85°	1258



TEST NUMBER: P582236
 CATALOG NUMBER: HCC6S30D010MW-HM63040935-61MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	248.6	8.6
10°-20°	689.8	23.9
20°-30°	900.4	31.2
30°-40°	688.0	23.9
40°-50°	249.2	8.6
50°-60°	72.4	2.5
60°-70°	25.9	0.9
70°-80°	8.9	0.3
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1838.8	63.7
0°-40°	2526.9	87.6
0°-60°	2848.4	98.7
0°-90°	2884.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2884.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2635	
5°	2623	249
15°	2466	690
25°	1980	900
35°	1122	688
45°	297	249
55°	71	72
65°	24	26
75°	8	9
85°	2	2
90°	0	



TEST NUMBER: P582236
CATALOG NUMBER: HCC6S30D010MW-HM63040935-61MDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2635.4
2.5°	2623.3
5°	2623.3
7.5°	2605.0
10°	2566.2
12.5°	2521.4
15°	2466.5
17.5°	2385.0
20°	2272.9
22.5°	2134.5
25°	1979.7
27.5°	1804.5
30°	1606.9
32.5°	1384.9
35°	1122.2
37.5°	847.3
40°	607.0
42.5°	419.6
45°	297.4
47.5°	213.9
50°	152.8
52.5°	108.0
55°	71.3
57.5°	50.9
60°	40.8
62.5°	32.6
65°	24.5
67.5°	20.3
70°	14.3
72.5°	10.2
75°	8.2
77.5°	6.1
80°	4.0
82.5°	2.0
85°	2.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)