

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582249

Luminaire Tested: **HCC6S30D010MB-HM63040935-61WWBB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582249
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S30D010MB-HM63040935-61WWBB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2579.3 lumens
Efficiency: N/A
Efficacy: 92.1 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582249
CATALOG NUMBER: HCC6S30D010MB-HM63040935-61WWBB

Luminous Intensity Polar Plot





TEST NUMBER: P582249

CATALOG NUMBER: HCC6S30D010MB-HM63040935-61WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89								
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78								
3	96	87	80	75	93	86	79	74	83	77	73	80	76	72	78	74	71	69								
4	89	79	71	66	87	78	71	65	75	69	64	73	68	64	71	67	63	61								
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54								
6	77	65	58	52	75	65	57	52	63	56	51	61	55	51	60	55	51	49								
7	72	60	52	47	70	59	52	47	58	51	46	56	51	46	55	50	46	44								
8	67	55	48	43	66	55	47	42	53	47	42	52	46	42	51	46	42	40								
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37								
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	79347	79347	79347
5°	80882	79204	77410
10°	83632	78194	74904
15°	86192	76834	72554
20°	87531	73629	68763
25°	85953	68587	64032
30°	81702	62497	58762
35°	73428	55861	52996
40°	63376	48949	47346
45°	53657	42136	41035
50°	46003	35589	35248
55°	39884	29963	28797
60°	34822	24329	20536
65°	30626	18757	11350
70°	26431	12406	5546
75°	22409	6037	2160
80°	17332	2557	1263
85°	10253	1258	1258



TEST NUMBER: P582249

CATALOG NUMBER: HCC6S30D010MB-HM63040935-61WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.6	5.3
10°-20°	386.3	15.0
20°-30°	543.9	21.1
30°-40°	555.7	21.5
40°-50°	448.1	17.4
50°-60°	300.5	11.7
60°-70°	152.1	5.9
70°-80°	48.6	1.9
80°-90°	7.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1066.8	41.4
0°-40°	1622.5	62.9
0°-60°	2371.1	91.9
0°-90°	2579.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2579.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1447	1447	1447	1447	1447	
5°	1470	1460	1439	1417	1407	142
15°	1519	1458	1354	1293	1278	429
25°	1421	1309	1134	1065	1059	651
35°	1097	998	835	788	792	683
45°	692	637	544	525	529	538
55°	417	370	314	299	301	375
65°	236	196	145	96	88	236
75°	106	75	28	10	10	114
85°	16	8	2	2	2	22
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582249

CATALOG NUMBER: HCC6S30D010MB-HM63040935-61WWBB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1447.4	1447.4	1447.4	1447.4	1447.4	1447.4	1447.4	1447.4	1447.4
2.5°	1453.6	1451.5	1449.5	1445.3	1439.3	1433.2	1429.1	1425.0	1423.0
5°	1469.8	1465.7	1459.6	1451.5	1439.3	1425.0	1416.9	1408.7	1406.7
7.5°	1492.2	1484.1	1467.8	1449.5	1429.1	1408.7	1394.5	1386.4	1380.2
10°	1502.4	1488.2	1465.7	1435.2	1404.7	1380.2	1361.9	1349.8	1345.6
12.5°	1510.5	1494.2	1461.6	1421.0	1380.2	1347.6	1327.3	1317.2	1313.0
15°	1518.7	1502.4	1457.6	1404.7	1353.8	1315.0	1292.7	1282.6	1278.4
17.5°	1518.7	1496.2	1443.3	1376.1	1315.0	1268.3	1245.8	1235.7	1233.7
20°	1500.4	1475.9	1410.7	1331.3	1262.1	1209.2	1188.9	1182.8	1178.7
22.5°	1465.7	1437.3	1363.9	1274.4	1199.1	1148.2	1125.7	1121.7	1117.7
25°	1421.0	1392.4	1309.0	1213.3	1133.9	1083.1	1064.7	1060.6	1058.6
27.5°	1363.9	1333.5	1245.8	1148.2	1062.6	1013.9	997.6	997.6	995.4
30°	1290.7	1256.1	1170.6	1072.8	987.3	942.5	930.4	930.4	928.3
32.5°	1201.1	1166.5	1089.1	995.4	914.1	867.3	857.0	861.1	859.1
35°	1097.2	1068.8	997.6	905.9	834.7	791.9	787.8	791.9	791.9
37.5°	993.4	967.0	905.9	826.5	759.3	720.7	720.7	726.7	724.7
40°	885.6	865.2	808.2	739.0	684.0	657.5	653.5	659.5	661.6
42.5°	783.8	767.5	718.6	661.6	612.8	586.3	592.4	596.5	598.5
45°	692.1	675.8	637.2	578.2	543.5	525.2	525.2	531.4	529.3
47.5°	610.7	598.5	559.8	502.8	472.3	464.2	468.2	472.3	472.3
50°	539.4	521.1	484.5	439.7	417.3	407.1	411.3	413.3	413.3
52.5°	472.3	460.0	423.4	382.7	362.4	356.2	356.2	358.2	358.2
55°	417.3	403.1	370.5	329.8	313.5	305.3	299.3	297.2	301.3
57.5°	364.4	352.2	321.6	283.0	264.7	256.5	244.3	240.2	244.3
60°	317.6	307.4	276.9	240.2	221.9	205.6	191.3	183.2	187.3
62.5°	276.9	264.7	234.1	203.6	183.2	164.9	142.6	130.3	136.4
65°	236.1	225.9	195.5	164.9	144.6	122.1	95.7	87.5	87.5
67.5°	199.5	189.3	160.9	134.4	110.0	83.5	59.1	57.0	59.1
70°	164.9	154.7	130.3	103.8	77.4	50.9	34.6	34.6	34.6
72.5°	136.4	124.1	101.8	75.3	48.9	26.5	18.3	20.3	20.3
75°	105.8	95.7	75.3	50.9	28.5	12.2	10.2	10.2	10.2
77.5°	79.4	71.2	52.9	32.6	14.3	4.0	4.0	4.0	4.0
80°	54.9	46.8	34.6	20.3	8.1	4.0	4.0	4.0	4.0
82.5°	32.6	28.5	20.3	10.2	4.0	2.0	2.0	2.0	2.0
85°	16.3	14.3	8.1	4.0	2.0	2.0	2.0	2.0	2.0
87.5°	4.0	4.0	2.0	2.0	0.0	2.0	2.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)