

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582248

Luminaire Tested: **HCC6S30D010MB-HM63040935-61WDWB**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582248  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-10)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S30D010MB-HM63040935-61WDWB  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3202.3 lumens  
Efficiency: N/A  
Efficacy: 114.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.05  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582248  
CATALOG NUMBER: HCC6S30D010MB-HM63040935-61WDWB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P582248

CATALOG NUMBER: HCC6S30D010MB-HM63040935-61WDWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91																																				
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82																																				
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75																																				
4	93	85	78	73	91	83	78	73	81	76	72	79	75	71	77	73	70	69																																				
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	65	63																																				
6	83	73	66	61	81	72	66	61	70	65	60	69	64	60	67	63	60	58																																				
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54																																				
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50																																				
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	48	46																																				
10	66	56	49	45	65	55	49	45	54	48	45	53	48	44	53	48	44	43																																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	119437
5°	120449
10°	124786
15°	135546
20°	140998
25°	134863
30°	116391
35°	83808
40°	47210
45°	24468
50°	14584
55°	10513
60°	8925
65°	10299
70°	13047
75°	13810
80°	13512
85°	12769



TEST NUMBER: P582248  
 CATALOG NUMBER: HCC6S30D010MB-HM63040935-61WDWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	210.6	6.6
10°-20°	673.6	21.0
20°-30°	1006.9	31.4
30°-40°	769.7	24.0
40°-50°	268.8	8.4
50°-60°	102.4	3.2
60°-70°	80.3	2.5
70°-80°	68.0	2.1
80°-90°	21.9	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1891.1	59.1
0°-40°	2660.8	83.1
0°-60°	3032.1	94.7
0°-90°	3202.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3202.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2179	
5°	2189	211
15°	2388	674
25°	2230	1007
35°	1252	770
45°	316	269
55°	110	102
65°	79	80
75°	65	68
85°	20	22
90°	0	



TEST NUMBER: P582248  
CATALOG NUMBER: HCC6S30D010MB-HM63040935-61WDWB

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2178.7
2.5°	2172.5
5°	2188.8
7.5°	2211.3
10°	2241.7
12.5°	2311.1
15°	2388.3
17.5°	2435.2
20°	2416.9
22.5°	2343.6
25°	2229.6
27.5°	2066.7
30°	1838.7
32.5°	1565.8
35°	1252.3
37.5°	928.5
40°	659.7
42.5°	462.2
45°	315.6
47.5°	222.0
50°	171.0
52.5°	134.4
55°	110.0
57.5°	89.5
60°	81.4
62.5°	79.4
65°	79.4
67.5°	83.5
70°	81.4
72.5°	75.4
75°	65.2
77.5°	54.9
80°	42.8
82.5°	30.6
85°	20.3
87.5°	8.1
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)