

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582206

Luminaire Tested: **HCC6W30D010BZ-HM63040927-61RWWC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582206
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W30D010BZ-HM63040927-61RWWC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2575.6 lumens
Efficiency: N/A
Efficacy: 92.0 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.15 / 1.2
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582206
CATALOG NUMBER: HCC6W30D010BZ-HM63040927-61RWWC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582206

CATALOG NUMBER: HCC6W30D010BZ-HM63040927-61RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88								
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77								
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	69	68								
4	88	78	70	64	86	76	69	64	74	68	63	72	67	62	70	65	61	59								
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	50	74	63	56	50	62	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	45	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	69934	69934	69934
5°	70300	70680	70680
10°	72265	71013	70729
15°	74558	71419	71419
20°	75432	69790	71395
25°	73928	66288	69433
30°	69922	61604	65219
35°	63282	56336	59113
40°	55053	50967	52949
45°	47036	45439	47036
50°	41278	39803	41423
55°	36013	33538	34866
60°	31840	27860	27476
65°	28252	21974	18835
70°	24924	15515	11364
75°	21223	8790	5486
80°	15848	2747	1642
85°	8680	1132	1132



TEST NUMBER: P582206

CATALOG NUMBER: HCC6W30D010BZ-HM63040927-61RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.4	4.8
10°-20°	358.0	13.9
20°-30°	522.9	20.3
30°-40°	548.4	21.3
40°-50°	462.0	17.9
50°-60°	323.7	12.6
60°-70°	173.6	6.7
70°-80°	58.2	2.3
80°-90°	6.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1003.3	39.0
0°-40°	1551.7	60.2
0°-60°	2337.5	90.8
0°-90°	2575.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2575.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1276	1276	1276	1276	1276	
5°	1278	1283	1284	1284	1284	123
15°	1314	1296	1258	1252	1258	371
25°	1222	1170	1096	1115	1148	560
35°	946	897	842	866	883	587
45°	607	596	586	602	607	473
55°	377	365	351	358	365	339
65°	218	199	169	140	145	217
75°	100	78	42	26	26	106
85°	14	7	2	2	2	19
90°	0	0	0	0	0	



TEST NUMBER: P582206

CATALOG NUMBER: HCC6W30D010BZ-HM63040927-61RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1275.7	1275.7	1275.7	1275.7	1275.7	1275.7	1275.7	1275.7	1275.7
2.5°	1267.1	1267.1	1270.6	1274.0	1277.5	1277.5	1279.2	1280.9	1279.2
5°	1277.5	1277.5	1282.7	1284.4	1284.4	1282.7	1284.4	1284.4	1284.4
7.5°	1293.0	1289.6	1291.3	1287.8	1284.4	1282.7	1280.9	1280.9	1280.9
10°	1298.2	1294.7	1291.3	1284.4	1275.7	1270.6	1268.8	1270.6	1270.6
12.5°	1305.2	1301.7	1293.0	1279.2	1268.8	1260.2	1258.4	1261.9	1261.9
15°	1313.7	1310.3	1296.5	1274.0	1258.4	1249.8	1251.5	1255.0	1258.4
17.5°	1313.7	1306.8	1284.4	1255.0	1236.0	1227.3	1234.3	1242.9	1248.1
20°	1293.0	1286.1	1255.0	1218.7	1196.3	1191.0	1203.1	1218.7	1223.8
22.5°	1265.3	1251.5	1215.3	1172.0	1147.9	1147.9	1165.1	1184.1	1191.0
25°	1222.2	1211.8	1170.3	1120.2	1095.9	1094.2	1114.9	1140.8	1147.9
27.5°	1173.8	1159.9	1114.9	1063.1	1037.2	1038.9	1061.4	1087.3	1094.2
30°	1104.6	1087.3	1047.5	997.5	973.2	980.1	1002.6	1021.6	1030.3
32.5°	1026.8	1011.2	975.0	928.3	907.6	914.5	933.5	950.7	957.6
35°	945.6	928.3	897.2	855.7	841.8	848.7	866.1	879.9	883.3
37.5°	853.9	841.8	819.3	786.5	776.2	784.9	798.7	807.3	810.8
40°	769.3	758.8	739.9	715.7	712.2	719.1	732.9	738.1	739.9
42.5°	686.3	677.6	665.5	648.2	648.2	655.1	667.3	670.7	672.5
45°	606.7	601.5	596.4	582.6	586.1	594.6	601.5	606.7	606.7
47.5°	537.5	539.3	532.4	522.1	525.5	534.1	539.3	544.6	544.6
50°	484.0	478.8	471.9	461.6	466.7	473.7	480.6	484.0	485.7
52.5°	421.7	420.1	414.8	402.7	406.3	409.7	416.6	421.7	423.5
55°	376.8	371.7	364.8	350.9	350.9	354.3	357.8	361.3	364.8
57.5°	333.6	328.4	318.1	302.5	300.8	300.8	299.0	302.5	307.7
60°	290.4	288.7	273.1	259.3	254.1	249.0	242.0	243.7	250.6
62.5°	252.4	249.0	235.1	217.8	207.5	198.8	190.1	188.5	195.4
65°	217.8	214.4	198.8	181.6	169.4	153.9	140.1	140.1	145.2
67.5°	186.7	179.8	166.0	147.0	131.4	112.4	98.6	102.0	103.7
70°	155.5	150.4	134.8	115.8	96.8	77.8	69.2	70.9	70.9
72.5°	127.9	121.0	105.5	86.4	67.4	50.2	46.7	44.9	44.9
75°	100.2	93.3	77.8	58.7	41.5	29.4	25.9	25.9	25.9
77.5°	72.6	67.4	53.6	36.3	22.5	13.8	12.1	10.3	10.3
80°	50.2	44.9	32.8	19.0	8.7	5.2	5.2	5.2	5.2
82.5°	29.4	24.3	15.6	8.7	3.4	1.8	1.8	1.8	1.8
85°	13.8	10.3	6.9	3.4	1.8	1.8	1.8	1.8	1.8
87.5°	1.8	1.8	1.8	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)