

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593230

Luminaire Tested: **HCC6S30D010MB-HM63040950-61WWW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593230
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S30D010MB-HM63040950-61WWW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2890.2 lumens
Efficiency: N/A
Efficacy: 103.2 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593230
CATALOG NUMBER: HCC6S30D010MB-HM63040950-61WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P593230

CATALOG NUMBER: HCC6S30D010MB-HM63040950-61WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	85053	85053	85053
5°	88829	84806	80899
10°	91253	83343	76023
15°	93508	81538	71226
20°	93925	77847	65415
25°	91959	72881	59997
30°	87241	67017	54989
35°	79237	60231	49336
40°	69044	53651	44383
45°	59743	46951	39020
50°	52186	40434	34191
55°	46106	35526	29342
60°	41444	31149	25404
65°	37112	27085	24646
70°	33147	23097	23097
75°	28764	19465	21689
80°	23077	16479	19794
85°	15788	14404	17046



TEST NUMBER: P593230
 CATALOG NUMBER: HCC6S30D010MB-HM63040950-61WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.8	5.0
10°-20°	405.3	14.0
20°-30°	564.9	19.5
30°-40°	582.0	20.1
40°-50°	482.4	16.7
50°-60°	346.7	12.0
60°-70°	220.8	7.6
70°-80°	113.4	3.9
80°-90°	28.8	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1116.1	38.6
0°-40°	1698.1	58.8
0°-60°	2527.2	87.4
0°-90°	2890.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2890.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1552	1552	1552	1552	1552	
5°	1614	1589	1541	1491	1470	155
15°	1648	1585	1437	1305	1255	464
25°	1520	1416	1205	1050	992	697
35°	1184	1088	900	781	737	735
45°	771	716	606	528	503	596
55°	482	443	372	330	307	435
65°	286	255	209	182	190	287
75°	136	117	92	96	102	145
85°	25	23	23	25	27	32
90°	0	0	0	0	0	



TEST NUMBER: P593230

CATALOG NUMBER: HCC6S30D010MB-HM63040950-61WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1551.5	1551.5	1551.5	1551.5	1551.5	1551.5	1551.5	1551.5	1551.5
2.5°	1580.8	1574.5	1566.2	1557.8	1545.2	1530.6	1518.1	1514.0	1507.7
5°	1614.2	1605.9	1589.1	1568.3	1541.1	1514.0	1491.0	1476.4	1470.1
7.5°	1635.1	1624.6	1601.7	1566.2	1526.4	1486.8	1453.4	1432.5	1424.2
10°	1639.3	1628.8	1597.4	1549.4	1497.2	1443.0	1401.2	1376.1	1365.7
12.5°	1645.5	1630.8	1591.2	1534.9	1468.1	1405.4	1353.2	1321.8	1311.3
15°	1647.6	1630.8	1584.9	1516.0	1436.7	1361.5	1305.2	1267.6	1255.0
17.5°	1639.3	1620.5	1566.2	1482.6	1392.8	1313.5	1246.7	1207.0	1190.3
20°	1610.0	1589.1	1526.4	1432.5	1334.4	1250.8	1181.9	1140.1	1121.3
22.5°	1572.5	1545.2	1474.2	1374.0	1271.8	1184.0	1115.0	1073.3	1054.5
25°	1520.3	1495.2	1415.7	1309.3	1204.9	1113.0	1050.4	1006.5	991.9
27.5°	1459.6	1430.4	1348.9	1242.5	1136.0	1044.1	983.5	943.8	925.0
30°	1378.2	1351.1	1269.6	1163.1	1058.7	973.1	910.4	877.0	868.7
32.5°	1282.1	1259.2	1179.8	1079.6	979.4	900.0	847.8	812.3	804.0
35°	1184.0	1156.9	1087.9	994.0	900.0	829.0	780.9	749.7	737.2
37.5°	1077.5	1052.5	994.0	910.4	826.9	760.1	718.4	691.2	678.7
40°	964.8	946.0	891.6	824.8	749.7	691.2	655.7	632.7	620.2
42.5°	860.4	841.6	804.0	741.3	678.7	626.5	595.1	574.3	563.8
45°	770.6	753.8	716.3	661.9	605.6	561.7	528.3	513.6	503.3
47.5°	680.7	672.4	639.0	588.9	536.7	499.0	476.1	459.4	451.1
50°	611.9	601.4	570.1	517.9	474.1	444.8	423.9	409.3	400.9
52.5°	540.9	530.4	501.2	457.3	421.9	394.6	373.8	361.2	352.9
55°	482.4	474.1	442.7	403.1	371.7	348.7	329.9	315.3	307.0
57.5°	428.0	419.7	390.5	352.9	325.8	304.9	288.2	275.6	265.1
60°	378.0	371.7	342.4	307.0	284.1	263.1	248.5	238.0	231.7
62.5°	334.1	321.6	296.5	265.1	244.3	227.6	212.9	206.8	210.9
65°	286.1	279.8	254.8	227.6	208.8	192.1	181.7	185.8	190.0
67.5°	246.4	238.0	217.2	192.1	175.4	162.9	156.6	164.9	167.1
70°	206.8	198.3	179.5	158.7	144.1	135.8	135.8	142.0	144.1
72.5°	169.2	162.9	146.1	129.5	119.0	112.7	117.0	121.2	123.2
75°	135.8	129.5	117.0	102.4	91.9	91.9	96.1	100.2	102.4
77.5°	104.4	100.2	87.7	77.3	73.1	73.1	77.3	79.3	81.4
80°	73.1	69.0	62.7	56.4	52.2	56.4	60.5	60.5	62.7
82.5°	48.0	45.9	41.7	37.6	37.6	39.7	41.7	43.9	43.9
85°	25.1	25.1	22.9	20.9	22.9	25.1	25.1	27.1	27.1
87.5°	8.3	8.3	8.3	8.3	10.5	10.5	10.5	10.5	10.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)