

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582229

Luminaire Tested: **HCC6S30D010MB-HM63040930-61WDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582229
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S30D010MB-HM63040930-61WDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3014.3 lumens
Efficiency: N/A
Efficacy: 107.7 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.09
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582229
CATALOG NUMBER: HCC6S30D010MB-HM63040930-61WDW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582229

CATALOG NUMBER: HCC6S30D010MB-HM63040930-61WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89	89	89	89
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78	78	78	78
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69	69	69	69
4	89	80	72	67	87	78	72	66	76	70	66	74	69	65	72	67	64	62	62	62	62
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56	56	56	56
6	78	67	59	54	76	66	59	54	64	58	53	63	57	53	61	56	52	51	51	51	51
7	73	62	54	49	72	61	54	49	60	53	48	58	52	48	57	52	48	46	46	46	46
8	69	57	50	45	68	57	50	45	55	49	44	54	48	44	53	48	44	42	42	42	42
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39	39	39	39
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	47	41	38	36	36	36	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	102870
5°	102806
10°	101813
15°	100755
20°	97909
25°	93774
30°	87026
35°	74874
40°	54660
45°	37453
50°	30106
55°	26236
60°	24220
65°	23025
70°	21510
75°	20122
80°	18247
85°	15536



TEST NUMBER: P582229
 CATALOG NUMBER: HCC6S30D010MB-HM63040930-61WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	177.1	5.9
10°-20°	498.6	16.5
20°-30°	709.1	23.5
30°-40°	682.7	22.6
40°-50°	392.8	13.0
50°-60°	248.9	8.3
60°-70°	176.2	5.8
70°-80°	100.4	3.3
80°-90°	28.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1384.8	45.9
0°-40°	2067.5	68.6
0°-60°	2709.1	89.9
0°-90°	3014.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3014.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1876	
5°	1868	177
15°	1775	499
25°	1550	709
35°	1119	683
45°	483	393
55°	274	249
65°	178	176
75°	95	100
85°	25	29
90°	0	



TEST NUMBER: P582229
CATALOG NUMBER: HCC6S30D010MB-HM63040930-61WDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1876.5
2.5°	1868.2
5°	1868.2
7.5°	1855.8
10°	1829.0
12.5°	1802.2
15°	1775.3
17.5°	1734.0
20°	1678.3
22.5°	1616.3
25°	1550.3
27.5°	1469.8
30°	1374.8
32.5°	1259.3
35°	1118.8
37.5°	947.5
40°	763.8
42.5°	602.8
45°	483.1
47.5°	406.6
50°	353.0
52.5°	309.6
55°	274.5
57.5°	243.6
60°	220.9
62.5°	200.2
65°	177.5
67.5°	156.8
70°	134.2
72.5°	113.5
75°	95.0
77.5°	76.3
80°	57.8
82.5°	41.3
85°	24.7
87.5°	10.3
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)