

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582278

Luminaire Tested: **HCC6W35D010SL-HM63040827-61RWWC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582278
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W35D010SL-HM63040827-61RWWC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3624.2 lumens
Efficiency: N/A
Efficacy: 107.5 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.15 / 1.2
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582278
CATALOG NUMBER: HCC6W35D010SL-HM63040827-61RWWC

Luminous Intensity Polar Plot





TEST NUMBER: P582278

CATALOG NUMBER: HCC6W35D010SL-HM63040827-61RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88		
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77		
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	69	68		
4	88	78	70	64	86	76	69	64	74	68	63	72	67	62	70	65	61	59		
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53		
6	76	64	56	50	74	63	56	50	62	55	50	60	54	49	58	53	49	47		
7	71	59	51	45	69	58	50	45	56	50	45	55	49	45	54	48	44	42		
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38		
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35		
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	98413	98413	98413
5°	98916	99455	99455
10°	101690	99931	99519
15°	104915	100500	100500
20°	106147	98201	100465
25°	104020	93284	97693
30°	98389	86691	91774
35°	89041	79277	83185
40°	77459	71720	74504
45°	66193	63929	66193
50°	58088	56015	58292
55°	50684	47195	49050
60°	44810	39207	38670
65°	39758	30924	26501
70°	35086	21831	15996
75°	29886	12370	7731
80°	22257	3820	2336
85°	12265	1572	1572



TEST NUMBER: P582278

CATALOG NUMBER: HCC6W35D010SL-HM63040827-61RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.2	4.8
10°-20°	503.8	13.9
20°-30°	735.8	20.3
30°-40°	771.7	21.3
40°-50°	650.1	17.9
50°-60°	455.5	12.6
60°-70°	244.2	6.7
70°-80°	81.9	2.3
80°-90°	9.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1411.8	39.0
0°-40°	2183.5	60.2
0°-60°	3289.1	90.8
0°-90°	3624.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3624.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1795	1795	1795	1795	1795	
5°	1798	1805	1807	1807	1807	173
15°	1849	1824	1771	1761	1771	521
25°	1720	1647	1542	1569	1615	788
35°	1330	1262	1185	1219	1243	826
45°	854	839	825	846	854	665
55°	530	513	494	504	513	477
65°	306	280	238	197	204	306
75°	141	110	58	36	36	150
85°	20	10	2	2	2	27
90°	0	0	0	0	0	



TEST NUMBER: P582278

CATALOG NUMBER: HCC6W35D010SL-HM63040827-61RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1795.2	1795.2	1795.2	1795.2	1795.2	1795.2	1795.2	1795.2	1795.2
2.5°	1782.9	1782.9	1787.8	1792.7	1797.5	1797.5	1800.0	1802.4	1800.0
5°	1797.5	1797.5	1804.9	1807.3	1807.3	1804.9	1807.3	1807.3	1807.3
7.5°	1819.5	1814.6	1817.0	1812.1	1807.3	1804.9	1802.4	1802.4	1802.4
10°	1826.8	1821.9	1817.0	1807.3	1795.2	1787.8	1785.4	1787.8	1787.8
12.5°	1836.5	1831.6	1819.5	1800.0	1785.4	1773.3	1770.8	1775.7	1775.7
15°	1848.6	1843.7	1824.4	1792.7	1770.8	1758.7	1761.1	1765.9	1770.8
17.5°	1848.6	1839.0	1807.3	1765.9	1739.2	1727.0	1736.7	1749.0	1756.2
20°	1819.5	1809.8	1765.9	1714.9	1683.3	1675.9	1693.0	1714.9	1722.1
22.5°	1780.5	1761.1	1710.0	1649.2	1615.1	1615.1	1639.5	1666.2	1675.9
25°	1719.7	1705.1	1646.8	1576.3	1542.2	1539.7	1568.9	1605.4	1615.1
27.5°	1651.7	1632.2	1568.9	1496.0	1459.5	1461.9	1493.5	1530.1	1539.7
30°	1554.3	1530.1	1474.0	1403.6	1369.5	1379.2	1410.8	1437.6	1449.8
32.5°	1444.9	1422.9	1371.9	1306.2	1277.0	1286.7	1313.6	1337.8	1347.5
35°	1330.5	1306.2	1262.5	1204.1	1184.6	1194.3	1218.7	1238.1	1243.0
37.5°	1201.7	1184.6	1153.0	1106.8	1092.2	1104.3	1123.8	1136.0	1140.9
40°	1082.4	1067.8	1041.1	1007.0	1002.2	1011.9	1031.4	1038.6	1041.1
42.5°	965.7	953.6	936.5	912.1	912.1	921.9	939.0	943.8	946.2
45°	853.8	846.5	839.2	819.7	824.6	836.7	846.5	853.8	853.8
47.5°	756.4	758.9	749.2	734.6	739.4	751.7	758.9	766.3	766.3
50°	681.1	673.8	664.0	649.4	656.8	666.5	676.3	681.1	683.5
52.5°	593.5	591.1	583.7	566.8	571.6	576.5	586.2	593.5	596.0
55°	530.3	522.9	513.2	493.8	493.8	498.7	503.6	508.3	513.2
57.5°	469.5	462.1	447.5	425.7	423.3	423.3	420.8	425.7	433.0
60°	408.7	406.2	384.3	364.9	357.6	350.2	340.5	343.0	352.7
62.5°	355.1	350.2	330.8	306.5	291.9	279.7	267.6	265.1	274.8
65°	306.5	301.7	279.7	255.5	238.4	216.5	197.0	197.0	204.3
67.5°	262.7	253.0	233.5	206.8	184.9	158.1	138.6	143.5	146.0
70°	218.9	211.6	189.8	163.0	136.2	109.5	97.3	99.8	99.8
72.5°	180.0	170.3	148.3	121.6	94.9	70.5	65.7	63.3	63.3
75°	141.1	131.4	109.5	82.7	58.4	41.3	36.5	36.5	36.5
77.5°	102.1	94.9	75.4	51.1	31.6	19.5	17.0	14.6	14.6
80°	70.5	63.3	46.2	26.7	12.1	7.4	7.4	7.4	7.4
82.5°	41.3	34.1	21.9	12.1	4.9	2.5	2.5	2.5	2.5
85°	19.5	14.6	9.7	4.9	2.5	2.5	2.5	2.5	2.5
87.5°	2.5	2.5	2.5	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)