

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582297

Luminaire Tested: **HCC6S35D010SL-HM63040830-61RWWH**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582297  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-15)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S35D010SL-HM63040830-61RWWH  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3901.1 lumens  
Efficiency: N/A  
Efficacy: 115.8 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.12 / 1.19  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 33.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582297  
CATALOG NUMBER: HCC6S35D010SL-HM63040830-61RWWH

### Luminous Intensity Polar Plot





TEST NUMBER: P582297

CATALOG NUMBER: HCC6S35D010SL-HM63040830-61RWWH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77								
3	95	86	79	74	93	84	78	73	82	76	72	79	74	70	77	73	69	67								
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59								
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	50	74	63	56	50	61	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	109141	109141	109141
5°	110279	109272	108551
10°	111838	108933	107775
15°	114467	108247	107214
20°	115533	105032	105336
25°	113009	99750	101643
30°	107035	92660	95800
35°	96911	84691	87830
40°	84401	76558	79363
45°	71612	67767	70201
50°	63418	59188	60749
55°	55855	50627	50369
60°	50062	42617	39196
65°	44674	34180	28096
70°	39318	24668	17567
75°	33169	14933	9934
80°	25540	6598	4136
85°	14781	1635	1635



TEST NUMBER: P582297  
 CATALOG NUMBER: HCC6S35D010SL-HM63040830-61RWWH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	189.0	4.8
10°-20°	543.1	13.9
20°-30°	785.1	20.1
30°-40°	826.1	21.2
40°-50°	694.5	17.8
50°-60°	487.4	12.5
60°-70°	268.1	6.9
70°-80°	95.2	2.4
80°-90°	12.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1517.2	38.9
0°-40°	2343.4	60.1
0°-60°	3525.3	90.4
0°-90°	3901.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3901.1	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1991	1991	1991	1991	1991	
5°	2004	1999	1986	1978	1973	191
15°	2017	1983	1907	1884	1889	569
25°	1868	1774	1649	1652	1680	855
35°	1448	1365	1266	1292	1312	898
45°	924	898	874	895	906	725
55°	584	553	530	530	527	526
65°	344	308	264	217	217	343
75°	157	125	70	47	47	168
85°	24	13	3	3	3	32
90°	0	0	0	0	0	



TEST NUMBER: P582297

CATALOG NUMBER: HCC6S35D010SL-HM63040830-61RWWH

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1990.9	1990.9	1990.9	1990.9	1990.9	1990.9	1990.9	1990.9	1990.9
2.5°	1990.9	1990.9	1988.2	1988.2	1983.1	1983.1	1980.4	1980.4	1980.4
5°	2004.0	2004.0	1998.7	1990.9	1985.7	1977.8	1977.8	1975.3	1972.6
7.5°	2011.8	2009.1	2001.3	1990.9	1977.8	1964.8	1959.5	1962.2	1959.5
10°	2009.1	2004.0	1993.5	1972.6	1956.9	1938.7	1936.1	1933.5	1936.1
12.5°	2014.4	2006.5	1985.7	1959.5	1933.5	1912.6	1910.0	1910.0	1912.6
15°	2016.9	2009.1	1983.1	1943.9	1907.3	1886.5	1883.9	1886.5	1889.1
17.5°	2009.1	1998.7	1959.5	1907.3	1865.7	1844.8	1844.8	1849.9	1855.2
20°	1980.4	1964.8	1910.0	1847.4	1800.4	1784.7	1789.9	1800.4	1805.6
22.5°	1928.2	1910.0	1847.4	1776.9	1727.4	1714.3	1727.4	1740.3	1745.6
25°	1868.3	1847.4	1774.3	1701.3	1649.1	1633.4	1651.7	1672.5	1680.4
27.5°	1787.4	1763.9	1696.0	1612.6	1560.4	1552.6	1573.3	1596.9	1602.1
30°	1690.9	1664.7	1589.1	1510.8	1463.8	1461.2	1484.7	1505.5	1513.4
32.5°	1573.3	1549.9	1484.7	1406.4	1364.7	1364.7	1388.1	1406.4	1414.2
35°	1448.1	1422.1	1364.7	1299.5	1265.5	1268.1	1291.6	1304.6	1312.4
37.5°	1299.5	1291.6	1247.3	1192.4	1169.0	1174.1	1192.4	1202.8	1210.8
40°	1179.4	1158.5	1129.8	1085.4	1069.8	1075.0	1093.2	1103.7	1109.0
42.5°	1048.9	1035.8	1012.4	981.1	970.6	978.5	994.2	1002.0	999.3
45°	923.7	921.1	897.5	879.3	874.1	884.6	895.0	902.8	905.5
47.5°	832.3	821.9	801.0	788.0	782.8	793.2	803.7	808.8	808.8
50°	743.6	733.2	712.3	699.3	694.0	704.5	712.3	717.6	712.3
52.5°	654.9	644.5	626.2	610.6	608.0	613.1	615.8	618.4	623.6
55°	584.4	574.0	553.2	535.0	529.7	532.3	529.7	529.7	527.0
57.5°	516.6	506.2	485.4	464.5	456.6	454.0	446.1	443.6	441.0
60°	456.6	443.6	422.7	399.2	388.7	378.3	365.3	357.5	357.5
62.5°	399.2	386.2	362.7	341.8	326.2	307.9	287.0	276.6	276.6
65°	344.4	334.0	307.9	284.4	263.5	240.1	216.6	211.3	216.6
67.5°	292.2	281.8	255.7	232.2	206.1	177.4	156.6	156.6	161.7
70°	245.3	234.8	211.3	182.6	153.9	125.2	109.6	109.6	109.6
72.5°	201.0	190.5	164.4	138.3	109.6	80.9	73.1	75.6	73.1
75°	156.6	148.7	125.2	96.5	70.5	49.6	46.9	44.3	46.9
77.5°	117.4	109.6	88.7	62.7	39.1	28.7	26.1	26.1	26.1
80°	80.9	73.1	57.4	36.5	20.9	13.1	13.1	13.1	13.1
82.5°	49.6	41.8	31.3	18.3	7.8	7.8	7.8	7.8	7.8
85°	23.5	18.3	13.1	5.3	2.6	2.6	2.6	2.6	2.6
87.5°	5.3	5.3	2.6	2.6	0.0	2.6	2.6	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)