

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582287

Luminaire Tested: **HCC6S35D010MW-HM63040827-61WWWB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582287
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S35D010MW-HM63040827-61WWWB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3485.5 lumens
Efficiency: N/A
Efficacy: 103.4 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.09 / 1.17
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582287
CATALOG NUMBER: HCC6S35D010MW-HM63040827-61WWWB

Luminous Intensity Polar Plot





TEST NUMBER: P582287

CATALOG NUMBER: HCC6S35D010MW-HM63040827-61WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100				
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87				87				
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76				76				
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66				66				
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58				58				
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52				52				
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46				46				
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42				42				
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38				38				
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34				34				
10	58	46	38	34	57	45	38	33	44	38	33	43	37	33	43	37	33	31				31				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	97569	97569	97569
5°	99681	97545	95801
10°	102731	96636	93391
15°	105977	95352	91073
20°	107664	91772	87373
25°	105889	86328	82366
30°	100813	80031	76961
35°	91939	72250	71112
40°	80393	64900	64557
45°	69178	57114	58440
50°	60134	49764	50813
55°	52519	43688	44156
60°	46652	37859	34657
65°	41626	31845	26488
70°	36625	26110	22215
75°	31411	20588	21117
80°	25350	17647	20741
85°	16794	15284	18367



TEST NUMBER: P582287
 CATALOG NUMBER: HCC6S35D010MW-HM63040827-61WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	168.5	4.8
10°-20°	479.7	13.8
20°-30°	684.8	19.6
30°-40°	717.3	20.6
40°-50°	604.0	17.3
50°-60°	429.9	12.3
60°-70°	251.6	7.2
70°-80°	119.1	3.4
80°-90°	30.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1333.1	38.2
0°-40°	2050.4	58.8
0°-60°	3084.2	88.5
0°-90°	3485.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3485.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1780	1780	1780	1780	1780	
5°	1811	1797	1773	1748	1741	174
15°	1867	1799	1680	1612	1605	527
25°	1751	1627	1427	1359	1362	801
35°	1374	1260	1080	1043	1063	853
45°	892	827	737	739	754	693
55°	550	503	457	457	462	495
65°	321	284	246	207	204	320
75°	148	124	97	95	100	159
85°	27	22	24	29	29	35
90°	0	0	0	0	0	



TEST NUMBER: P582287

CATALOG NUMBER: HCC6S35D010MW-HM63040827-61WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1779.8	1779.8	1779.8	1779.8	1779.8	1779.8	1779.8	1779.8	1779.8
2.5°	1782.2	1782.2	1779.8	1777.3	1772.6	1765.2	1760.4	1755.5	1755.5
5°	1811.4	1806.5	1796.8	1784.7	1772.6	1758.0	1748.2	1740.9	1740.9
7.5°	1835.7	1826.0	1806.5	1784.7	1762.8	1743.4	1726.3	1716.7	1714.2
10°	1845.5	1833.4	1804.2	1770.1	1736.0	1709.3	1689.8	1677.7	1677.7
12.5°	1855.2	1840.6	1801.7	1753.1	1709.3	1672.8	1653.4	1643.6	1641.3
15°	1867.3	1847.9	1799.3	1738.5	1680.1	1638.8	1612.1	1604.7	1604.7
17.5°	1867.3	1843.0	1782.2	1706.9	1633.9	1587.7	1563.4	1556.1	1558.5
20°	1845.5	1818.8	1745.8	1653.4	1573.1	1524.6	1500.2	1495.4	1497.7
22.5°	1804.2	1772.6	1689.8	1590.2	1502.6	1451.6	1429.7	1429.7	1427.2
25°	1750.6	1716.7	1626.7	1522.1	1427.2	1376.2	1359.2	1361.7	1361.7
27.5°	1680.1	1646.1	1556.1	1444.3	1349.4	1298.4	1286.3	1291.1	1293.5
30°	1592.6	1556.1	1461.3	1351.9	1264.3	1213.3	1206.0	1213.3	1215.8
32.5°	1485.6	1458.9	1366.4	1254.6	1171.9	1128.1	1125.8	1133.0	1142.7
35°	1373.8	1344.6	1259.5	1157.3	1079.6	1043.1	1043.1	1055.2	1062.6
37.5°	1252.2	1223.0	1145.2	1060.1	994.5	960.4	965.2	977.5	979.9
40°	1123.4	1101.4	1035.8	962.9	906.9	880.2	887.5	899.6	902.1
42.5°	1001.8	982.3	928.8	863.1	821.8	802.4	812.1	826.7	831.6
45°	892.3	870.5	826.7	770.8	736.7	727.0	739.2	748.9	753.8
47.5°	792.6	773.3	736.7	685.6	661.3	656.4	668.7	673.5	678.4
50°	705.1	685.6	649.2	603.0	583.5	583.5	593.3	598.1	595.8
52.5°	620.0	603.0	568.9	530.1	517.9	517.9	525.2	527.6	532.5
55°	549.5	532.5	503.3	466.8	457.1	452.2	457.1	457.1	462.0
57.5°	483.8	469.3	442.5	408.4	396.3	391.4	389.1	386.6	391.4
60°	425.5	413.4	384.2	355.0	345.3	333.1	323.4	313.7	316.1
62.5°	372.0	359.9	333.1	303.9	294.2	277.2	265.0	252.9	257.8
65°	320.9	308.8	284.5	260.1	245.5	226.2	206.7	199.3	204.2
67.5°	274.7	265.0	240.8	216.4	204.2	182.4	162.9	162.9	165.4
70°	228.5	218.8	199.3	177.5	162.9	143.4	136.2	138.6	138.6
72.5°	187.2	180.0	160.5	141.0	126.4	114.2	114.2	116.7	119.2
75°	148.3	143.4	124.1	107.0	97.2	90.0	94.9	97.2	99.7
77.5°	114.2	107.0	92.4	80.3	72.9	75.4	80.3	82.6	85.1
80°	80.3	77.8	65.7	58.4	55.9	58.4	63.3	65.7	65.7
82.5°	51.1	48.7	41.3	38.9	38.9	41.3	46.2	46.2	46.2
85°	26.7	24.3	21.9	21.9	24.3	26.7	29.2	29.2	29.2
87.5°	9.7	7.4	9.7	9.7	12.1	12.1	12.1	12.1	12.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)