

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593245

Luminaire Tested: **HCC6S35D010MB-HM63040850-61RWWC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593245
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S35D010MB-HM63040850-61RWWC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4239.4 lumens
Efficiency: N/A
Efficacy: 125.8 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.15 / 1.2
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593245
CATALOG NUMBER: HCC6S35D010MB-HM63040850-61RWWC

Luminous Intensity Polar Plot





TEST NUMBER: P593245

CATALOG NUMBER: HCC6S35D010MB-HM63040850-61RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88				88
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77				77
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	69	68				68
4	88	78	70	64	86	76	69	64	74	68	63	72	67	62	70	65	61	60				60
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53				53
6	76	64	56	50	74	63	56	50	62	55	50	60	54	49	58	53	49	47				47
7	71	59	51	45	69	58	50	45	56	50	45	55	49	45	54	48	44	42				42
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38				38
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35				35
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32				32

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	115117	115117	115117
5°	115711	116338	116338
10°	118952	116893	116420
15°	122731	117560	117560
20°	124167	114868	117523
25°	121682	109113	114285
30°	115094	101402	107352
35°	104159	92735	97306
40°	90613	83893	87156
45°	77427	74783	77427
50°	67947	65516	68185
55°	59286	55214	57384
60°	52408	45863	45227
65°	46503	36165	31002
70°	41033	25533	18705
75°	34948	14467	9044
80°	26045	4483	2683
85°	14341	1761	1761



TEST NUMBER: P593245
 CATALOG NUMBER: HCC6S35D010MB-HM63040850-61RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	201.4	4.8
10°-20°	589.3	13.9
20°-30°	860.7	20.3
30°-40°	902.7	21.3
40°-50°	760.5	17.9
50°-60°	532.8	12.6
60°-70°	285.7	6.7
70°-80°	95.8	2.3
80°-90°	10.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1651.5	39.0
0°-40°	2554.2	60.2
0°-60°	3847.5	90.8
0°-90°	4239.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4239.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2100	2100	2100	2100	2100	
5°	2103	2111	2114	2114	2114	202
15°	2162	2134	2071	2060	2071	610
25°	2012	1926	1804	1835	1889	922
35°	1556	1477	1386	1426	1454	966
45°	999	982	965	990	999	778
55°	620	600	578	589	600	558
65°	358	327	279	230	239	358
75°	165	128	68	43	43	175
85°	23	11	3	3	3	31
90°	0	0	0	0	0	



TEST NUMBER: P593245

CATALOG NUMBER: HCC6S35D010MB-HM63040850-61RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	2099.9	2099.9	2099.9	2099.9	2099.9	2099.9	2099.9	2099.9	2099.9
2.5°	2085.7	2085.7	2091.4	2097.1	2102.7	2102.7	2105.6	2108.4	2105.6
5°	2102.7	2102.7	2111.2	2114.1	2114.1	2111.2	2114.1	2114.1	2114.1
7.5°	2128.4	2122.7	2125.5	2119.9	2114.1	2111.2	2108.4	2108.4	2108.4
10°	2136.9	2131.2	2125.5	2114.1	2099.9	2091.4	2088.5	2091.4	2091.4
12.5°	2148.2	2142.6	2128.4	2105.6	2088.5	2074.2	2071.4	2077.1	2077.1
15°	2162.5	2156.8	2134.1	2097.1	2071.4	2057.2	2060.1	2065.7	2071.4
17.5°	2162.5	2151.1	2114.1	2065.7	2034.4	2020.2	2031.6	2045.9	2054.4
20°	2128.4	2116.9	2065.7	2006.0	1969.0	1960.4	1980.4	2006.0	2014.5
22.5°	2082.9	2060.1	2000.4	1929.2	1889.4	1889.4	1917.7	1949.1	1960.4
25°	2011.7	1994.6	1926.4	1843.9	1803.9	1801.1	1835.2	1877.9	1889.4
27.5°	1932.0	1909.2	1835.2	1749.9	1707.2	1710.1	1747.1	1789.7	1801.1
30°	1818.2	1789.7	1724.2	1641.7	1601.9	1613.4	1650.4	1681.6	1695.9
32.5°	1690.2	1664.5	1604.7	1528.0	1493.9	1505.2	1536.5	1564.9	1576.4
35°	1556.4	1528.0	1476.7	1408.5	1385.7	1397.1	1425.5	1448.2	1454.0
37.5°	1405.7	1385.7	1348.7	1294.7	1277.6	1291.8	1314.5	1328.7	1334.5
40°	1266.2	1249.2	1217.9	1178.0	1172.3	1183.7	1206.4	1215.0	1217.9
42.5°	1129.7	1115.4	1095.5	1067.0	1067.0	1078.4	1098.3	1104.0	1106.9
45°	998.7	990.2	981.7	958.9	964.6	978.8	990.2	998.7	998.7
47.5°	884.9	887.7	876.4	859.3	865.0	879.2	887.7	896.3	896.3
50°	796.7	788.2	776.8	759.7	768.2	779.7	791.0	796.7	799.5
52.5°	694.2	691.4	682.9	663.0	668.7	674.4	685.7	694.2	697.2
55°	620.3	611.7	600.4	577.7	577.7	583.3	589.0	594.7	600.4
57.5°	549.2	540.7	523.5	498.0	495.0	495.0	492.2	498.0	506.5
60°	478.0	475.2	449.5	426.8	418.3	409.7	398.3	401.2	412.5
62.5°	415.5	409.7	387.0	358.5	341.5	327.2	313.0	310.2	321.5
65°	358.5	352.8	327.2	298.8	278.8	253.2	230.5	230.5	239.0
67.5°	307.3	296.0	273.2	241.8	216.2	185.0	162.2	167.9	170.7
70°	256.0	247.5	222.0	190.7	159.3	128.0	113.8	116.7	116.7
72.5°	210.5	199.2	173.5	142.3	111.0	82.5	76.8	74.0	74.0
75°	165.0	153.7	128.0	96.7	68.3	48.3	42.7	42.7	42.7
77.5°	119.5	111.0	88.2	59.8	37.0	22.8	20.0	17.0	17.0
80°	82.5	74.0	54.0	31.3	14.2	8.5	8.5	8.5	8.5
82.5°	48.3	39.8	25.6	14.2	5.7	2.8	2.8	2.8	2.8
85°	22.8	17.0	11.4	5.7	2.8	2.8	2.8	2.8	2.8
87.5°	2.8	2.8	2.8	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)