

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582376

Luminaire Tested: **HCC6S35D010MW-HM63040930-61WWW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582376
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S35D010MW-HM63040930-61WWW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3395.1 lumens
Efficiency: N/A
Efficacy: 100.7 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582376
CATALOG NUMBER: HCC6S35D010MW-HM63040930-61WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582376

CATALOG NUMBER: HCC6S35D010MW-HM63040930-61WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87					87			
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76					76			
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66					66			
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58					58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51					51			
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46					46			
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42					42			
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38					38			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34					34			
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	99915	99915	99915
5°	104342	99626	95031
10°	107196	97905	89305
15°	109847	95784	83672
20°	110330	91445	76849
25°	108024	85620	70480
30°	102484	78727	64592
35°	93077	70758	57949
40°	81102	63018	52141
45°	70170	55153	45834
50°	61303	47495	40169
55°	54163	41738	34465
60°	48680	36576	29855
65°	43597	31819	28953
70°	38933	27120	27120
75°	33762	22854	25459
80°	27118	19384	23235
85°	18492	16983	20065



TEST NUMBER: P582376
 CATALOG NUMBER: HCC6S35D010MW-HM63040930-61WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.3	5.0
10°-20°	476.2	14.0
20°-30°	663.6	19.5
30°-40°	683.7	20.1
40°-50°	566.7	16.7
50°-60°	407.2	12.0
60°-70°	259.3	7.6
70°-80°	133.2	3.9
80°-90°	33.9	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1311.1	38.6
0°-40°	1994.8	58.8
0°-60°	2968.7	87.4
0°-90°	3395.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3395.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1823	1823	1823	1823	1823	
5°	1896	1867	1810	1751	1727	182
15°	1936	1862	1688	1533	1474	545
25°	1786	1663	1416	1234	1165	818
35°	1391	1278	1057	917	866	864
45°	905	841	711	621	591	701
55°	567	520	437	388	361	510
65°	336	299	245	213	223	337
75°	159	137	108	113	120	170
85°	29	27	27	29	32	38
90°	0	0	0	0	0	



TEST NUMBER: P582376

CATALOG NUMBER: HCC6S35D010MW-HM63040930-61WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1822.6	1822.6	1822.6	1822.6	1822.6	1822.6	1822.6	1822.6	1822.6
2.5°	1856.9	1849.6	1839.8	1830.0	1815.3	1798.1	1783.4	1778.5	1771.0
5°	1896.1	1886.3	1866.7	1842.2	1810.4	1778.5	1751.4	1734.3	1726.9
7.5°	1920.8	1908.5	1881.4	1839.8	1793.2	1746.5	1707.3	1682.8	1673.0
10°	1925.7	1913.4	1876.5	1820.2	1758.8	1695.1	1645.9	1616.5	1604.3
12.5°	1933.0	1915.9	1869.2	1803.0	1724.5	1650.8	1589.6	1552.8	1540.6
15°	1935.5	1915.9	1861.8	1781.0	1687.7	1599.4	1533.2	1489.0	1474.3
17.5°	1925.7	1903.6	1839.8	1741.6	1636.1	1543.0	1464.5	1417.9	1398.2
20°	1891.2	1866.7	1793.2	1682.8	1567.5	1469.4	1388.4	1339.4	1317.3
22.5°	1847.1	1815.3	1731.8	1614.1	1493.9	1390.8	1310.0	1260.8	1238.8
25°	1785.9	1756.3	1663.2	1538.1	1415.5	1307.5	1233.9	1182.4	1165.2
27.5°	1714.7	1680.4	1584.7	1459.6	1334.5	1226.5	1155.3	1108.8	1086.7
30°	1619.0	1587.1	1491.4	1366.3	1243.7	1143.1	1069.6	1030.2	1020.4
32.5°	1506.1	1479.2	1385.9	1268.2	1150.4	1057.3	995.9	954.3	944.5
35°	1390.8	1359.0	1278.0	1167.7	1057.3	973.9	917.4	880.6	865.9
37.5°	1265.7	1236.3	1167.7	1069.6	971.4	892.9	843.9	812.0	797.3
40°	1133.3	1111.2	1047.5	969.0	880.6	812.0	770.2	743.3	728.6
42.5°	1010.6	988.6	944.5	870.8	797.3	735.9	699.1	674.6	662.3
45°	905.1	885.5	841.4	777.6	711.4	659.8	620.6	603.5	591.2
47.5°	799.7	789.8	750.6	691.8	630.4	586.3	559.3	539.6	529.8
50°	718.8	706.5	669.6	608.4	556.9	522.5	498.0	480.8	471.0
52.5°	635.3	623.1	588.8	537.2	495.5	463.6	439.1	424.3	414.5
55°	566.7	556.9	520.0	473.5	436.7	409.6	387.6	370.4	360.6
57.5°	502.9	493.1	458.7	414.5	382.7	358.2	338.5	323.8	311.6
60°	444.0	436.7	402.3	360.6	333.6	309.1	291.9	279.6	272.3
62.5°	392.5	377.8	348.3	311.6	287.0	267.4	250.2	242.9	247.8
65°	336.1	328.7	299.2	267.4	245.3	225.7	213.4	218.3	223.2
67.5°	289.4	279.6	255.1	225.7	206.1	191.4	184.0	193.8	196.3
70°	242.9	233.0	211.0	186.5	169.2	159.4	159.4	166.8	169.2
72.5°	198.7	191.4	171.7	152.1	139.8	132.5	137.4	142.3	144.7
75°	159.4	152.1	137.4	120.2	107.9	107.9	112.8	117.8	120.2
77.5°	122.7	117.8	103.0	90.8	85.9	85.9	90.8	93.2	95.7
80°	85.9	81.0	73.6	66.3	61.4	66.3	71.2	71.2	73.6
82.5°	56.4	53.9	49.0	44.1	44.1	46.6	49.0	51.5	51.5
85°	29.4	29.4	27.0	24.5	27.0	29.4	29.4	31.9	31.9
87.5°	9.8	9.8	9.8	9.8	12.3	12.3	12.3	12.3	12.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)