

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582314

Luminaire Tested: **HCC6W35D010SL-HM63040835-61RWWC**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582314  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-14)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6W35D010SL-HM63040835-61RWWC  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4034.8 lumens  
Efficiency: N/A  
Efficacy: 119.7 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.15 / 1.2  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 33.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582314  
CATALOG NUMBER: HCC6W35D010SL-HM63040835-61RWWC

### Luminous Intensity Polar Plot





TEST NUMBER: P582314

CATALOG NUMBER: HCC6W35D010SL-HM63040835-61RWWC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88				88
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77				77
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	69	68				68
4	88	78	70	64	86	76	69	64	74	68	63	72	67	62	70	65	61	60				60
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53				53
6	76	64	56	50	74	63	56	50	62	55	50	60	54	49	58	53	49	47				47
7	71	59	51	45	69	58	50	45	56	50	45	55	49	45	54	48	44	42				42
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38				38
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35				35
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32				32

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	109558	109558	109558
5°	110131	110720	110720
10°	113208	111248	110797
15°	116805	111885	111885
20°	118170	109326	111852
25°	115809	103851	108762
30°	109536	96509	102168
35°	99133	88258	92608
40°	86233	79850	82948
45°	73690	71178	73690
50°	64663	62352	64902
55°	56428	52548	54612
60°	49875	43648	43056
65°	44259	34427	29497
70°	39061	24299	17791
75°	33275	13768	8599
80°	24782	4262	2589
85°	13649	1698	1698



TEST NUMBER: P582314  
 CATALOG NUMBER: HCC6W35D010SL-HM63040835-61RWWC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	191.7	4.8
10°-20°	560.9	13.9
20°-30°	819.2	20.3
30°-40°	859.1	21.3
40°-50°	723.8	17.9
50°-60°	507.1	12.6
60°-70°	271.9	6.7
70°-80°	91.2	2.3
80°-90°	9.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1571.8	39.0
0°-40°	2430.9	60.2
0°-60°	3661.8	90.8
0°-90°	4034.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4034.8	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1998	1998	1998	1998	1998	
5°	2001	2009	2012	2012	2012	192
15°	2058	2031	1971	1961	1971	581
25°	1915	1833	1717	1747	1798	877
35°	1481	1405	1319	1357	1384	919
45°	950	934	918	942	950	740
55°	590	571	550	560	571	531
65°	341	312	265	219	227	341
75°	157	122	65	41	41	167
85°	22	11	3	3	3	30
90°	0	0	0	0	0	



TEST NUMBER: P582314

CATALOG NUMBER: HCC6W35D010SL-HM63040835-61RWWC

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1998.5	1998.5	1998.5	1998.5	1998.5	1998.5	1998.5	1998.5	1998.5
2.5°	1985.0	1985.0	1990.4	1995.8	2001.3	2001.3	2004.0	2006.7	2004.0
5°	2001.3	2001.3	2009.3	2012.0	2012.0	2009.3	2012.0	2012.0	2012.0
7.5°	2025.6	2020.2	2022.9	2017.5	2012.0	2009.3	2006.7	2006.7	2006.7
10°	2033.7	2028.4	2022.9	2012.0	1998.5	1990.4	1987.8	1990.4	1990.4
12.5°	2044.6	2039.1	2025.6	2004.0	1987.8	1974.2	1971.4	1976.9	1976.9
15°	2058.1	2052.6	2031.0	1995.8	1971.4	1957.9	1960.6	1966.0	1971.4
17.5°	2058.1	2047.3	2012.0	1966.0	1936.3	1922.7	1933.5	1947.0	1955.2
20°	2025.6	2014.8	1966.0	1909.2	1874.0	1865.8	1884.8	1909.2	1917.3
22.5°	1982.3	1960.6	1903.7	1836.0	1798.1	1798.1	1825.2	1854.9	1865.8
25°	1914.6	1898.4	1833.4	1754.8	1716.9	1714.2	1746.6	1787.3	1798.1
27.5°	1838.7	1817.1	1746.6	1665.4	1624.8	1627.5	1662.7	1703.4	1714.2
30°	1730.4	1703.4	1641.0	1562.5	1524.6	1535.4	1570.7	1600.4	1614.0
32.5°	1608.6	1584.2	1527.4	1454.2	1421.8	1432.6	1462.4	1489.4	1500.3
35°	1481.3	1454.2	1405.4	1340.5	1318.8	1329.7	1356.8	1378.3	1383.8
37.5°	1337.7	1318.8	1283.6	1232.1	1215.9	1229.4	1251.1	1264.7	1270.0
40°	1205.0	1188.8	1159.1	1121.1	1115.8	1126.5	1148.2	1156.4	1159.1
42.5°	1075.0	1061.5	1042.6	1015.5	1015.5	1026.4	1045.3	1050.8	1053.5
45°	950.5	942.4	934.3	912.6	918.1	931.6	942.4	950.5	950.5
47.5°	842.2	844.9	834.1	817.8	823.2	836.7	844.9	853.1	853.1
50°	758.2	750.1	739.3	723.1	731.1	742.0	752.8	758.2	761.0
52.5°	660.8	658.1	649.9	631.0	636.4	641.8	652.6	660.8	663.4
55°	590.4	582.2	571.4	549.8	549.8	555.1	560.5	566.0	571.4
57.5°	522.7	514.5	498.3	473.9	471.2	471.2	468.4	473.9	482.1
60°	454.9	452.2	427.8	406.2	398.1	390.0	379.2	381.8	392.7
62.5°	395.4	390.0	368.3	341.2	325.0	311.5	297.9	295.1	306.0
65°	341.2	335.7	311.5	284.4	265.4	241.0	219.4	219.4	227.4
67.5°	292.5	281.6	260.0	230.1	205.9	176.0	154.4	159.8	162.4
70°	243.7	235.6	211.2	181.5	151.6	121.8	108.3	111.0	111.0
72.5°	200.4	189.5	165.2	135.4	105.6	78.5	73.2	70.4	70.4
75°	157.1	146.2	121.8	92.1	65.0	46.0	40.6	40.6	40.6
77.5°	113.8	105.6	83.9	56.8	35.2	21.7	18.9	16.2	16.2
80°	78.5	70.4	51.5	29.8	13.5	8.2	8.2	8.2	8.2
82.5°	46.0	37.9	24.4	13.5	5.4	2.7	2.7	2.7	2.7
85°	21.7	16.2	10.9	5.4	2.7	2.7	2.7	2.7	2.7
87.5°	2.7	2.7	2.7	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)