

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582351

Luminaire Tested: **HCC6S35D010MB-HM63040927-61RWWH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582351
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S35D010MB-HM63040927-61RWWH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3070.4 lumens
Efficiency: N/A
Efficacy: 91.1 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.12 / 1.19
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582351
CATALOG NUMBER: HCC6S35D010MB-HM63040927-61RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582351

CATALOG NUMBER: HCC6S35D010MB-HM63040927-61RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88		
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77		
3	95	86	79	74	93	84	78	73	82	76	72	79	74	70	77	73	69	67		
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59		
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53		
6	76	64	56	50	74	63	56	50	61	55	50	60	54	49	58	53	49	47		
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42		
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38		
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35		
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	85898	85898	85898
5°	86793	86000	85439
10°	88024	85737	84824
15°	90097	85199	84388
20°	90938	82666	82905
25°	88941	78507	80001
30°	84234	72929	75404
35°	76279	66655	69132
40°	66424	60256	62460
45°	56362	53331	55246
50°	49917	46591	47811
55°	43965	39846	39655
60°	39405	33550	30853
65°	35166	26903	22117
70°	30935	19410	13816
75°	26095	11734	7837
80°	20110	5209	3252
85°	11573	1321	1321



TEST NUMBER: P582351
 CATALOG NUMBER: HCC6S35D010MB-HM63040927-61RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.7	4.8
10°-20°	427.5	13.9
20°-30°	617.9	20.1
30°-40°	650.2	21.2
40°-50°	546.6	17.8
50°-60°	383.6	12.5
60°-70°	211.0	6.9
70°-80°	74.9	2.4
80°-90°	9.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1194.2	38.9
0°-40°	1844.4	60.1
0°-60°	2774.6	90.4
0°-90°	3070.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3070.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1567	1567	1567	1567	1567	
5°	1577	1573	1563	1557	1553	151
15°	1588	1561	1501	1483	1487	448
25°	1470	1396	1298	1300	1323	673
35°	1140	1074	996	1017	1033	706
45°	727	706	688	704	713	570
55°	460	435	417	417	415	414
65°	271	242	207	170	170	270
75°	123	99	55	37	37	132
85°	18	10	2	2	2	25
90°	0	0	0	0	0	



TEST NUMBER: P582351

CATALOG NUMBER: HCC6S35D010MB-HM63040927-61RWWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1566.9	1566.9	1566.9	1566.9	1566.9	1566.9	1566.9	1566.9	1566.9
2.5°	1566.9	1566.9	1564.8	1564.8	1560.7	1560.7	1558.8	1558.8	1558.8
5°	1577.2	1577.2	1573.1	1566.9	1562.8	1556.7	1556.7	1554.6	1552.6
7.5°	1583.4	1581.3	1575.1	1566.9	1556.7	1546.4	1542.3	1544.3	1542.3
10°	1581.3	1577.2	1569.0	1552.6	1540.2	1525.9	1523.8	1521.8	1523.8
12.5°	1585.4	1579.2	1562.8	1542.3	1521.8	1505.3	1503.2	1503.2	1505.3
15°	1587.5	1581.3	1560.7	1529.9	1501.2	1484.8	1482.7	1484.8	1486.9
17.5°	1581.3	1573.1	1542.3	1501.2	1468.3	1451.9	1451.9	1456.1	1460.2
20°	1558.8	1546.4	1503.2	1454.0	1417.0	1404.7	1408.8	1417.0	1421.1
22.5°	1517.7	1503.2	1454.0	1398.5	1359.6	1349.3	1359.6	1369.8	1373.9
25°	1470.4	1454.0	1396.4	1339.0	1297.9	1285.6	1299.9	1316.4	1322.6
27.5°	1406.7	1388.3	1334.8	1269.1	1228.0	1222.0	1238.3	1256.9	1260.9
30°	1330.7	1310.2	1250.7	1189.1	1152.1	1150.1	1168.5	1185.0	1191.2
32.5°	1238.3	1219.9	1168.5	1106.9	1074.1	1074.1	1092.5	1106.9	1113.1
35°	1139.8	1119.3	1074.1	1022.8	996.0	998.0	1016.6	1026.8	1033.0
37.5°	1022.8	1016.6	981.7	938.5	920.1	924.1	938.5	946.7	952.9
40°	928.2	911.8	889.3	854.4	842.0	846.1	860.4	868.7	872.8
42.5°	825.5	815.3	796.8	772.2	763.9	770.1	782.5	788.5	786.6
45°	727.0	724.9	706.5	692.0	687.9	696.2	704.4	710.6	712.6
47.5°	655.2	646.9	630.4	620.1	616.1	624.3	632.5	636.6	636.6
50°	585.3	577.1	560.6	550.4	546.3	554.4	560.6	564.7	560.6
52.5°	515.5	507.3	492.8	480.6	478.5	482.6	484.7	486.8	490.8
55°	460.0	451.7	435.4	420.9	416.9	419.0	416.9	416.9	414.9
57.5°	406.6	398.4	382.0	365.5	359.4	357.3	351.2	349.2	347.1
60°	359.4	349.2	332.7	314.2	306.0	297.8	287.5	281.4	281.4
62.5°	314.2	303.9	285.4	269.0	256.7	242.4	225.9	217.6	217.6
65°	271.1	262.8	242.4	223.8	207.4	188.9	170.5	166.3	170.5
67.5°	230.0	221.8	201.3	182.8	162.2	139.7	123.2	123.2	127.3
70°	193.0	184.9	166.3	143.8	121.1	98.6	86.2	86.2	86.2
72.5°	158.1	150.0	129.4	108.9	86.2	63.7	57.5	59.5	57.5
75°	123.2	117.1	98.6	76.0	55.4	39.0	37.0	34.9	37.0
77.5°	92.4	86.2	69.8	49.2	30.8	22.6	20.5	20.5	20.5
80°	63.7	57.5	45.2	28.7	16.5	10.3	10.3	10.3	10.3
82.5°	39.0	32.9	24.6	14.4	6.2	6.2	6.2	6.2	6.2
85°	18.4	14.4	10.3	4.1	2.1	2.1	2.1	2.1	2.1
87.5°	4.1	4.1	2.1	2.1	0.0	2.1	2.1	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)