

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582448

Luminaire Tested: **HCC6W40D010BZ-HM63040830-61WWW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582448
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W40D010BZ-HM63040830-61WWW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4193.6 lumens
Efficiency: N/A
Efficacy: 102.3 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582448
CATALOG NUMBER: HCC6W40D010BZ-HM63040830-61WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582448

CATALOG NUMBER: HCC6W40D010BZ-HM63040830-61WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76								
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66								
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58								
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51								
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	123417	123417	123417
5°	128885	123052	117384
10°	132407	120934	110313
15°	135682	118315	103349
20°	136284	112955	94922
25°	133429	105750	87059
30°	126595	97243	79784
35°	114974	87395	71581
40°	100181	77846	64406
45°	86683	68123	56611
50°	75716	58668	49619
55°	66903	51544	42570
60°	60127	45183	36872
65°	53845	39304	35763
70°	48069	33515	33515
75°	41705	28255	31454
80°	33464	23898	28697
85°	22895	21008	24782



TEST NUMBER: P582448
 CATALOG NUMBER: HCC6W40D010BZ-HM63040830-61WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	211.6	5.0
10°-20°	588.2	14.0
20°-30°	819.7	19.5
30°-40°	844.6	20.1
40°-50°	699.9	16.7
50°-60°	503.0	12.0
60°-70°	320.3	7.6
70°-80°	164.5	3.9
80°-90°	41.8	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1619.4	38.6
0°-40°	2464.0	58.8
0°-60°	3667.0	87.4
0°-90°	4193.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4193.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2251	2251	2251	2251	2251	
5°	2342	2306	2236	2163	2133	225
15°	2391	2300	2085	1894	1821	674
25°	2206	2054	1748	1524	1439	1011
35°	1718	1579	1306	1133	1070	1067
45°	1118	1039	879	767	730	865
55°	700	642	539	479	445	631
65°	415	370	303	264	276	416
75°	197	170	133	139	148	210
85°	36	33	33	36	39	47
90°	0	0	0	0	0	



TEST NUMBER: P582448

CATALOG NUMBER: HCC6W40D010BZ-HM63040830-61WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	2251.3	2251.3	2251.3	2251.3	2251.3	2251.3	2251.3	2251.3	2251.3
2.5°	2293.7	2284.6	2272.5	2260.4	2242.2	2221.1	2202.9	2196.8	2187.7
5°	2342.1	2330.1	2305.9	2275.5	2236.1	2196.8	2163.4	2142.2	2133.1
7.5°	2372.5	2357.3	2324.1	2272.5	2215.0	2157.4	2108.9	2078.6	2066.5
10°	2378.6	2363.4	2318.0	2248.2	2172.5	2093.8	2033.1	1996.8	1981.7
12.5°	2387.7	2366.4	2308.9	2227.0	2130.1	2039.2	1963.5	1918.0	1902.8
15°	2390.7	2366.4	2299.8	2199.8	2084.7	1975.6	1893.8	1839.2	1821.0
17.5°	2378.6	2351.2	2272.5	2151.3	2021.0	1905.8	1808.9	1751.4	1727.1
20°	2336.1	2305.9	2215.0	2078.6	1936.2	1814.9	1715.0	1654.4	1627.1
22.5°	2281.6	2242.2	2139.2	1993.8	1845.3	1718.0	1618.0	1557.5	1530.2
25°	2205.9	2169.5	2054.3	1899.8	1748.3	1615.0	1524.1	1460.5	1439.3
27.5°	2117.9	2075.6	1957.4	1802.8	1648.4	1515.0	1427.2	1369.5	1342.3
30°	1999.9	1960.4	1842.2	1687.7	1536.2	1412.0	1321.1	1272.6	1260.4
32.5°	1860.4	1827.1	1711.9	1566.6	1421.1	1305.9	1230.2	1178.7	1166.5
35°	1718.0	1678.7	1578.6	1442.3	1305.9	1202.9	1133.3	1087.8	1069.6
37.5°	1563.5	1527.1	1442.3	1321.1	1199.9	1102.9	1042.3	1003.0	984.8
40°	1399.9	1372.6	1293.8	1196.9	1087.8	1003.0	951.4	918.2	900.0
42.5°	1248.3	1221.1	1166.5	1075.6	984.8	909.1	863.5	833.2	818.0
45°	1118.1	1093.8	1039.2	960.5	878.7	815.0	766.6	745.4	730.2
47.5°	987.8	975.7	927.1	854.4	778.7	724.1	690.9	666.6	654.5
50°	887.8	872.7	827.1	751.4	687.9	645.4	615.0	593.9	581.8
52.5°	784.8	769.6	727.2	663.6	612.0	572.7	542.4	524.2	512.0
55°	700.0	687.9	642.4	584.8	539.3	506.0	478.8	457.6	445.4
57.5°	621.1	609.0	566.6	512.0	472.7	442.4	418.1	399.9	384.8
60°	548.4	539.3	496.9	445.4	412.1	381.7	360.6	345.4	336.3
62.5°	484.9	466.7	430.3	384.8	354.5	330.3	309.0	299.9	306.0
65°	415.1	406.0	369.7	330.3	303.0	278.7	263.7	269.7	275.7
67.5°	357.6	345.4	315.1	278.7	254.6	236.4	227.3	239.4	242.4
70°	299.9	287.8	260.6	230.3	209.1	196.9	196.9	206.0	209.1
72.5°	245.5	236.4	212.1	187.8	172.7	163.6	169.6	175.7	178.7
75°	196.9	187.8	169.6	148.5	133.4	133.4	139.4	145.5	148.5
77.5°	151.6	145.5	127.3	112.1	106.0	106.0	112.1	115.1	118.2
80°	106.0	100.0	90.9	81.8	75.7	81.8	87.8	87.8	90.9
82.5°	69.6	66.6	60.5	54.5	54.5	57.5	60.5	63.6	63.6
85°	36.4	36.4	33.4	30.3	33.4	36.4	36.4	39.4	39.4
87.5°	12.1	12.1	12.1	12.1	15.2	15.2	15.2	15.2	15.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)