

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582357

Luminaire Tested: **HCC6W35D010BZ-HM63040927-61WWBB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582357
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W35D010BZ-HM63040927-61WWBB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2602.1 lumens
Efficiency: N/A
Efficacy: 77.2 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582357
CATALOG NUMBER: HCC6W35D010BZ-HM63040927-61WWBB

Luminous Intensity Polar Plot





TEST NUMBER: P582357

CATALOG NUMBER: HCC6W35D010BZ-HM63040927-61WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89								
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78								
3	96	87	80	75	93	86	79	74	83	77	73	80	76	72	78	74	71	69								
4	89	79	71	66	87	78	71	65	75	69	64	73	68	64	71	66	63	61								
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54								
6	77	65	58	52	75	65	57	52	63	56	51	61	55	51	60	55	51	49								
7	72	60	52	47	70	59	52	47	58	51	46	56	51	46	55	50	46	44								
8	67	55	48	43	66	55	47	42	53	47	42	52	46	42	51	46	42	40								
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37								
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	80048	80048	80048
5°	81598	79903	78092
10°	84367	78884	75566
15°	86947	77509	73201
20°	88301	74282	69370
25°	86709	69191	64594
30°	82418	63048	59281
35°	74077	56349	53465
40°	63927	49378	47761
45°	54130	42516	41400
50°	46421	35914	35555
55°	40247	30231	29055
60°	35118	24538	20711
65°	30898	18913	11454
70°	26655	12518	5594
75°	22621	6079	2182
80°	17490	2589	1294
85°	10378	1321	1321



TEST NUMBER: P582357

CATALOG NUMBER: HCC6W35D010BZ-HM63040927-61WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.8	5.3
10°-20°	389.7	15.0
20°-30°	548.7	21.1
30°-40°	560.6	21.5
40°-50°	452.0	17.4
50°-60°	303.2	11.7
60°-70°	153.4	5.9
70°-80°	49.0	1.9
80°-90°	7.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1076.2	41.4
0°-40°	1636.8	62.9
0°-60°	2392.0	91.9
0°-90°	2602.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2602.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1460	1460	1460	1460	1460	
5°	1483	1472	1452	1429	1419	143
15°	1532	1470	1366	1304	1290	433
25°	1434	1321	1144	1074	1068	656
35°	1107	1006	842	795	799	689
45°	698	643	548	530	534	543
55°	421	374	316	302	304	379
65°	238	197	146	96	88	238
75°	107	76	29	10	10	115
85°	16	8	2	2	2	22
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582357

CATALOG NUMBER: HCC6W35D010BZ-HM63040927-61WWBB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1460.2	1460.2	1460.2	1460.2	1460.2	1460.2	1460.2	1460.2	1460.2
2.5°	1466.3	1464.2	1462.3	1458.2	1452.0	1445.8	1441.7	1437.6	1435.5
5°	1482.8	1478.7	1472.5	1464.2	1452.0	1437.6	1429.3	1421.2	1419.1
7.5°	1505.3	1497.1	1480.7	1462.3	1441.7	1421.2	1406.8	1398.5	1392.5
10°	1515.6	1501.2	1478.7	1447.9	1417.1	1392.5	1373.9	1361.7	1357.5
12.5°	1523.9	1507.4	1474.5	1433.5	1392.5	1359.6	1339.0	1328.7	1324.7
15°	1532.0	1515.6	1470.4	1417.1	1365.7	1326.6	1304.1	1293.9	1289.8
17.5°	1532.0	1509.5	1456.1	1388.3	1326.6	1279.5	1256.9	1246.6	1244.5
20°	1513.6	1489.0	1423.3	1343.1	1273.3	1219.9	1199.3	1193.3	1189.1
22.5°	1478.7	1449.9	1376.0	1285.6	1209.6	1158.2	1135.7	1131.6	1127.4
25°	1433.5	1404.7	1320.6	1224.1	1143.9	1092.5	1074.1	1070.0	1067.9
27.5°	1376.0	1345.2	1256.9	1158.2	1072.0	1022.8	1006.3	1006.3	1004.3
30°	1302.0	1267.1	1180.9	1082.3	996.0	950.9	938.5	938.5	936.5
32.5°	1211.7	1176.8	1098.7	1004.3	922.2	874.9	864.6	868.7	866.6
35°	1106.9	1078.2	1006.3	913.9	842.0	798.9	794.7	798.9	798.9
37.5°	1002.2	975.5	913.9	833.8	766.0	727.0	727.0	733.2	731.1
40°	893.3	872.8	815.3	745.5	690.0	663.3	659.2	665.4	667.4
42.5°	790.6	774.3	724.9	667.4	618.2	591.4	597.6	601.7	603.8
45°	698.2	681.9	642.8	583.3	548.4	529.8	529.8	536.0	534.0
47.5°	616.1	603.8	564.7	507.3	476.5	468.2	472.4	476.5	476.5
50°	544.3	525.7	488.7	443.6	421.1	410.8	414.9	416.9	416.9
52.5°	476.5	464.1	427.1	386.0	365.5	359.4	359.4	361.4	361.4
55°	421.1	406.6	373.8	332.7	316.3	308.1	301.9	299.8	304.0
57.5°	367.6	355.2	324.5	285.4	267.0	258.7	246.5	242.4	246.5
60°	320.3	310.1	279.3	242.4	223.8	207.4	193.0	184.9	188.9
62.5°	279.3	267.0	236.2	205.4	184.9	166.3	143.8	131.4	137.6
65°	238.2	227.9	197.1	166.3	145.8	123.2	96.5	88.3	88.3
67.5°	201.3	191.0	162.2	135.5	110.9	84.3	59.5	57.5	59.5
70°	166.3	156.0	131.4	104.8	78.1	51.3	34.9	34.9	34.9
72.5°	137.6	125.2	102.7	76.0	49.2	26.7	18.4	20.5	20.5
75°	106.8	96.5	76.0	51.3	28.7	12.4	10.3	10.3	10.3
77.5°	80.1	71.9	53.4	32.9	14.4	4.1	4.1	4.1	4.1
80°	55.4	47.3	34.9	20.5	8.2	4.1	4.1	4.1	4.1
82.5°	32.9	28.7	20.5	10.3	4.1	2.1	2.1	2.1	2.1
85°	16.5	14.4	8.2	4.1	2.1	2.1	2.1	2.1	2.1
87.5°	4.1	4.1	2.1	2.1	0.0	2.1	2.1	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)