

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582447

Luminaire Tested: **HCC6W40D010MW-HM63040830-61WWBB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582447
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W40D010MW-HM63040830-61WWBB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3839.2 lumens
Efficiency: N/A
Efficacy: 93.6 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582447
CATALOG NUMBER: HCC6W40D010MW-HM63040830-61WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582447

CATALOG NUMBER: HCC6W40D010MW-HM63040830-61WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89								
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78								
3	96	87	80	75	93	86	79	74	83	77	73	80	76	72	78	74	71	69								
4	89	79	71	66	87	78	71	65	75	69	64	73	68	64	71	66	63	61								
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54								
6	77	65	58	52	75	65	57	52	63	56	51	61	55	51	60	55	51	49								
7	72	60	52	47	70	59	52	47	58	51	46	56	51	46	55	50	46	44								
8	67	55	48	43	66	55	47	42	53	47	42	52	46	42	51	46	42	40								
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37								
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	118099	118099	118099
5°	120388	117884	115221
10°	124480	116381	111493
15°	128287	114359	107997
20°	130281	109600	102349
25°	127931	102091	95310
30°	121601	93027	87463
35°	109299	83145	78882
40°	94327	72858	70475
45°	79877	62727	61076
50°	68484	52971	52450
55°	59362	44605	42866
60°	51827	36214	30557
65°	45595	27902	16902
70°	39350	18449	8271
75°	33381	9002	3219
80°	25824	3820	1926
85°	15284	1887	1887



TEST NUMBER: P582447
 CATALOG NUMBER: HCC6W40D010MW-HM63040830-61WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	203.3	5.3
10°-20°	574.9	15.0
20°-30°	809.6	21.1
30°-40°	827.2	21.5
40°-50°	666.9	17.4
50°-60°	447.3	11.7
60°-70°	226.4	5.9
70°-80°	72.4	1.9
80°-90°	11.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1587.8	41.4
0°-40°	2415.0	62.9
0°-60°	3529.3	91.9
0°-90°	3839.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3839.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2154	2154	2154	2154	2154	
5°	2188	2172	2142	2109	2094	211
15°	2260	2170	2015	1924	1903	638
25°	2115	1948	1688	1585	1576	968
35°	1633	1485	1242	1173	1179	1016
45°	1030	948	809	782	788	801
55°	621	552	467	445	448	559
65°	352	291	215	142	130	351
75°	158	112	42	15	15	169
85°	24	12	3	3	3	33
90°	0	0	0	0	0	



TEST NUMBER: P582447

CATALOG NUMBER: HCC6W40D010MW-HM63040830-61WWBB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	2154.3	2154.3	2154.3	2154.3	2154.3	2154.3	2154.3	2154.3	2154.3
2.5°	2163.4	2160.4	2157.4	2151.3	2142.2	2133.2	2127.2	2121.1	2118.1
5°	2187.7	2181.6	2172.5	2160.4	2142.2	2121.1	2108.9	2096.8	2093.8
7.5°	2221.1	2208.9	2184.7	2157.4	2127.2	2096.8	2075.6	2063.4	2054.3
10°	2236.2	2215.0	2181.6	2136.1	2090.7	2054.3	2027.0	2009.0	2002.9
12.5°	2248.2	2224.1	2175.6	2115.0	2054.3	2005.9	1975.6	1960.4	1954.4
15°	2260.4	2236.2	2169.5	2090.7	2015.0	1957.4	1924.0	1909.0	1902.9
17.5°	2260.4	2227.1	2148.3	2048.3	1957.4	1887.8	1854.4	1839.2	1836.2
20°	2233.2	2196.8	2099.8	1981.7	1878.7	1799.9	1769.6	1760.5	1754.4
22.5°	2181.6	2139.2	2030.1	1896.9	1784.7	1708.9	1675.7	1669.6	1663.5
25°	2115.0	2072.5	1948.3	1805.8	1687.8	1611.9	1584.8	1578.7	1575.7
27.5°	2030.1	1984.7	1854.4	1708.9	1581.7	1508.9	1484.7	1484.7	1481.6
30°	1921.0	1869.6	1742.3	1596.8	1469.6	1402.9	1384.7	1384.7	1381.7
32.5°	1787.8	1736.2	1621.1	1481.6	1360.5	1290.8	1275.6	1281.7	1278.6
35°	1633.2	1590.7	1484.7	1348.4	1242.4	1178.7	1172.6	1178.7	1178.7
37.5°	1478.6	1439.3	1348.4	1230.2	1130.3	1072.6	1072.6	1081.7	1078.7
40°	1318.1	1287.7	1202.9	1099.9	1018.1	978.7	972.6	981.7	984.8
42.5°	1166.5	1142.4	1069.6	984.8	912.1	872.7	881.8	887.8	890.9
45°	1030.3	1006.0	948.4	860.5	809.1	781.8	781.8	790.9	787.8
47.5°	909.1	890.9	833.2	748.4	703.0	690.9	697.0	703.0	703.0
50°	803.0	775.7	721.1	654.5	621.1	605.9	612.0	615.0	615.0
52.5°	703.0	684.8	630.2	569.7	539.3	530.2	530.2	533.3	533.3
55°	621.1	600.0	551.5	490.9	466.7	454.5	445.4	442.4	448.5
57.5°	542.4	524.2	478.8	421.2	393.9	381.9	363.6	357.6	363.6
60°	472.7	457.6	412.1	357.6	330.3	306.0	284.8	272.8	278.7
62.5°	412.1	393.9	348.5	303.0	272.8	245.5	212.1	193.9	203.0
65°	351.5	336.3	290.8	245.5	215.1	181.8	142.5	130.3	130.3
67.5°	296.9	281.7	239.4	200.0	163.7	124.2	87.8	84.8	87.8
70°	245.5	230.3	193.9	154.6	115.1	75.7	51.6	51.6	51.6
72.5°	203.0	184.8	151.6	112.1	72.7	39.4	27.3	30.3	30.3
75°	157.6	142.5	112.1	75.7	42.5	18.2	15.2	15.2	15.2
77.5°	118.2	106.0	78.7	48.5	21.2	6.1	6.1	6.1	6.1
80°	81.8	69.6	51.6	30.3	12.1	6.1	6.1	6.1	6.1
82.5°	48.5	42.5	30.3	15.2	6.1	3.0	3.0	3.0	3.0
85°	24.3	21.2	12.1	6.1	3.0	3.0	3.0	3.0	3.0
87.5°	6.1	6.1	3.0	3.0	0.0	3.0	3.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)