

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582355

Luminaire Tested: **HCC6S35D010SL-HM63040927-61WDW**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582355  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-9)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S35D010SL-HM63040927-61WDW  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2998.5 lumens  
Efficiency: N/A  
Efficacy: 89.0 lumens/watt  
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.09  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 33.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582355  
CATALOG NUMBER: HCC6S35D010SL-HM63040927-61WDW

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P582355

CATALOG NUMBER: HCC6S35D010SL-HM63040927-61WDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89			89
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78			78
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69			69
4	89	80	72	67	87	78	72	66	76	70	66	74	69	65	72	67	64	62			62
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	61	58	56			56
6	78	67	59	54	76	66	59	54	64	58	53	63	57	53	61	56	52	51			51
7	73	62	54	49	72	61	54	49	60	53	48	58	52	48	57	52	48	46			46
8	69	57	50	45	68	57	50	45	55	49	44	54	48	44	53	48	44	42			42
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39			39
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	47	41	38	36			36

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	102322
5°	102261
10°	101267
15°	100222
20°	97390
25°	93278
30°	86570
35°	74485
40°	54366
45°	37252
50°	29952
55°	26102
60°	24088
65°	22908
70°	21398
75°	19995
80°	18153
85°	15473



TEST NUMBER: P582355  
 CATALOG NUMBER: HCC6S35D010SL-HM63040927-61WDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	176.2	5.9
10°-20°	495.9	16.5
20°-30°	705.4	23.5
30°-40°	679.1	22.6
40°-50°	390.7	13.0
50°-60°	247.6	8.3
60°-70°	175.2	5.8
70°-80°	99.9	3.3
80°-90°	28.5	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1377.5	45.9
0°-40°	2056.5	68.6
0°-60°	2694.8	89.9
0°-90°	2998.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2998.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1866	
5°	1858	176
15°	1766	496
25°	1542	705
35°	1113	679
45°	480	391
55°	273	248
65°	177	175
75°	94	100
85°	25	28
90°	0	



TEST NUMBER: P582355

CATALOG NUMBER: HCC6S35D010SL-HM63040927-61WDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1866.5
2.5°	1858.3
5°	1858.3
7.5°	1846.0
10°	1819.2
12.5°	1792.6
15°	1765.9
17.5°	1724.8
20°	1669.4
22.5°	1607.8
25°	1542.1
27.5°	1462.0
30°	1367.6
32.5°	1252.5
35°	1113.0
37.5°	942.5
40°	759.7
42.5°	599.6
45°	480.5
47.5°	404.5
50°	351.2
52.5°	308.0
55°	273.1
57.5°	242.3
60°	219.7
62.5°	199.2
65°	176.6
67.5°	156.0
70°	133.5
72.5°	113.0
75°	94.4
77.5°	76.0
80°	57.5
82.5°	41.1
85°	24.6
87.5°	10.3
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)